

Antenna cable - RAD-CON-MCX90-N-SS - 2885207

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Antenna cable, outside diameter: 2.5 mm (0.1 in.), inner conductor: stranded, attenuation: 0.9 dB at 900 MHz, connection: 90° MCX (male) -> N (male), cable length: 1.2 m (4 ft.)

Your advantages

- ✓ Easy installation, thanks to flexible inner conductor
- ✓ For indoors

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 017918 986513
GTIN	4017918986513

Technical data

Dimensions

Fixed cable length	1.2 m
External diameter	2.50 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 75 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C

General

Connection 1	Connector connection
Connection method	Type 90° MCX (male)
Connection 2	Connector connection
Connection method	Type N (male)
Cable type	RG 316
Outer sheath, material	Fluorinated ethylene propylene (FEP)
Minimum bending radius	25.40 mm

Antenna cable - RAD-CON-MCX90-N-SS - 2885207

Technical data

General

Frequency range	0.1 GHz ... 1 GHz
Impedance	50 Ω

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Classifications

eCl@ss

eCl@ss 10.0.1	27060310
eCl@ss 4.0	27060800
eCl@ss 4.1	27060800
eCl@ss 5.0	27061800
eCl@ss 5.1	27061800
eCl@ss 6.0	27061800
eCl@ss 7.0	27061802
eCl@ss 8.0	27060310
eCl@ss 9.0	27060310

ETIM

ETIM 2.0	EC000019
ETIM 3.0	EC000019
ETIM 4.0	EC000019
ETIM 5.0	EC001682
ETIM 6.0	EC001682
ETIM 7.0	EC001682

UNSPSC

UNSPSC 6.01	26121608
UNSPSC 7.0901	26121608
UNSPSC 11	26121608
UNSPSC 12.01	26121608
UNSPSC 13.2	26121606
UNSPSC 18.0	26121606
UNSPSC 19.0	26121606
UNSPSC 20.0	26121606
UNSPSC 21.0	26121606

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

2885207