

Front adapters - FLKM S135/S400/SO122 - 2301749

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



The FLKM S135/S400/SO adapter links a SIMATIC® S5 plug directly with the basic SIMATIC® S7 400 card.
Conversion: S5 card 6ES5 432-4UA12 to S7 card 6ES7-421-1BL01-0AA0

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 017918 962487
GTIN	4017918962487

Technical data

Note

Type of note	Notes on operation
Note	The LEDs of the S7-400 module are hidden.

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Degree of protection	IP00

General

Max. permissible operating voltage	60 V DC
Max. permissible current	4 A (per path)
	4 A (per connection, supply via separate power supply)
Mounting position	any

Connection data

Connection name	Field level
Connection method	SIEMENS S5-135 U pin strip

Supported controller

Controller	SIEMENS S5-135 U
------------	------------------

Front adapters - FLKM S135/S400/SO122 - 2301749

Technical data

Supported controller


- suitable I/O card	6ES5 432-4UA12
Controller	SIEMENS S7-400
- suitable I/O card	6ES7 421-1BL01-0AA0

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50 years
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"


Drawings

Connection diagram



Connection scheme: FLKM S135/S400/SO122

Circuit diagram



Connection scheme: FLKM S135/S400/SO122

Front adapters - FLKM S135/S400/SO122 - 2301749

Classifications

eCl@ss

eCl@ss 4.0	27250300
eCl@ss 4.1	27250300
eCl@ss 5.0	27250300
eCl@ss 5.1	27250300
eCl@ss 6.0	27249200
eCl@ss 7.0	27249290
eCl@ss 8.0	27249290
eCl@ss 9.0	27242292

ETIM

ETIM 4.0	EC002584
ETIM 5.0	EC002584
ETIM 6.0	EC002584
ETIM 7.0	EC002584

UNSPSC

UNSPSC 6.01	30211824
UNSPSC 7.0901	39121421
UNSPSC 11	39121421
UNSPSC 12.01	39121421
UNSPSC 13.2	32151601
UNSPSC 19.0	32151601

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2301749](#)