

Active module - UM-32 OM-230AC/48DC/I/M/PLC - 2394982

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Module with 32 electrically isolated optocouplers, input 230 V AC (for input cards of the Delta V control system)

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 017918 995829
GTIN	4017918995829

Technical data

Dimensions

Width	240 mm
Height	125.5 mm
Depth	66 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

Input data

Nominal input voltage U_N	230 V AC $\pm 10\%$
Typical input current at U_N	1.1 mA
Type of protection	Surge protection
Protective circuit/component	Varistor
Switching level 0 signal ("L")	< 106 V AC
Switching level 1 signal ("H")	> 180 V AC
Transmission frequency	5 Hz

Output data

Nominal supply voltage	24 V DC
------------------------	---------

Active module - UM-32 OM-230AC/48DC/I/M/PLC - 2394982

Technical data

Output data

Supply voltage range	10 V DC ... 48 V DC
Continuous load current	10 mA
Status display	Yellow LED

General

No. of channels	32
Mounting position	any
Assembly instructions	In rows with zero spacing
Housing insulation material	PVC, side panel PA non-reinforced,
Color	green

Connection data

Connection name	Field level
Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Number of connections	66
Number of positions	6
Conductor cross section solid	0.2 mm ² ... 4 mm ²
Conductor cross section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross section AWG	24 ... 12

Connection data 2

Connection name	Controller level
Connection method	IDC/FLK pin strip
Number of connections	1
Number of positions	50
Pitch	2.54 mm

Supported controller

Controller	Emerson DeltaV
- suitable I/O card	VE4001S2T2B5

Standards and Regulations

Standards/regulations	DIN EN 50178
Rated surge voltage	4 kV (basic insulation)
Pollution degree	2
Overvoltage category	III


Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Active module - UM-32 OM-230AC/48DC/I/M/PLC - 2394982

Drawings

Connection diagram



Classifications

eCl@ss

eCl@ss 4.0	27371100
eCl@ss 4.1	27371100
eCl@ss 5.0	27371000
eCl@ss 5.1	27371000
eCl@ss 6.0	27371000
eCl@ss 7.0	27141152
eCl@ss 8.0	27141152
eCl@ss 9.0	27141152

ETIM

ETIM 5.0	EC002780
ETIM 6.0	EC002780
ETIM 7.0	EC002780

UNSPSC

UNSPSC 6.01	30211916
UNSPSC 7.0901	39121515
UNSPSC 11	39121515
UNSPSC 12.01	39121515
UNSPSC 13.2	39121432
UNSPSC 19.0	39121432

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

2394982