

Touch panel - TP121XIT-10/3051C240 S00018 - 2400892

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Touch panel with 30.7 cm/12.1" TFT-display (analog resistive (polyester)), 800 x 600 pixel(s) (SVGA), 262144 colors, XScale® PXA320, 806 MHz, 2x USB host 1.1, 1x COM (RS-232), 1 x Ethernet (10/100 Mbps), RJ45, Windows CE 5.0 and user software: Open platform. (bus system: PROFIBUS MASTER)

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 105314
GTIN	4055626105314

Technical data

Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

Dimensions

Outer dimensions: width, height, depth	340 mm x 270 mm x 5 mm (Dimensions of the front plate)
Installation dimensions: width, height, depth	315 mm x 244 mm x 66 mm (Mounting cutout, depth with bus if bus system present in the device)

Display

Display type	30.7 cm/12.1" TFT
Screen resolution	800 x 600 Pixel(s) (SVGA)
Touch technology	analog resistive (polyester)
Brightness	360 cd/m² typical (adjustable)
Backlighting	LED
Display backlight MTBF	50000 h
Colors	262144 colors
Reading angle left	80 °
Reading angle right	80 °
Reading angle top	60 °

Touch panel - TP121XIT-10/3051C240 S00018 - 2400892

Technical data

Display

Reading angle bottom	80 °
----------------------	------

Computer data

Processor	XScale® PXA320, 806 MHz
Operating system	Windows® CE 5.0
User software	Open platform
RAM	128 MB SDRAM
	1 MB SRAM
Mass storage	NAND-Flash, 1 GB
Network	1 x Ethernet (10/100 Mbps), RJ45
Interfaces	2x USB host 1.1
	1x COM (RS-232)
Bus system	PROFIBUS MASTER
Optional interfaces	CF slot
Realtime clock	Yes
Service life of battery	5 years (typical)

General

Material front plate	Aluminum (natural anodized)
Housing material	Steel sheet, zinc-plated
Mounting type	Front installation
Weight	2500 g

Ambient conditions

Degree of protection	IP65 (front), IP20 (back)
	NEMA 4X
Ambient temperature (operation)	0 °C ... 50 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Permissible humidity (operation)	20 % ... 85 % (non-condensing)
Vibration (operation)	1g, according to EN 60068-2-6
Shock	15g, according to IEC 60068-2-27

Device supply

Typical current consumption	0.7 A
Power supply unit	24 V DC ±20 %

Standards and Regulations

Shock	15g, according to IEC 60068-2-27
Vibration (operation)	1g, according to EN 60068-2-6

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 15;

Touch panel - TP121XIT-10/3051C240 S00018 - 2400892

Technical data

Environmental Product Compliance

	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"
--	---

Classifications

eCl@ss

eCl@ss 10.0.1	27330201
eCl@ss 4.0	27330200
eCl@ss 4.1	27330200
eCl@ss 5.0	27330200
eCl@ss 5.1	27330200
eCl@ss 6.0	27242300
eCl@ss 7.0	27242302
eCl@ss 8.0	27242302
eCl@ss 9.0	27330201

ETIM

ETIM 4.0	EC001412
ETIM 5.0	EC001412
ETIM 6.0	EC001412
ETIM 7.0	EC001412

UNSPSC

UNSPSC 13.2	43211904
UNSPSC 18.0	43211904
UNSPSC 19.0	43211904
UNSPSC 20.0	43211904
UNSPSC 21.0	43211904

Approvals

Approvals

Approvals

UL Listed / cUL Listed / cULus Listed

Ex Approvals

Approval details

Touch panel - TP121XIT-10/3051C240 S00018 - 2400892

Approvals

UL Listed



<http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm>

FILE E 205795

cUL Listed



<http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm>

FILE E 205795

cULus Listed



Accessories

Accessories

Battery module

Battery / accumulator - HMI BATTERY - 2701383

Lithium battery



Mounting material

Mounting material - HMI SCB MOUNTING KIT 8 - 2701387



HMI mounting kit for installation on a front plate. The mounting kit includes 8 x mounting brackets, 8 x screw threads, and a hexagonal wrench.

Mounting material - HMI WALL MOUNTING KIT - 2701380



HMI mounting kit for panel installation. The mounting kit includes 2 spring clips.

Operating stylus

Touch panel - TP121XIT-10/3051C240 S00018 - 2400892

Accessories

Touch pen - TOUCH PEN - 2701379



Touch pen for analog-resistive HMI, silver coated. Delivery includes self-adhesive pen holder.

PCB plug

Printed-circuit board connector - MSTB 2,5/ 3-STF BD:1-3 - 1896381



PCB connector, nominal current: 12 A, rated voltage (III/2): 320 V, nominal cross section: 2.5 mm², number of positions: 3, pitch: 5 mm, connection method: Screw connection with tension sleeve, color: green, contact surface: Tin

Protective foil

Protective foil - 12,1" DISPLAY PROTECTIVE FOIL - 2701377



Protective film set comprising 10 pieces of film for a 12.1" display. Including a squeegee to apply film and instructions.

Storage medium

USB memory stick - USB FLASH DRIVE - 2402809



USB memory stick, 8 GB

Memory card - VL 1 GB CF - 2913155



CompactFlash® card, pluggable, 1 GB

Touch panel - TP121XIT-10/3051C240 S00018 - 2400892

Accessories

Memory card - VL 4 GB CF - 2913157



CompactFlash® card, pluggable, 4 GB

Memory card - VL 8 GB CF - 2913158



CompactFlash® card, pluggable, 8 GB

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

2400892