

Touch panel - TP35AM/722000 S00001 - 2401037


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Touch panel with 8,9 cm / 3,5"-FSTN-display (analog resistive (polyester)), 320 x 240 pixel(s) (QVGA), 256-step grayscale, Arm9™, 200 MHz, 2x USB host 2.0, 1 x Ethernet (10/100 Mbps), RJ45, Windows CE 5.0 and user software: TSvisRT. (bus system: PROFIBUS DP)

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 096889
GTIN	4055626096889

Technical data

Dimensions

Outer dimensions: width, height, depth	120 mm x 90 mm x 5 mm (Dimensions of the front plate)
Installation dimensions: width, height, depth	112 mm x 82 mm x 47 mm (Mounting cutout, depth with bus if bus system present in the device)

Display

Display type	8,9 cm / 3,5"-FSTN
Screen resolution	320 x 240 Pixel(s) (QVGA)
Touch technology	analog resistive (polyester)
Brightness	350 cd/m², typical (adjustable)
Backlighting	LED
Display backlight MTBF	40000 h
Colors	256-step grayscale
Reading angle left	75 °
Reading angle right	75 °
Reading angle top	55 °
Reading angle bottom	75 °

Computer data

Processor	Arm9™, 200 MHz
-----------	----------------

Touch panel - TP35AM/722000 S00001 - 2401037

Technical data

Computer data

Operating system	Windows® CE 5.0
User software	TSvisRT
RAM	64 MB SDRAM
	512 KB SRAM
Mass storage	NOR-Flash, 32 MB
Network	1 x Ethernet (10/100 Mbps), RJ45
Interfaces	2x USB Host 2.0
Bus system	PROFIBUS DP
Optional interfaces	none
Realtime clock	Yes
Service life of battery	5 years (typical)

General

Material front plate	Aluminum (natural anodized)
Housing material	Steel sheet, zinc-plated
Mounting type	Front installation
Weight	1700 g

Ambient conditions

Degree of protection	IP65 (front), IP20 (back)
	NEMA 4X
Ambient temperature (operation)	0 °C ... 50 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Permissible humidity (operation)	20 % ... 85 %
Vibration (operation)	1g, according to EN 60068-2-6
Shock	15g, according to IEC 60068-2-27

Device supply

Typical current consumption	0.25 A
Power supply unit	24 V DC +/- 20 %

Standards and Regulations

Shock	15g, according to IEC 60068-2-27
Vibration (operation)	1g, according to EN 60068-2-6

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 15;
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Touch panel - TP35AM/722000 S00001 - 2401037

Classifications

eCl@ss

eCl@ss 10.0.1	27330201
eCl@ss 4.0	27330200
eCl@ss 4.1	27330200
eCl@ss 5.0	27330200
eCl@ss 5.1	27330200
eCl@ss 6.0	27242300
eCl@ss 7.0	27242302
eCl@ss 8.0	27242302
eCl@ss 9.0	27330201

ETIM

ETIM 4.0	EC001412
ETIM 5.0	EC001412
ETIM 6.0	EC001412
ETIM 7.0	EC001412

UNSPSC

UNSPSC 13.2	43211904
UNSPSC 18.0	43211904
UNSPSC 19.0	43211904
UNSPSC 20.0	43211904
UNSPSC 21.0	43211904

Accessories

Accessories

Battery module

Battery / accumulator - HMI BATTERY - 2701383

Lithium battery



Mounting material

Mounting material - HMI SCB MOUNTING KIT 4 - 2701384



HMI mounting kit for installation on a front plate. The mounting kit includes 4 x mounting brackets, 4 x screw threads, and a hexagonal wrench.

Touch panel - TP35AM/722000 S00001 - 2401037

Accessories

Mounting material - HMI WALL MOUNTING KIT - 2701380



HMI mounting kit for panel installation. The mounting kit includes 2 spring clips.

Operating stylus

Touch pen - TOUCH PEN - 2701379



Touch pen for analog-resistive HMIs, silver coated. Delivery includes self-adhesive pen holder.

PCB plug

Printed-circuit board connector - MC 1,5/ 3-STF-3,5 BD:1-3 - 1751312



PCB connector, nominal current: 8 A, rated voltage (III/2): 160 V, nominal cross section: 1.5 mm², number of positions: 3, pitch: 3.5 mm, connection method: Screw connection with tension sleeve, color: green, contact surface: Tin

Storage medium

USB memory stick - USB FLASH DRIVE - 2402809



USB memory stick, 8 GB

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2401037](#)