

Program / configuration memory - SD FLASH 2GB APPLIC A M-W - 2701976

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Program and configuration memory for extending the internal Flash memory, plug-in, 2 GB with license key for basic function block libraries for the marine and wind power industry.


Similar figure

Your advantages

- ✓ Program and configuration memory, plug-in, with license key for function block libraries.
- ✓ For storing application programs and other files in the file system of the PLC
- ✓ License key for the function block libraries

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 901321
GTIN	4046356901321

Technical data

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
---------------------------------	------------------

General

Supply voltage	3.3 V DC
Supply voltage range	2.7 V DC ... 3.6 V DC

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50 years
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Program / configuration memory - SD FLASH 2GB APPLIC A M-W - 2701976

Classifications

eCl@ss

eCl@ss 10.0.1	27242212
eCl@ss 4.0	27240400
eCl@ss 4.1	27240400
eCl@ss 5.0	27242200
eCl@ss 5.1	24210100
eCl@ss 6.0	27242200
eCl@ss 7.0	27242212
eCl@ss 8.0	27242212
eCl@ss 9.0	27242212

ETIM

ETIM 4.0	EC000192
ETIM 5.0	EC000192
ETIM 6.0	EC000192
ETIM 7.0	EC000192

UNSPSC

UNSPSC 13.2	43202005
UNSPSC 18.0	32101606
UNSPSC 19.0	32101606
UNSPSC 20.0	32101606
UNSPSC 21.0	32101606

Accessories

Accessories

Controller

Controller - ILC 131 ETH - 2700973



The Inline controller offers the option of communicating via PROFINET and Modbus/TCP. Programming is carried out using PC Worx Express or PC Worx (IEC 61131-3).

Controller - ILC 131 ETH/XC - 2701034



Inline controller for use under harsh ambient conditions, with Ethernet interface for coupling to other controllers and systems, with programming options according to IEC 61131-3, complete with connector and labeling field.

Program / configuration memory - SD FLASH 2GB APPLIC A M-W - 2701976

Accessories

Controller - ILC 151 ETH - 2700974



The Inline controller offers the option of communicating via PROFINET and Modbus/TCP. Programming is carried out using PC Worx Express or PC Worx (IEC 61131-3).

Controller - ILC 151 ETH/XC - 2701141



Inline controller for use under harsh ambient conditions, with Ethernet interface for coupling to other controllers and systems, with programming options according to IEC 61131-3, complete with connector and labeling field.

Controller - ILC 171 ETH 2TX - 2700975



The Inline controller offers the option of communicating via PROFINET and Modbus/TCP. Programming is carried out using PC Worx Express or PC Worx (IEC 61131-3).

Controller - ILC 191 ETH 2TX - 2700976



The Inline controller offers the option of communicating via PROFINET and Modbus/TCP. Programming is carried out using PC Worx Express or PC Worx (IEC 61131-3).

Controller - ILC 191 ME/AN - 2700074



Inline controller with integrated pulse/direction/PWM interface, RS-485/RS-422, analog inputs (0 ... 10 V), and analog outputs (0 ... 10 V), with programming options according to IEC 61131-3

Program / configuration memory - SD FLASH 2GB APPLIC A M- W - 2701976

Accessories

Controller - ILC 191 ME/INC - 2700075



Inline controller with integrated pulse/direction/PWM interface, RS-485/RS-422, fast counters, and incremental encoder inputs, with programming options according to IEC 61131-3

Controller - AXC 1050 - 2700988



Axio control for direct open-loop control of Axioline I/Os. With 2 Ethernet interfaces and programming capabilities according to IEC 61131-3. Complete with connector connector and labeling field.

Controller - AXC 1050 XC - 2701295



Axiocontrol for the direct control of Axioline I/Os. With 2 Ethernet interfaces, extended temperature range, and programming options according to IEC 61131-3. Complete with connector connector and marking field.

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2701976](#)