

Type 3 surge protection device - MNT-TEL B/F - 2882404

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Socket attachment plug with surge protection for the power supply and signal connection of an end device with analog or digital telecommunications interface (VDSL up to 50 Mbps, on short paths (< 300 m) up to 80 Mbps). Cable is included.



Your advantages

- ✓ Easy operation
- ✓ Thermal monitoring of the protective circuit
- ✓ Compact protection for termination devices
- ✓ Green LED - operating indicator for the power supply



VDSL

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 073479
GTIN	4046356073479

Technical data

Dimensions

Height	103 mm
Width	63 mm
Depth	78 mm

Ambient conditions

Ambient temperature (operation)	-25 °C ... 75 °C
Ambient temperature (storage/transport)	-25 °C ... 75 °C

General

Housing material	PA 6
Flammability rating according to UL 94	V-0
Color	jet black RAL 9005
For country-specific use in	B, F, CZ, SVK, PL

Type 3 surge protection device - MNT-TEL B/F - 2882404

Technical data

General

Mounting type	Plugging into the mains socket
Type	Attachment plug
Direction of action	L/N-PE & Signal Line-Earth Ground

Protective circuit, power supply

EN type	T3
Nominal voltage U_N	230 V AC
Arrester rated voltage U_C (L-N)	275 V AC
Arrester rated voltage U_C (L-PE)	360 V AC
Arrester rated voltage U_C (N-PE)	360 V AC
Nominal frequency f_N	50 Hz (60 Hz)
Rated load current I_L	16 A (30 °C)
Standby power consumption P_C	≤ 1 VA
Residual current I_{PE}	≤ 5 μ A
Nominal discharge current I_n (8/20) μ s	3 kA (> 5x)
Combination wave U_{OC}	4 kV
Energy absorption symmetrical	140 J (L-N)
Energy absorption, asymmetrical	220 J (L(N)-PE)
Voltage protection level U_p (L-N)	≤ 1.2 kV
Voltage protection level U_p (L-PE)	≤ 1.5 kV
Voltage protection level U_p (N-PE)	≤ 1.5 kV
Response time (L-N)	≤ 25 ns
Response time (L-PE)	≤ 100 ns
Response time (N-PE)	≤ 100 ns
Surge protection fault message	optical
Max. required back-up fuse	16 A (gG / B / C)

Connection (protective circuit, power supply)

Connection method	Grounding plug/socket
Connection method IN	Protective contact plug CEE7
Connection method OUT	Protective contact socket CEE7

Protective circuit, information technology

Arrester rated voltage U_C	200 V DC
Rated current	150 mA (25 °C)
Operating effective current I_C at U_C	≤ 150 μ A
Residual current I_{PE}	≤ 2 μ A
Insulation resistance R_{iso}	≥ 1 M Ω
	≥ 1 G Ω
Nominal discharge current I_n (8/20) μ s (line-line)	1 kA
Nominal discharge current I_n (8/20) μ s (line-earth)	2.5 kA

Type 3 surge protection device - MNT-TEL B/F - 2882404

Technical data

Protective circuit, information technology

Max. discharge current $I_{\max}$ (8/20) μ s	2.5 kA
Voltage protection level U_p (line-line)	≤ 460 V (C2 - 1 kA)
	≤ 350 V (C3 - 25 A)
Voltage protection level U_p (line-earth)	≤ 900 V (C2 - 2 kA)
	≤ 900 V (C3 - 100 A)
Response time t_A (line-line)	≤ 25 ns
Response time t_A (line-earth)	≤ 100 ns
Cut-off frequency f_g (3 dB), sym. in 100 Ohm system	typ. 4 MHz
Cut-off frequency f_g (3 dB), sym. in 150 Ohm system	typ. 3 MHz
Cut-off frequency f_g (3 dB), sym. in 600 Ohm system	typ. 700 kHz
Capacity (line-line)	typ. 1 nF
Capacity (line-earth)	typ. 5 pF
Output voltage limitation at 1 kV/ μ s (wire-wire)	≤ 360 V
Residual voltage at I_n (line-line)	≤ 500 V
Residual voltage at I_n (line-earth)	≤ 30 V
Residual voltage with I_{an} (10/1000) μ s (line-line)	≤ 35 V
Residual voltage with I_{an} (10/1000) μ s (line-earth)	≤ 35 V
Impulse durability (line-line)	C2 - 2 kV / 1 kA
	C3 - 25 A
Impulse durability (line-earth)	C2 - 4 kV / 2 kA
	C3 - 100 A
	D1 - 500 A
Alternating current carrying capacity (line-line)	250 mA - 1 s
Alternating current carrying capacity (line-earth)	10 A - 1 s
Pulse reset time (line-line)	≤ 15 ms

Power supply, general

Connection method	RJ12
Connection method IN	RJ12 female connector
Connection method OUT	RJ12 female connector

Connection, equipotential bonding, information technology

Connection method	Via protective contact plug
-------------------	-----------------------------

Standards (protective circuit, information technology)

IEC test classification	C1
	C2
	C3
	D1


Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------


Type 3 surge protection device - MNT-TEL B/F - 2882404

Drawings

Dimensional drawing



Circuit diagram



Type 3 surge protection device - MNT-TEL B/F - 2882404

Classifications

eCl@ss

eCl@ss 10.0.1	27130806
eCl@ss 4.0	27130800
eCl@ss 4.1	27130800
eCl@ss 5.0	27130800
eCl@ss 5.1	27130800
eCl@ss 6.0	27130800
eCl@ss 7.0	27130810
eCl@ss 8.0	27130810
eCl@ss 9.0	27130806

ETIM

ETIM 2.0	EC001473
ETIM 3.0	EC001473
ETIM 4.0	EC000942
ETIM 5.0	EC001473
ETIM 6.0	EC000942
ETIM 7.0	EC000942

UNSPSC

UNSPSC 6.01	30212010
UNSPSC 7.0901	39121610
UNSPSC 11	39121610
UNSPSC 12.01	39121610
UNSPSC 13.2	39121620
UNSPSC 18.0	39121620
UNSPSC 19.0	39121620
UNSPSC 20.0	39121620
UNSPSC 21.0	39121620

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

Type 3 surge protection device - MNT-TEL B/F - 2882404

Approvals

EAC



RU C-
DE.*09.B.00169

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2882404](#)