

Fuse plug - P-FU 5X20-5 - 3209235

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Fuse plug, connection method: Plug connection, nominal current: 6.3 A, nom. voltage: 400 V, width: 6.2 mm, fuse type: G / 5 x 20, mounting type: Plug-in mounting, color: black

Your advantages

- ✓ Large-surface labeling option
- ✓ Versions with bipolar error display
- ✓ Test contacts on both sides of the fuse
- ✓ Can be used for overload/short-circuit protection

RoHS

COMPLIANT

Key Commercial Data

Packing unit	10 pc
GTIN	 4 046356 548335
GTIN	4046356548335

Technical data

General

Note	Suitable for terminal blocks with a width of 5.2 mm and above with TG zone
	Prior to replacing the cartridge fuse, disconnect the fuse connector from the basic terminal block.
Color	black
Insulating material	PA
Flammability rating according to UL 94	V0
Maximum power dissipation for nominal condition	1.6 W

Dimensions

Width	6.2 mm
Length	25 mm
Pitch	5.2 mm

Fuse plug - P-FU 5X20-5 - 3209235

Technical data

General

Fuse	G / 5 x 20
Degree of pollution	3
Maximum load current	6.3 A (the current is determined by the fuse used)
Nominal current I_N	6.3 A (the current is determined by the fuse used)
Nominal voltage U_N	400 V (The voltage is determined by the fuse or selected LED display)
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	130 °C
Static insulating material application in cold	-60 °C
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed
Calorimetric heat release NFPA 130 (ASTM E 1354)	28 MJ/kg
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3

Connection data

Connection method	Plug connection
-------------------	-----------------

Standards and Regulations

Connection in acc. with standard	CSA
Flammability rating according to UL 94	V0


Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Drawings

Fuse plug - P-FU 5X20-5 - 3209235

Application drawing



Classifications

eCl@ss

eCl@ss 10.0.1	27142001
eCl@ss 4.0	27142000
eCl@ss 4.1	27142000
eCl@ss 5.0	27142000
eCl@ss 5.1	27142000
eCl@ss 6.0	27142000
eCl@ss 7.0	27142001
eCl@ss 8.0	27142001
eCl@ss 9.0	27142001

Fuse plug - P-FU 5X20-5 - 3209235

Classifications

ETIM

ETIM 4.0	EC002018
ETIM 5.0	EC000035
ETIM 6.0	EC000035
ETIM 7.0	EC000035

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121629
UNSPSC 18.0	39121629
UNSPSC 19.0	39121629
UNSPSC 20.0	39121629
UNSPSC 21.0	39121629

Approvals

Approvals

Approvals

CSA / UL Recognized / cUL Recognized / EAC / cULus Recognized

Ex Approvals

Approval details

CSA		http://www.csagroup.org/services-industries/product-listing/	13631
Nominal voltage UN		300 V	
Nominal current IN		10 A	

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 60425
Nominal voltage UN		300 V	
Nominal current IN		10 A	

Fuse plug - P-FU 5X20-5 - 3209235

Approvals

cUL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 60425
Nominal voltage UN		300 V	
Nominal current IN		10 A	

EAC		RU C- DE.BL08.B.00714
-----	---	--------------------------

cULus Recognized	
------------------	---

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

3209235