


## Cable duct - CD-HF 60X80 BU - 3240596

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable duct for installation and mounting in control cabinets, blue, halogen-free, comprising upper part and mounting base, width: 60 mm, height: 80 mm, length: 2000 mm

RoHS



### Key Commercial Data

|              |                                                                                                         |
|--------------|---------------------------------------------------------------------------------------------------------|
| Packing unit | 10 pc                                                                                                   |
| GTIN         | <br>4 046356 630146 |
| GTIN         | 4046356630146                                                                                           |

### Technical data

#### Dimensions

|            |         |
|------------|---------|
| Length (b) | 2000 mm |
| Width (a)  | 60 mm   |
| Height (c) | 80 mm   |

#### Ambient conditions

|                                 |                  |
|---------------------------------|------------------|
| Ambient temperature (operation) | -40 °C ... 90 °C |
|---------------------------------|------------------|

#### General

|                                        |                      |
|----------------------------------------|----------------------|
| Color                                  | blue                 |
| Components                             | halogen-free         |
| Flammability rating according to UL 94 | V0                   |
| Material                               | PC/ABS               |
| Nominal cross section                  | 3243 mm <sup>2</sup> |

#### Standards and Regulations

|                                        |     |
|----------------------------------------|-----|
| Halogen-free                           | yes |
| Connection in acc. with standard       | CSA |
| Flammability rating according to UL 94 | V0  |

#### Environmental Product Compliance

## Cable duct - CD-HF 60X80 BU - 3240596


### Technical data

#### Environmental Product Compliance

|            |                                                         |
|------------|---------------------------------------------------------|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
|            | No hazardous substances above threshold values          |

### Drawings

Dimensional drawing



Base perforation according to DIN EN 50085

### Classifications

eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 27400703 |
| eCl@ss 4.0    | 27140600 |
| eCl@ss 4.1    | 27140600 |
| eCl@ss 5.0    | 27140600 |
| eCl@ss 5.1    | 27140600 |
| eCl@ss 6.0    | 27400700 |
| eCl@ss 7.0    | 27400703 |
| eCl@ss 8.0    | 27400703 |
| eCl@ss 9.0    | 27400703 |

## Cable duct - CD-HF 60X80 BU - 3240596

### Classifications

#### ETIM

|          |          |
|----------|----------|
| ETIM 4.0 | EC000012 |
| ETIM 5.0 | EC000012 |
| ETIM 6.0 | EC000012 |
| ETIM 7.0 | EC000012 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30101815 |
| UNSPSC 7.0901 | 30101815 |
| UNSPSC 11     | 30101815 |
| UNSPSC 12.01  | 30101815 |
| UNSPSC 13.2   | 39131712 |
| UNSPSC 18.0   | 39131712 |
| UNSPSC 19.0   | 39131712 |
| UNSPSC 20.0   | 39131712 |
| UNSPSC 21.0   | 39131712 |

### Approvals

#### Approvals

#### Approvals

CSA / VDE Zeichengenehmigung

#### Ex Approvals

#### Approval details

|     |                                                                                     |                                                                                                                                         |        |
|-----|-------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------|--------|
| CSA |  | <a href="http://www.csagroup.org/services-industries/product-listing/">http://www.csagroup.org/services-industries/product-listing/</a> | 248269 |
|-----|-------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------|--------|

|                        |                                                                                     |                                                                                                                                                                                                           |          |
|------------------------|-------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------|
| VDE Zeichengenehmigung |  | <a href="http://www2.vde.com/de/Institut/Online-Service/VDE-gepruefteProdukte/Seiten/Online-Suche.aspx">http://www2.vde.com/de/Institut/Online-Service/VDE-gepruefteProdukte/Seiten/Online-Suche.aspx</a> | 40028972 |
|------------------------|-------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------|

### Accessories

#### Accessories

Filler plug

## Cable duct - CD-HF 60X80 BU - 3240596

### Accessories

Fastening clip - RVT-PA 4 - 3240498



Plastic body-bound rivet, for hole diameter of 4 mm and a material thickness of 1.5 ... 6 mm

---

Fastening clip - RVT-PA 6 - 3240499



Plastic body-bound rivet, for hole diameter of 6 mm and a material thickness of 1.5 ... 6 mm

---

### Riveting tools

Tool - UNIFOX-RVT P 4 - 1212478



Rivet setting tool, for use with RVT-PA 4 plastic body-bound rivets

---

Tool - UNIFOX-RVT P 6 - 1212509



Rivet setting tool, for use with RVT-PA 6 plastic body-bound rivets

---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

3240596