

## Insert label - PMP (90X38) - 0800006

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Insert label, Sheet, white, unlabeled, can be labeled with: BLUEMARK CLED, Mounting type: snapped into marker carrier, Lettering field: 90 x 38 mm




The figure shows the white version

### Product Features

- ✓ The PMP (90x38) system marking label is in a matrix
- ✓ The marker can be printed quickly and easily with the BLUEMARK CLED
- ✓ The marker is suitable for mounting in the CARRIER-PMP label holder
- ✓ Marking service: Phoenix Contact can custom-mark all labels according to your requirements
- ✓ The wide temperature range means that the labels can be used in control cabinets as well as the field
- ✓ The format automatically ensures printing with a high degree of positioning accuracy
- ✓ The sheets provide space for including function texts
- ✓ The format automatically ensures printing with a high degree of positioning accuracy

### Key commercial data

Packing unit	1
GTIN	 4 046356 910064
Custom tariff number	48211010

### Technical data

#### Dimensions

Length (b)	90 mm
Width (a)	38 mm

#### Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
Recommended storage conditions	10-25 °C / 35-65 % relative humidity. Storage in a cool and dry place is recommended.

#### General

Color	white
-------	-------

## Insert label - PMP (90X38) - 0800006

### Technical data

#### General

Components	Silicone-free
Material	PVC
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	1
Number of individual labels per row	1
Printability	Inkjet printing
Device	5147999 BLUEMARK CLED
Ink ribbon	5146662 BLUEMARK CLED-FLUID-CARTR.
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Wipe resistance test result	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	Following DIN 50018:2013-05
Climate level	AHT 1.0 S
Cycles	2
Condensation test result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result	Test passed
Foil strength	1.1 mm
Marking mounting type	snapped into marker carrier

### Classifications

#### eCl@ss

eCl@ss 4.1	24190219
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 8.0	27141137

#### ETIM

ETIM 4.0	EC000761
ETIM 5.0	EC000761

## Insert label - PMP (90X38) - 0800006

### Accessories

#### Accessories

#### Marker carriers

Marker carriers - CARRIER-PMP (108X38) - 0830958

Marker carriers, black, unlabeled, Mounting type: Screws, rivets, Lettering field: 90 x 38 mm



---

Phoenix Contact 2014 © - all rights reserved  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[0800006](#)