

Printed-circuit board connector - PTF 0,3/ 2-WB-8-H PC0140PL60 - 1715753

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Assembled PCB connectors

Figure shows the standard item

Your advantages

- ✓ Tool-free fast connection for flexible PCBs
- ✓ Small component size for applications where space is at a premium
- ✓ Reliable contacting of flexible PCBs, thanks to fixing pin
- ✓ Designed and tested according to IEC 60838-2-2



Key Commercial Data

Packing unit	20 pc
GTIN	
GTIN	4055626426099

Technical data

Item properties

Brief article description	Cable set
Plug-in system	COMBICON COMPACT PTF
Type of contact	Female connector
Range of articles	PTF 0,3/...-WB-H
Pitch	1.8 mm
Number of positions	2
Mounting type	Direct plug-in method
Number of levels	1
Number of connections	2
Number of potentials	2

Printed-circuit board connector - PTF 0,3/ 2-WB-8-H PC0140PL60 - 1715753

Technical data

Electrical parameters

Nom. voltage	< 25 V
Rated voltage	25 V

Dimensions for the product

Caption	Schematische Abbildung - weitere Details siehe Produktfamilienzeichnung im Download Center
Length [l]	60.00 mm
Pitch	1.90 mm

Header 1

Insulating material	PBT
CTI according to IEC 60112	275

Packaging information

Type of packaging	packed in cardboard
Pieces per package	20
Denomination packing units	Pcs.

Ambient conditions

Ambient temperature (storage/transport)	-40 °C ... 85 °C
Ambient temperature (operation)	-30 °C ... 100 °C (dependent on the derating curve)

Air clearances and creepage distances

Clearances and creepage distances	IEC 60838-1:2004-10 + AMD 1:2008-07 + AMD 2:2011-03
Specification	IEC 60838-1:2004-10 + AMD 1:2008-07 + AMD 2:2011-03

Temperature-rise test

Specification	IEC 60838-1:2004-10 + AMD 1:2008-07 + AMD 2:2011-03
Result	Test passed
Requirement temperature-rise test	Increase in temperature ≤ 45 K

Vibration test

Specification	IEC 60068-2-6:2007-12
Result	Test passed
Frequency	10 - 500 - 10 Hz
Sweep speed	1 octave/min
Amplitude	0.35 mm (10 - 60.1 Hz)
Acceleration	5 g (60.1 - 150 Hz)
Test duration per axis	2 h

Glow-wire test

Specification	IEC 60695-2-11:2000-10
Result	Test passed
Temperature	650 °C

Printed-circuit board connector - PTF 0,3/ 2-WB-8-H PC0140PL60 - 1715753

Technical data

Glow-wire test

Time of exposure	30 s
------------------	------

Needle flame test


Specification	IEC 60695-11-5:2004-12
Result	Test passed
Time of exposure	10 s

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Drawings

Diagram



Type: PTF 0,3/ 2-WB-8-H

Classifications

eCl@ss

eCl@ss 10.0.1	27440309
eCl@ss 8.0	27440309
eCl@ss 9.0	27440309

ETIM

ETIM 5.0	EC002638
----------	----------

Printed-circuit board connector - PTF 0,3/ 2-WB-8-H PC0140PL60 - 1715753

Classifications

ETIM

ETIM 6.0	EC002638
ETIM 7.0	EC002638

Approvals

Approvals

Approvals

UL Recognized / EAC

Ex Approvals

Approval details

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm E118976-20130430
Nominal voltage UN	60 V	
Nominal current IN	5 A	
mm²/AWG/kcmil	22	

EAC		B.01687
-----	---	---------

Accessories

Additional products

Printed-circuit board connector - PTF 0,3/ 4-BB-8-H - 1707559



PCB connector, rated voltage (III/2): 25 V, nominal cross section: 0.34 mm², product range: PTF 0,3/..-BB-H, pitch: 1.9 mm, mounting: Direct plug-in method, color: white, type of packaging: packed in cardboard. For flexible PCBs with a width of 8 mm and a permissible PCB thickness in the contact zone of 0.15 mm ... 0.3 mm

Printed-circuit board connector - PTF 0,3/ 2-WB-8-H PC0140PL60 - 1715753


Accessories

Printed-circuit board connector - PTF 0,3/ 4-WB-8-H - 1707561



Assembled PCB connectors

PCB - PTF 0,3/ 4-FLEX-I-8 - 1848477



PCB direct plug, color: white, product range: PTF 0,3/..-Flex, pitch: 1.8 mm, type of packaging: packed in cardboard

PCB - PTF 0,3/ 4-FLEX-L-8 - 1848480



PCB direct plug, nominal cross section: 0.34 mm², color: white, number of connections: 4, product range: PTF 0,3/..-Flex, pitch: 1.8 mm, mounting: Direct plug-in method, Stecksystem: COMBICON COMPACT PTF, type of packaging: packed in cardboard

PCB - PTF 0,3/ 4-FLEX-T-8 - 1848493



PCB direct plug, color: white, product range: PTF 0,3/..-Flex, pitch: 1.8 mm, type of packaging: packed in cardboard

Printed-circuit board connector - PTSM 0,5/ 2-P-2,5 - 1778832



PCB connector, nominal cross section: 0.5 mm², color: black, nominal current: 6 A, rated voltage (III/2): 160 V, contact surface: Tin, type of contact: Female connector, number of connections: 2, product range: PTSM 0,5/..-P, pitch: 2.5 mm, connection method: Push-in spring connection, conductor/PCB connection direction: 0 °, Stecksystem: COMBICON COMPACT PTSM, Locking: without, type of packaging: packed in cardboard

Printed-circuit board connector - PTF 0,3/ 2-WB-8-H PC0140PL60 - 1715753

Accessories

Printed-circuit board connector - PTSM 0,5/ 2-P-2,5 WH - 1704853



PCB connector, nominal cross section: 0.5 mm², color: white, nominal current: 6 A, rated voltage (III/2): 160 V, contact surface: Tin, type of contact: Female connector, number of connections: 2, product range: PTSM 0,5/...-P WH, pitch: 2.5 mm, connection method: Push-in spring connection, conductor/PCB connection direction: 0 °, Stecksystem: COMBICON COMPACT PTSM, Locking: without, type of packaging: packed in cardboard

Printed-circuit board connector - PTSM 0,5/ 2-PI-2,5 BK - 1709435



PCB connector, nominal cross section: 0.5 mm², color: black, nominal current: 6 A, rated voltage (III/2): 160 V, contact surface: Tin, type of contact: Male connector, number of connections: 2, product range: PTSM 0,5/...-PI, pitch: 2.5 mm, connection method: Push-in spring connection, conductor/PCB connection direction: 0 °, Stecksystem: COMBICON COMPACT PTSM, Locking: without, type of packaging: packed in cardboard

Printed-circuit board connector - PTSM 0,5/ 2-PI-2,5 WH - 1709450



PCB connector, nominal cross section: 0.5 mm², color: white, nominal current: 6 A, rated voltage (III/2): 160 V, contact surface: Tin, type of contact: Male connector, number of connections: 2, product range: PTSM 0,5/...-PI WH, pitch: 2.5 mm, connection method: Push-in spring connection, conductor/PCB connection direction: 0 °, Stecksystem: COMBICON COMPACT PTSM, Locking: without, type of packaging: packed in cardboard

Printed-circuit board connector - PTSM 0,5/ 2-PL-2,5 WH - 1709457



PCB connector, nominal cross section: 0.5 mm², color: white, nominal current: 6 A, rated voltage (III/2): 160 V, contact surface: Tin, type of contact: Female connector, number of connections: 2, product range: PTSM 0,5/...-PL WH, pitch: 2.5 mm, connection method: Push-in spring connection, conductor/PCB connection direction: 0 °, Stecksystem: COMBICON COMPACT PTSM, Locking: Snap-in locking, type of packaging: packed in cardboard

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1715753](#)