

## Test terminal strip - PTWE 6-2/E7 - 3069438

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Test terminal strip, VDE coded type E7, A detailed circuit diagram can be found under Miscellaneous Downloads, nom. voltage: 400 V AC/DC, connection method: Push-in connection, number of connections: 14, number of positions: 7, cross section: 0.5 mm<sup>2</sup> - 10 mm<sup>2</sup>, AWG: 20 - 8, width: 90.2 mm, height: 56.5 mm, color: gray, mounting type: Wall mounting

### Your advantages

- ✓ Space saving, thanks to compact, modular test terminal strips
- ✓ Cost-effective, thanks to the tailored, modular design and use of standardized CLIPLINE complete accessories
- ✓ The integrated, robust switch contact is designed for the most stringent demands, and the use of high-quality materials ensures the transmission of signal currents, even after multiple actuations
- ✓ Maximum safety with leading and automatic transformer short circuit



### Key Commercial Data

|              |                                                                                                         |
|--------------|---------------------------------------------------------------------------------------------------------|
| Packing unit | 1 pc                                                                                                    |
| GTIN         | <br>4 046356 943505 |
| GTIN         | 4046356943505                                                                                           |

### Technical data

#### General

|                                        |                                                                       |
|----------------------------------------|-----------------------------------------------------------------------|
| Note                                   | A detailed circuit diagram can be found under Miscellaneous Downloads |
| Number of positions                    | 7                                                                     |
| Number of levels                       | 1                                                                     |
| Number of connections                  | 14                                                                    |
| Potentials                             | 7                                                                     |
| Nominal cross section                  | 6 mm <sup>2</sup>                                                     |
| Color                                  | gray                                                                  |
| Insulating material                    | PA                                                                    |
| Flammability rating according to UL 94 | V0                                                                    |
| Rated surge voltage                    | 4 kV                                                                  |
| Test surge voltage                     | 5 kV                                                                  |
| Overvoltage category                   | III                                                                   |

# Test terminal strip - PTWE 6-2/E7 - 3069438

## Technical data

### General

|                                                                                           |                                                                        |
|-------------------------------------------------------------------------------------------|------------------------------------------------------------------------|
| Insulating material group                                                                 | I                                                                      |
| Maximum power dissipation for nominal condition                                           | 1.31 W                                                                 |
| Maximum load current                                                                      | 30 A (with 6 mm <sup>2</sup> conductor cross section)                  |
| Nominal voltage U <sub>N</sub>                                                            | 400 V AC/DC                                                            |
| Open side panel                                                                           | No                                                                     |
| Terminal block mounting                                                                   | 0.8 Nm ... 1 Nm                                                        |
| Ambient temperature (operation)                                                           | -60 °C ... 85 °C                                                       |
| Ambient temperature (storage/transport)                                                   | -25 °C ... 55 °C (For a short time, not exceeding 24 h, -60 to +70 °C) |
| Permissible humidity (storage/transport)                                                  | 30 % ... 70 %                                                          |
| Ambient temperature (assembly)                                                            | -5 °C ... 70 °C                                                        |
| Ambient temperature (actuation)                                                           | -5 °C ... 70 °C                                                        |
| Shock protection test specification                                                       | DIN EN 50274 (VDE 0660-514):2002-11                                    |
| Back of the hand protection                                                               | guaranteed                                                             |
| Finger protection                                                                         | guaranteed                                                             |
| Note regarding shock protection                                                           | When test disconnect plug is plugged in.                               |
| Result of surge voltage test                                                              | Test passed                                                            |
| Result of power-frequency withstand voltage test                                          | Test passed                                                            |
| Power frequency withstand voltage setpoint                                                | 1.89 kV                                                                |
| Result of the test for mechanical stability of terminal points (5 x conductor connection) | Test passed                                                            |
| Result of bending test                                                                    | Test passed                                                            |
| Bending test rotation speed                                                               | 10 rpm                                                                 |
| Bending test turns                                                                        | 135                                                                    |
| Bending test conductor cross section/weight                                               | 0.5 mm <sup>2</sup> / 0.3 kg                                           |
|                                                                                           | 6 mm <sup>2</sup> / 1.4 kg                                             |
|                                                                                           | 10 mm <sup>2</sup> / 2 kg                                              |
| Tensile test result                                                                       | Test passed                                                            |
| Result of tight fit on support                                                            | Test passed                                                            |
| Setpoint                                                                                  | 5 N                                                                    |
| Result of voltage-drop test                                                               | Test passed                                                            |
| Result of temperature-rise test                                                           | Test passed                                                            |
| Requirement temperature-rise test                                                         | Increase in temperature ≤ 45 K                                         |
| Short circuit stability result                                                            | Test passed                                                            |
| Conductor cross section short circuit testing                                             | 4 mm <sup>2</sup>                                                      |
| Short-time current                                                                        | 0.5 kA                                                                 |
| Conductor cross section short circuit testing                                             | 4 mm <sup>2</sup>                                                      |
| Short-time current                                                                        | 0.3 kA                                                                 |
| Conductor cross section short circuit testing                                             | 4 mm <sup>2</sup>                                                      |
| Short-time current                                                                        | 0.15 kA                                                                |
| Result of thermal test                                                                    | Test passed                                                            |
| Ageing test for screwless modular terminal block temperature cycles                       | 192                                                                    |

# Test terminal strip - PTWE 6-2/E7 - 3069438

## Technical data

### General

|                                                                         |                                                |
|-------------------------------------------------------------------------|------------------------------------------------|
| Proof of thermal characteristics (needle flame) effective duration      | 30 s                                           |
| Result of aging test                                                    | Test passed                                    |
| Oscillation, broadband noise test result                                | Test passed                                    |
| Test specification, oscillation, broadband noise                        | DIN EN 50155 (VDE 0115-200):2008-03            |
| Test spectrum                                                           | Service life test category 2, bogie-mounted    |
| Test frequency                                                          | $f_1 = 5 \text{ Hz}$ to $f_2 = 250 \text{ Hz}$ |
| ASD level                                                               | $6.12 \text{ (m/s}^2\text{)}^2/\text{Hz}$      |
| Acceleration                                                            | 3.12 g                                         |
| Test duration per axis                                                  | 5 h                                            |
| Test directions                                                         | X-, Y- and Z-axis                              |
| Shock test result                                                       | Test passed                                    |
| Test specification, shock test                                          | DIN EN 50155 (VDE 0115-200):2008-03            |
| Shock form                                                              | Half-sine                                      |
| Acceleration                                                            | 30g                                            |
| Shock duration                                                          | 18 ms                                          |
| Number of shocks per direction                                          | 3                                              |
| Test directions                                                         | X-, Y- and Z-axis (pos. and neg.)              |
| Relative insulation material temperature index (Elec., UL 746 B)        | 130 °C                                         |
| Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21)) | 125 °C                                         |
| Static insulating material application in cold                          | -60 °C                                         |
| Surface flammability NFPA 130 (ASTM E 162)                              | passed                                         |
| Specific optical density of smoke NFPA 130 (ASTM E 662)                 | passed                                         |
| Calorimetric heat release NFPA 130 (ASTM E 1354)                        | 27,5 MJ/kg                                     |
| Smoke gas toxicity NFPA 130 (SMP 800C)                                  | passed                                         |
| Fire protection for rail vehicles (DIN EN 45545-2) R22                  | HL 1 - HL 3                                    |
| Fire protection for rail vehicles (DIN EN 45545-2) R23                  | HL 1 - HL 3                                    |
| Fire protection for rail vehicles (DIN EN 45545-2) R24                  | HL 1 - HL 3                                    |
| Fire protection for rail vehicles (DIN EN 45545-2) R26                  | HL 1 - HL 3                                    |

### Dimensions

|                 |               |
|-----------------|---------------|
| Width           | 90.2 mm       |
| Length          | 100 mm        |
| Height          | 56.5 mm       |
| Plate thickness | 1 mm ... 4 mm |
| Pitch           | 8.2 mm        |

### Connection data

|                                  |                    |
|----------------------------------|--------------------|
| Connection                       | 1 level            |
| Connection method                | Push-in connection |
| Stripping length                 | 12 mm              |
| Connection in acc. with standard | IEC 60947-7-1      |

# Test terminal strip - PTWE 6-2/E7 - 3069438

## Technical data

### Connection data

|                                                                                                        |                                      |
|--------------------------------------------------------------------------------------------------------|--------------------------------------|
| Conductor cross section solid min.                                                                     | 0.5 mm <sup>2</sup>                  |
| Conductor cross section solid max.                                                                     | 10 mm <sup>2</sup>                   |
| Conductor cross section AWG min.                                                                       | 20                                   |
| Conductor cross section AWG max.                                                                       | 8                                    |
| Conductor cross section flexible min.                                                                  | 0.5 mm <sup>2</sup>                  |
| Conductor cross section flexible max.                                                                  | 6 mm <sup>2</sup>                    |
| Min. AWG conductor cross section, flexible                                                             | 20                                   |
| Max. AWG conductor cross section, flexible                                                             | 10                                   |
| Conductor cross section flexible, with ferrule without plastic sleeve min.                             | 0.5 mm <sup>2</sup>                  |
| Conductor cross section flexible, with ferrule without plastic sleeve max.                             | 6 mm <sup>2</sup>                    |
| Conductor cross section flexible, with ferrule with plastic sleeve min.                                | 0.5 mm <sup>2</sup>                  |
| Conductor cross section flexible, with ferrule with plastic sleeve max.                                | 6 mm <sup>2</sup>                    |
| Two conductors with the same cross section, flexible, with TWIN ferrules, with plastic sleeve, minimum | 0.5 mm <sup>2</sup>                  |
| Two conductors with the same cross section, flexible, with TWIN ferrules, with plastic sleeve, maximum | 1.5 mm <sup>2</sup>                  |
| Connection cross sections directly pluggable                                                           | 1 mm <sup>2</sup> 10 mm <sup>2</sup> |
| Conductor cross section solid min.                                                                     | 1 mm <sup>2</sup>                    |
| Conductor cross section solid max.                                                                     | 10 mm <sup>2</sup>                   |
| Conductor cross section flexible, with ferrule without plastic sleeve min.                             | 1 mm <sup>2</sup>                    |
| Conductor cross section flexible, with ferrule without plastic sleeve max.                             | 6 mm <sup>2</sup>                    |
| Conductor cross section flexible, with ferrule with plastic sleeve min.                                | 1 mm <sup>2</sup>                    |
| Conductor cross section flexible, with ferrule with plastic sleeve max.                                | 6 mm <sup>2</sup>                    |
| Internal cylindrical gage                                                                              | A5                                   |

### Mounting

|                                               |               |
|-----------------------------------------------|---------------|
| Mounting type                                 | Wall mounting |
| Plate thickness                               | 1 mm ... 4 mm |
| Min. tightening torque of the mounting screw: | 0.8 Nm        |
| Max. tightening torque of the mounting screw: | 1 Nm          |

### Standards and Regulations


|                                        |               |
|----------------------------------------|---------------|
| Connection in acc. with standard       | IEC 60947-7-1 |
| Flammability rating according to UL 94 | V0            |

### Environmental Product Compliance

|            |                                                         |
|------------|---------------------------------------------------------|
| REACH SVHC | Lead 7439-92-1                                          |
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
|            | No hazardous substances above threshold values          |


## Drawings

## Test terminal strip - PTWE 6-2/E7 - 3069438



## Test terminal strip - PTWE 6-2/E7 - 3069438

Dimensional drawing



Circuit diagram



### Classifications

eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 27141126 |
| eCl@ss 5.0    | 27141100 |
| eCl@ss 5.1    | 27141100 |
| eCl@ss 6.0    | 27141100 |
| eCl@ss 7.0    | 27141126 |
| eCl@ss 8.0    | 27141126 |
| eCl@ss 9.0    | 27141126 |

ETIM

|          |          |
|----------|----------|
| ETIM 4.0 | EC000897 |
| ETIM 5.0 | EC000902 |

## Test terminal strip - PTWE 6-2/E7 - 3069438

### Classifications

#### ETIM

|          |          |
|----------|----------|
| ETIM 6.0 | EC000902 |
| ETIM 7.0 | EC000902 |

#### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 13.2 | 39121410 |
| UNSPSC 18.0 | 39121410 |
| UNSPSC 19.0 | 39121410 |
| UNSPSC 20.0 | 39121410 |
| UNSPSC 21.0 | 39121410 |

### Approvals

#### Approvals

#### Approvals

CSA / UL Recognized / cUL Recognized / EAC / EAC / cULus Recognized

#### Ex Approvals

#### Approval details

|                    |                                                                                     |                                                                                                                                         |       |
|--------------------|-------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------|-------|
| CSA                |  | <a href="http://www.csagroup.org/services-industries/product-listing/">http://www.csagroup.org/services-industries/product-listing/</a> | 13631 |
|                    | B                                                                                   | C                                                                                                                                       |       |
| Nominal voltage UN | 600 V                                                                               | 600 V                                                                                                                                   |       |
| Nominal current IN | 20 A                                                                                | 20 A                                                                                                                                    |       |
| mm²/AWG/kcmil      | 20-8                                                                                | 20-8                                                                                                                                    |       |

|                    |                                                                                     |                                                                                                                                                       |              |
|--------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|--------------|
| UL Recognized      |  | <a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a> | FILE E 60425 |
|                    | D                                                                                   |                                                                                                                                                       |              |
| Nominal voltage UN | 300 V                                                                               |                                                                                                                                                       |              |
| Nominal current IN | 10 A                                                                                |                                                                                                                                                       |              |
| mm²/AWG/kcmil      | 20-8                                                                                |                                                                                                                                                       |              |

## Test terminal strip - PTWE 6-2/E7 - 3069438

### Approvals

|                    |                                                                                   |                                                                                                                                                       |              |
|--------------------|-----------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|--------------|
| cUL Recognized     |  | <a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a> | FILE E 60425 |
|                    |                                                                                   | D                                                                                                                                                     |              |
| Nominal voltage UN |                                                                                   | 300 V                                                                                                                                                 |              |
| Nominal current IN |                                                                                   | 10 A                                                                                                                                                  |              |
| mm²/AWG/kcmil      |                                                                                   | 20-8                                                                                                                                                  |              |

|     |                                                                                   |                          |
|-----|-----------------------------------------------------------------------------------|--------------------------|
| EAC |  | RU C-<br>DE.AI30.B.01102 |
|-----|-----------------------------------------------------------------------------------|--------------------------|

|     |                                                                                   |                          |
|-----|-----------------------------------------------------------------------------------|--------------------------|
| EAC |  | RU C-<br>DE.BL08.B.00682 |
|-----|-----------------------------------------------------------------------------------|--------------------------|

|                  |                                                                                     |  |
|------------------|-------------------------------------------------------------------------------------|--|
| cULus Recognized |  |  |
|------------------|-------------------------------------------------------------------------------------|--|

### Accessories

#### Accessories

##### Blind plug

Dummy plug - FBP-2/E7 - 3069499



Dummy plug, VDE coded type E7, pitch: 8.2 mm, length: 81 mm, width: 71 mm, number of positions: 7, color: gray

### Cover profile

Cover profile - AP RSC-T - 3059139



Cover profile, for covering terminal strips, directly snapped onto RBO... and RSC... test disconnect terminal blocks.  
Length supplied: 1 m

### Cover profile carrier



## Test terminal strip - PTWE 6-2/E7 - 3069438

### Accessories

Cover profile carrier - APH-UTWE 6-2 - 3069057



Cover profile carrier, width: 8 mm, height: 56.6 mm, material: PA, length: 80.9 mm, color: gray

---

### Documentation

Mounting material - PT-IL - 3208090



Operating decal for the push-in Technology

---

### Labeled terminal marker

Zack marker strip - ZB 8 CUS - 0825011



Zack marker strip, can be ordered: Strip, white, labeled according to customer specifications, mounting type: snap into tall marker groove, for terminal block width: 8.2 mm, lettering field size: 10.5 x 8.15 mm, Number of individual labels: 10

---

Marker for terminal blocks - UC-TM 8 CUS - 0824597



Marker for terminal blocks, can be ordered: by sheet, white, labeled according to customer specifications, mounting type: snap into tall marker groove, for terminal block width: 8.2 mm, lettering field size: 7.6 x 10.5 mm, Number of individual labels: 56

---

Marker for terminal blocks - UCT-TM 8 CUS - 0829616



Marker for terminal blocks, can be ordered: by sheet, white, labeled according to customer specifications, mounting type: snap into tall marker groove, for terminal block width: 8.2 mm, lettering field size: 7.6 x 10.5 mm, Number of individual labels: 42

## Test terminal strip - PTWE 6-2/E7 - 3069438

### Accessories

#### Zack marker strip - ZB 8,LGS:FORTL.ZAHLEN - 1052015



Zack marker strip, Strip, white, labeled, can be labeled with: CMS-P1-PLOTTER, printed horizontally: consecutive numbers 1 ... 10, 11 ... 20, etc. up to 91 ... 100, mounting type: snap into tall marker groove, for terminal block width: 8.2 mm, lettering field size: 10.5 x 8.15 mm, Number of individual labels: 10

#### Zack marker strip - ZB 8,QR:FORTL.ZAHLEN - 1052028



Zack marker strip, Strip, white, labeled, can be labeled with: CMS-P1-PLOTTER, Printed vertically: consecutive numbers 1 ... 10, 11 ... 20, etc. up to 91 ... 100, mounting type: snap into tall marker groove, for terminal block width: 8.2 mm, lettering field size: 10.5 x 8.15 mm, Number of individual labels: 10

#### Marker for terminal blocks - ZB 8,LGS:L1-N,PE - 1052413



Marker for terminal blocks, Strip, white, labeled, can be labeled with: CMS-P1-PLOTTER, horizontal: L1, L2, L3, N, PE, L1, L2, L3, N, PE, mounting type: snap into tall marker groove, for terminal block width: 8.2 mm, lettering field size: 10.5 x 8.15 mm, Number of individual labels: 10

### Screwdriver tools

#### Screwdriver - SZF 2-0,8X4,0 - 1204520



Actuation tool, for ST terminal blocks, also suitable for use as a bladed screwdriver, size: 0.8 x 4.0 x 100 mm, 2-component grip, with non-slip grip

### Terminal marking

#### Zack marker strip - ZB 8:UNBEDRUCKT - 1052002



Zack marker strip, Strip, white, unlabeled, can be labeled with: CMS-P1-PLOTTER, PLOTMARK, mounting type: snap into tall marker groove, for terminal block width: 8.2 mm, lettering field size: 10.5 x 8.15 mm, Number of individual labels: 10

## Test terminal strip - PTWE 6-2/E7 - 3069438

### Accessories

#### Marker for terminal blocks - UC-TM 8 - 0818072



Marker for terminal blocks, Sheet, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: snap into tall marker groove, for terminal block width: 8.2 mm, lettering field size: 7.6 x 10.5 mm, Number of individual labels: 56

#### Marker for terminal blocks - UCT-TM 8 - 0828740



Marker for terminal blocks, Sheet, white, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snap into tall marker groove, for terminal block width: 8.2 mm, lettering field size: 7.6 x 10.5 mm, Number of individual labels: 42

#### Marker for terminal blocks - TMT (EX9,5)R - 0828295



Marker for terminal blocks, Roll, white, unlabeled, can be labeled with: THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, mounting type: snap into universal marker groove, snap into tall marker groove, for terminal block width: 50000 mm, lettering field size: 9.5 x 50000 mm, Number of individual labels: 1

#### Marker for terminal blocks - US-TM 100 - 0829255



Marker for terminal blocks, Card, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snap into universal marker groove, lettering field size: 104 x 9.8 mm, Number of individual labels: 13

### Test plug terminal block

#### Test plug - FTPR-2/E7 - 3069486



Test plug, with twist grip, VDE coded type E7, A detailed circuit diagram can be found under Miscellaneous Downloads, nom. voltage: 400 V AC/DC, nominal current: 24 A, number of positions: 7, width: 71 mm, color: gray

## Test terminal strip - PTWE 6-2/E7 - 3069438

### Accessories

Test plug - FTP-2/E7 - 3069472



Test plug, VDE coded type E7, number of positions: 7, width: 71 mm, color: gray

---

Test plug - FTP-2/1 SERVICE - 3069469



Test plug, number of positions: 1, width: 9 mm, color: red

---

Test socket

Test adapter - PAI-4-N GY - 3032871



4 mm test adapter, for terminal blocks with 5.2 mm, 6.2 mm and 8.2 mm pitch

---

Test adapter - PAI-4-FIX BU - 3032729



Test adapter, for 4 mm test plug and terminal blocks with 8.2 mm pitch, color: blue

---

Test adapter - PAI-4-FIX OG - 3034455



4 mm test adapter, for terminal blocks with 8.2 mm pitch

---

## Test terminal strip - PTWE 6-2/E7 - 3069438

### Accessories

Test adapter - PAI-4-FIX YE - 3032745



Test adapter, for 4 mm test plug and terminal blocks with 8.2 mm pitch, color: yellow

---

Test adapter - PAI-4-FIX RD - 3032732



Test adapter, for 4 mm test plug and terminal blocks with 8.2 mm pitch, color: red

---

Test adapter - PAI-4-FIX GN - 3032758



Test adapter, for 4 mm test plug and terminal blocks with 8.2 mm pitch, color: green

---

Test adapter - PAI-4-FIX BK - 3032774



Test adapter, for 4 mm test plug and terminal blocks with 8.2 mm pitch, color: black

---

Test adapter - PAI-4-FIX GY - 3032790



Test adapter, for 4 mm test plug and terminal blocks with 8.2 mm pitch, color: gray

---

## Test terminal strip - PTWE 6-2/E7 - 3069438

### Accessories

Test adapter - PAI-4-FIX VT - 3032761



Test adapter, for 4 mm test plug and terminal blocks with 4.2 mm ... 8.2 mm pitch, color: violet

---

Test adapter - PAI-4-FIX BN - 3032787



Test adapter, for 4 mm test plug and terminal blocks with 8.2 mm pitch, color: brown

---

Test adapter - PAI-4-FIX WH - 3032797



4 mm test adapter, for terminal blocks with 8.2 mm pitch

---

Test adapter - PAIS-4-FIX GY - 3032791



Test adapter, for 4 mm test plug and terminal blocks with 5.2 mm, 6.2 mm, and 8.2 mm pitch, color: gray

---

Test adapter - PAIS-4-FIX BK - 3032792



Test adapter, for 4 mm test plug and terminal blocks with 5.2 mm, 6.2 mm, and 8.2 mm pitch, color: black

---

## Test terminal strip - PTWE 6-2/E7 - 3069438

### Accessories

Test adapter - PAIS-4-FIX RD - 3032793



Test adapter, for 4 mm test plug and terminal blocks with 5.2 mm, 6.2 mm, and 8.2 mm pitch, color: red

---

Test adapter - PAIS-4-FIX BU - 3032798



Test adapter, for 4 mm test plug and terminal blocks with 5.2 mm, 6.2 mm, and 8.2 mm pitch, color: blue

---

Test adapter - PAIS-4-FIX YE - 3032799



Test adapter, for 4 mm test plug and terminal blocks with 5.2 mm, 6.2 mm, and 8.2 mm pitch, color: yellow

---

Test adapter - PAIS-4-FIX GN - 3032801



Test adapter, for 4 mm test plug and terminal blocks with 5.2 mm, 6.2 mm, and 8.2 mm pitch, color: green

---

Test adapter - PAIS-4-FIX VT - 3032802



Test adapter, for 4 mm test plug and terminal blocks with 5.2 mm, 6.2 mm, and 8.2 mm pitch, color: violet

---

---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

3069438