

## Network cable - NBC-MSD/3,0-937/MSD RX-TX - 1412280

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Network cable, PROFINET CAT5, PROFINET CAT5e, 4-pos., RADOX® GKW S, RAL 9005 (black), shielded, straight M12-SPEEDCON plug/IP65, coding: D to straight M12-SPEEDCON plug/IP65, coding D, cable length: 3 m, product checked according to customer specification/railway application



### Key Commercial Data

|                        |                                                                                                         |
|------------------------|---------------------------------------------------------------------------------------------------------|
| Packing unit           | 1 pc                                                                                                    |
| Minimum order quantity | 50 pc                                                                                                   |
| GTIN                   | <br>4 046356 953139 |
| GTIN                   | 4046356953139                                                                                           |

### Technical data

#### Dimensions

|                 |     |
|-----------------|-----|
| Length of cable | 3 m |
|-----------------|-----|

#### General data

|                       |                                |
|-----------------------|--------------------------------|
| Rated current at 40°C | 4 A                            |
| Rated voltage         | 48 V AC                        |
|                       | 60 V DC                        |
| Number of positions   | 4                              |
| Signal type/category  | PROFINET CAT5 (IEC 11801:2002) |
| Standards/regulations | M12 connector IEC 61076-2-101  |
| Overvoltage category  | II                             |
| Degree of pollution   | 3                              |

#### Characteristics head 2

|                                          |                                   |
|------------------------------------------|-----------------------------------|
| Head type                                | Plug straight M12 SPEEDCON / IP65 |
| No. of positions (pin connector pattern) | 4                                 |
| Coding                                   | D (Data)                          |
| Color                                    | black                             |
| Material (component)                     | CuSn (Contact)                    |

# Network cable - NBC-MSD/3,0-937/MSD RX-TX - 1412280

## Technical data

### Characteristics head 2

|                                 |                                                                  |
|---------------------------------|------------------------------------------------------------------|
|                                 | Ni/Au (Contact surface)                                          |
|                                 | PA (Contact carriers)                                            |
|                                 | TPU, hardly inflammable, self-extinguishing (Grip)               |
|                                 | Zinc die-cast, nickel-plated (Screw connection)                  |
| Shielded                        | yes                                                              |
| Insulation resistance           | $\geq 100 \text{ M}\Omega$                                       |
| Insertion/withdrawal cycles     | $\geq 100$ (Quantity: 500 with Phoenix Contact mating connector) |
| Torque                          | 0.4 Nm                                                           |
| Ambient temperature (operation) | -40 °C ... 90 °C                                                 |
| Weight                          | 10 g $\pm$ 5 g                                                   |

### Standards and Regulations

|                                        |                 |
|----------------------------------------|-----------------|
| Standard designation                   | M12 connector   |
| Standards/regulations                  | IEC 61076-2-101 |
| Flammability rating according to UL 94 | V0              |

### Cable

|                                            |                                                            |
|--------------------------------------------|------------------------------------------------------------|
| Cable type                                 | PROFINET railway applications                              |
| Cable type (abbreviation)                  | 937                                                        |
| Signal type/category                       | PROFINET CAT5 (IEC 11801), 100 Mbps                        |
|                                            | EtherCAT <sup>®</sup> CAT5 (IEC 11801), 100 Mbps           |
| Cable structure                            | 1x4xAWG22/7; SF/TQ                                         |
| Conductor cross section                    | 4x 0.34 mm <sup>2</sup>                                    |
| AWG signal line                            | 22                                                         |
| Conductor structure signal line            | 7x 0.25 mm                                                 |
| Core diameter including insulation         | approx. 1.5 mm                                             |
| Wire colors                                | white-blue, orange-yellow                                  |
| Overall twist                              | Star quad                                                  |
| Shielding                                  | Plastic-coated aluminum foil, tinned copper braided shield |
| External sheath, color                     | black RAL 9005                                             |
| Outer sheath thickness                     | approx. 1 mm                                               |
| External cable diameter D                  | 6.6 mm $\pm$ 0.4 mm                                        |
| Minimum bending radius, fixed installation | 6 x D                                                      |
| Cable weight                               | 70 kg/km                                                   |
| Outer sheath, material                     | PE-X                                                       |
| Material conductor insulation              | Foamed PE                                                  |
| Conductor material                         | silver-plated Cu litz wires                                |
| Conductor resistance                       | $\leq 54.4 \text{ }\Omega/\text{km}$                       |
| Working capacitance                        | $\leq 65 \text{ pF}$ (core-core)                           |
|                                            | $\leq 100 \text{ pF}$ (core-shield)                        |
| Wave impedance                             | 100 $\Omega$ $\pm$ 5 $\Omega$ (f = 100 MHz)                |
| Near end crosstalk attenuation (NEXT)      | 73 dB (with 1 MHz)                                         |

# Network cable - NBC-MSD/3,0-937/MSD RX-TX - 1412280

## Technical data

### Cable

|                                     |                                             |
|-------------------------------------|---------------------------------------------|
|                                     | 70 dB (at 4 MHz)                            |
|                                     | 65 dB (at 10 MHz)                           |
|                                     | 57 dB (at 31.5 MHz)                         |
|                                     | 52 dB (at 62.5 MHz)                         |
|                                     | 48 dB (at 100 MHz)                          |
| Remote crosstalk attenuation (FEXT) | 78 dB (with 1 MHz)                          |
|                                     | 77 dB (at 4 MHz)                            |
|                                     | 70 dB (at 10 MHz)                           |
|                                     | 65 dB (at 31.5 MHz)                         |
|                                     | 56 dB (at 62.5 MHz)                         |
|                                     | 48 dB (at 100 MHz)                          |
| Attenuation                         | 2 dB (with 1 MHz)                           |
|                                     | 4.4 dB (at 4 MHz)                           |
|                                     | 7.4 dB (at 10 MHz)                          |
|                                     | 14 dB (at 31.5 MHz)                         |
|                                     | 20 dB (at 62.5 MHz)                         |
|                                     | 26 dB (at 100 MHz)                          |
| Return loss (RL)                    | 25 dB (at 4 MHz)                            |
|                                     | 30 dB (at 10 MHz)                           |
|                                     | 30 dB (at 31.5 MHz)                         |
|                                     | 30 dB (at 62.5 MHz)                         |
|                                     | 28 dB (at 100 MHz)                          |
| Signal speed                        | 75 c                                        |
| Shield attenuation                  | 40 dB (30 MHz ≤ f ≤ 100 MHz)                |
| Coupling resistance                 | 200.00 mΩ/m (f ≤ 30 MHz)                    |
| Nominal voltage, cable              | 300 V AC                                    |
| Test voltage, cable                 | 2000 V AC (50 Hz, 5 minutes)                |
| Fire protection in rail vehicles    | BS 6853 (Category Ia, Ib, II)               |
|                                     | GM/RT 2130 (Category Ia, Ib, II)            |
|                                     | EN 45545 (Risk level HL1 - HL3)             |
|                                     | DIN 5510 (Fire protection level 1, 2, 3, 4) |
|                                     | NF F16-101 (Category A1, A2, B)             |
|                                     | NF F16-101 (Class C/F0)                     |
|                                     | NFPA 130                                    |
|                                     | UNI CEI 11170 (Risk level LR1 - LR4)        |
| Flame resistance                    | EN 60332-1-2                                |
|                                     | EN 50266                                    |
|                                     | EN 60332-3-25                               |
|                                     | NF C32-070, 2.1                             |
|                                     | NF C32-070, 2.2                             |

## Network cable - NBC-MSD/3,0-937/MSD RX-TX - 1412280

### Technical data

#### Cable


|                                    |                                                          |
|------------------------------------|----------------------------------------------------------|
|                                    | UL 1685, 12 (FT4)                                        |
|                                    | in accordance with ISO 6722-1 5.22 (UN ECE-R 118.01)     |
| Halogen-free                       | According to EN 50267-2-1                                |
| Resistance to oil                  | according to IRM 902, 72 h at 100 °C                     |
| Other resistance                   | Resistance to fuels according to IRM 903, 168 h at 70 °C |
| Concentration of fumes             | BS 6853 D.8.7                                            |
|                                    | EN 61034-2                                               |
|                                    | UL 1685, 12 (FT4)                                        |
| Fume corrosiveness                 | EN 50267-2-2                                             |
| Fume toxicity                      | BS 6853 B.1                                              |
|                                    | EN 50305, 9.2                                            |
| Ambient temperature (operation)    | -50 °C ... 90 °C (cable, fixed installation)             |
|                                    | -40 °C ... 90 °C (cable, flexible installation)          |
| Ambient temperature (installation) | -25 °C ... 90 °C                                         |

#### Environmental Product Compliance

|            |                                                         |
|------------|---------------------------------------------------------|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
|            | No hazardous substances above threshold values          |

### Drawings

Schematic diagram




Pin assignment M12 male connector, 4-pos., D-coded, male side

Cable cross section



PROFINET railway applications [937]

Dimensional drawing



M12 SPEEDCON plug, straight, shielded

Phoenix Contact 2018 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1412280](#)