

Sleeve housing for cable connector - RC-0000000T0FZ - 1592992


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Sleeve housing for cable connector, angled, Screw locking, M23, shielded: yes, cable diameter range: 2 mm ... 10.5 mm



RoHS

Key Commercial Data

| | |
|------------------------|---|
| Packing unit | 8 pc |
| Minimum order quantity | 8 pc |
| GTIN |  4 046356 193689 |
| GTIN | 4046356193689 |

Technical data

General

| | |
|-----------------------------|---|
| Note | Order information: Order contact inserts and cable clamping/shield accessories separately |
| Type of locking | Screw locking |
| Contact connection method | Crimp connection |
| Type of contacts | Socket |
| Conductor entry | 2 mm ... 10.5 mm |
| Pg housing screw connection | none |

Ambient conditions

| | |
|----------------------|-------------------|
| Ambient temperature | -20 °C ... 125 °C |
| Degree of protection | IP67 |

Material

| | |
|----------------------------|--|
| Housing material | Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn) |
| Gasket and O-ring material | FPM |

Specifications according to DIN EN 61984:2001

| | |
|--------------------------|--------|
| Installation height max. | 2000 m |
|--------------------------|--------|



Sleeve housing for cable connector - RC-0000000T0FZ - 1592992

Technical data


Environmental Product Compliance

| | |
|------------|---|
| REACH SVHC | Lead 7439-92-1 |
| China RoHS | Environmentally Friendly Use Period = 50 |
| | For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration" |

Drawings



Dimensional drawing



Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

Sleeve housing for cable connector - RC-0000000T0FZ - 1592992

Approvals

| | | |
|-----|---|---------|
| EAC |  | B.01742 |
|-----|---|---------|

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

1592992