

## Contact insert - HC-B 6-EBUQ-2,5-OLOGO - 1605561

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Female insert, 6-pos., QUICKON connection, marking 1-x


### Product Description

#### Contact insert

With QUICKON connection technology, the wires are connected with just a turn of the screwdriver. The wires do not have to be stripped first. This reduces connection time by at least 60%.

RoHS

### Key Commercial Data

Packing unit	10 pc
GTIN	 4 017918 940768
GTIN	4017918940768

### Technical data

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

#### General


Note	Connectors may be operated only when there is no load/voltage.
Size	B
Number of positions	6
Flammability rating according to UL 94	V0
Assembly instructions	To ensure correct use, installation in housing with IP54 protection or better is required

### Standards and Regulations

Flammability rating according to UL 94	V0
--	----


### Drawings

Contact insert - HC-B 6-EBUQ-2,5-OLOGO - 1605561




Derating diagram: HC-B...Q2,5 series

Female insert



Dimensional drawing



Mounting cutout when used without housing

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU C- DE.AI30.B.01102
-----	--	--------------------------

Phoenix Contact 2018 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

1605561