

Europe connectors - EC 10 - 3240176

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Polypropylene Europe terminal strip, white, for connecting solid conductors and stranded conductors with and without ferrules with a cross section of 1 to 10 mm²

Your advantages

- ✓ The polypropylene insulating housing enables individual positions to be disconnected simply by twisting and without the need for tools
- ✓ The high-quality metal parts, which feature corrosion-resistant surfaces, are fixed securely in the housing
- ✓ The prismatic clamping part facilitates conductor entry and reliable contact can be established even for conductors without ferrules

Key Commercial Data

Packing unit	10 pc
GTIN	 4 046356 457811
GTIN	4046356457811

Technical data

General

Number of positions	12
Number of levels	1
Number of connections	24
Nominal cross section	10 mm ²
Color	white
Insulating material	PP
Flammability rating according to UL 94	-
Maximum load current	57 A (with 10 mm ² conductor cross section)
Nominal current I _N	57 A (with 10 mm ² conductor cross section)
Nominal voltage U _N	450 V (Only use up to 250 V without securing.)
Open side panel	No
Ambient temperature (operation)	-40 °C ... 80 °C

Dimensions

Europe connectors - EC 10 - 3240176

Technical data

Dimensions

Width	17.3 mm
Length	133.8 mm
Height	23.4 mm
Depth	17.3 mm
Drill hole spacing	11.5 mm
Pitch	11.5 mm

Connection data

Connection method	Screw connection
Screw thread	M3,5
Stripping length	7 mm
Tightening torque, min	0.8 Nm
Tightening torque max	1 Nm
Conductor cross section solid min.	1 mm ²
Conductor cross section solid max.	10 mm ²
Conductor cross section AWG min.	16
Conductor cross section AWG max.	8
Conductor cross section flexible min.	1 mm ²
Conductor cross section flexible max.	10 mm ²
Min. AWG conductor cross section, flexible	16
Max. AWG conductor cross section, flexible	8
Conductor cross section flexible, with ferrule without plastic sleeve min.	1.5 mm ²
Conductor cross section flexible, with ferrule without plastic sleeve max.	6 mm ²
Conductor cross section flexible, with ferrule with plastic sleeve min.	1.5 mm ²
Conductor cross section flexible, with ferrule with plastic sleeve max.	4 mm ²
2 conductors with same cross section, solid min.	1 mm ²
2 conductors with same cross section, solid max.	2.5 mm ²
2 conductors with same cross section, stranded min.	1.5 mm ²
2 conductors with same cross section, stranded max.	2.5 mm ²
Two conductors with the same cross section, flexible, with TWIN ferrules, with plastic sleeve, minimum	0.5 mm ²
Two conductors with the same cross section, flexible, with TWIN ferrules, with plastic sleeve, maximum	1.5 mm ²
Two conductors with the same cross section stranded, with ferrule and without plastic sleeve, minimum	0.75 mm ²
Two conductors with the same cross section stranded, with ferrule and without plastic sleeve, maximum	1.5 mm ²

Standards and Regulations

Flammability rating according to UL 94	-
--	---

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
------------	---

Europe connectors - EC 10 - 3240176

Technical data

Environmental Product Compliance

	No hazardous substances above threshold values
--	--

Classifications

eCl@ss

eCl@ss 10.0.1	27141106
eCl@ss 4.0	27141100
eCl@ss 4.1	27141100
eCl@ss 5.0	27141100
eCl@ss 5.1	27141100
eCl@ss 6.0	27141100
eCl@ss 7.0	27141106
eCl@ss 8.0	27141106
eCl@ss 9.0	27141106

ETIM

ETIM 3.0	EC001284
ETIM 4.0	EC001284
ETIM 5.0	EC001284
ETIM 6.0	EC001284
ETIM 7.0	EC001284

UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	27121703
UNSPSC 11	27121703
UNSPSC 12.01	27121703
UNSPSC 13.2	39121409
UNSPSC 18.0	39121409
UNSPSC 19.0	39121409
UNSPSC 20.0	39121409
UNSPSC 21.0	39121409

Approvals

Approvals

Approvals

EAC

Europe connectors - EC 10 - 3240176

Approvals

Ex Approvals

Approval details

EAC



RU C-
DE.BL08.B.00534

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[3240176](#)