

# 2SC0635T2A1-45 Preliminary Datasheet

Dual-Channel Cost-Effective SCALE™-2 IGBT Driver Core for 4500V IGBTs

## Abstract

The SCALE™-2 dual-driver core 2SC0635T2A1-45 combines unrivalled compactness with broad applicability. The driver is designed for universal applications requiring high reliability. The 2SC0635T2A1-45 drives all usual high-power IGBT modules up to 4500V. Its embedded paralleling capability allows easy inverter design covering higher power ratings. Multi-level topologies involving 1700V or 3300V IGBTs with higher isolation requirements can also be easily supported by 2SC0635T2A1-45.

The 2SC0635T2A1-45 combines a complete two-channel driver core with all components required for driving, such as an isolated DC/DC converter, short-circuit protection, Advanced Active Clamping as well as supply voltage monitoring. Each of the two output channels is electrically isolated from the primary side and from the other secondary channel.

An output current of 35A and 6W drive power is available per channel, making the 2SC0635T2A1-45 an ideal driver platform for universal use in medium and high-power applications. The driver provides a gate voltage swing of 15V/-10V. The turn-on voltage is regulated to maintain a stable 15V regardless of the output power level.

Its outstanding EMC allows safe and reliable operation even in hard industrial applications.

## Product Highlights

- ✓ Ultra-compact dual-channel driver
- ✓ Highly integrated SCALE-2 chipset
- ✓ Gate current  $\pm 35A$ , 6W output power per channel
- ✓ 15V/-10V gate driving
- ✓ Blocking voltages up to 4500V
- ✓ Basic isolation to IEC 61800-5-1 and IEC 60664-1
- ✓ Short delay and low jitter
- ✓ 15V logic level interface
- ✓ UL compliant
- ✓ Lead free

## Applications

- ✓ Traction
- ✓ Railroad power supplies
- ✓ Light rail vehicles
- ✓ HVDC
- ✓ Flexible AC transmission systems (FACTS)
- ✓ Medium-voltage converters
- ✓ Wind-power converters
- ✓ Industrial drives
- ✓ Medical applications

## Preliminary Data Sheet

### Safety Notice!

The data contained in this data sheet is intended exclusively for technically trained staff. Handling all high-voltage equipment involves risk to life. Strict compliance with the respective safety regulations is mandatory!

Any handling of electronic devices is subject to the general specifications for protecting electrostatic-sensitive devices according to international standard IEC 60747-1, Chapter IX or European standard EN 100015 (i.e. the workplace, tools, etc. must comply with these standards). Otherwise, this product may be damaged.

### Important Product Documentation

This data sheet contains only product-specific data. For a detailed description, must-read application notes and important information that apply to this product, please refer to "2SC0635T Description & Application Manual" on [www.power.com/igbt-driver/go/2SC0635T](http://www.power.com/igbt-driver/go/2SC0635T).

### Absolute Maximum Ratings

| Parameter                       | Remarks                                     | Min  | Max          | Unit       |
|---------------------------------|---|------|--------------|------------|
| Supply voltage $V_{DC}$         | VDC to GND                                  | 0    | 16           | V          |
| Supply voltage $V_{CC}$         | VCC to GND                                  | 0    | 16           | V          |
| Logic input and output voltages | Primary side, to GND                        | -0.5 | $V_{CC}+0.5$ | V          |
| SOx current                     | Failure condition, total current            |      | 20           | mA         |
| Gate peak current $I_{out}$     | Note 1                                      | -35  | +35          | A          |
| External gate resistance        | Turn-on and turn-off                        | 0.5  |              | $\Omega$   |
| Average supply current $I_{DC}$ | Notes 2, 3                                  |      | 1450         | mA         |
| Output power                    | Ambient temperature 0°C...70°C (Notes 4, 5) |      | 9            | W          |
|                                 | Ambient temperature -40°C...85°C (Note 4)   |      | 6            | W          |
| Switching frequency $f$         |   |      | 100          | kHz        |
| Test voltage (50Hz/1min.)       | Primary to secondary (Note 14)              |      | 10.2         | $kV_{eff}$ |
|                                 | Secondary to secondary (Note 14)            |      | 10.2         | $kV_{eff}$ |
| $ dV/dt $                       | Rate of change of input to output voltage   |      | 35           | $kV/\mu s$ |
| Operating voltage               | Primary/secondary, secondary/secondary      |      | 4500         | $V_{peak}$ |
| Operating temperature           | Notes 5, 17                                 | -40  | +85          | °C         |
| Storage temperature             |   | -55  | +90          | °C         |

## Preliminary Data Sheet

**Recommended Operating Conditions**

| Power Supply            | Remarks               | Min  | Typ | Max  | Unit |
|-------------------------|-----------------------|------|-----|------|------|
| Supply voltage $V_{DC}$ | VDC to GND, IGBT mode | 14.5 | 15  | 15.5 | V    |
| Supply voltage $V_{CC}$ | VCC to GND            | 14.5 | 15  | 15.5 | V    |

**Electrical Characteristics (IGBT mode)**

All data refer to +25°C and  $V_{CC} = V_{DC} = 15V$  unless otherwise specified.

| Power supply                  | Remarks                  | Min | Typ | Max | Unit |
|-------------------------------|--------------------------|-----|-----|-----|------|
| Supply current $I_{DC}$       | Without load             |     | 70  |     | mA   |
| Supply current $I_{CC}$       | $f = 0Hz$                |     | 25  |     | mA   |
| Supply current $I_{CC}$       | $f = 100kHz$             |     | 34  |     | mA   |
| Coupling capacitance $C_{io}$ | Primary to output, total |     | 19  |     | pF   |

| Power Supply Monitoring            | Remarks                             | Min  | Typ  | Max  | Unit |
|------------------------------------|-------------------------------------|------|------|------|------|
| Supply threshold $V_{CC}$          | Primary side, clear fault           | 11.9 | 12.6 | 13.3 | V    |
|                                    | Primary side, set fault (Note 11)   | 11.3 | 12.0 | 12.7 | V    |
| Monitoring hysteresis              | Primary side, set/clear fault       | 0.35 |      |      | V    |
| Supply threshold $V_{ISOx}-V_{Ex}$ | Secondary side, clear fault         | 12.1 | 12.6 | 13.1 | V    |
|                                    | Secondary side, set fault (Note 12) | 11.5 | 12.0 | 12.5 | V    |
| Monitoring hysteresis              | Secondary side, set/clear fault     | 0.35 |      |      | V    |
| Supply threshold $V_{Ex}-V_{COMx}$ | Secondary side, clear fault         | 5    | 5.15 | 5.3  | V    |
|                                    | Secondary side, set fault (Note 12) | 4.7  | 4.85 | 5    | V    |
| Monitoring hysteresis              | Secondary side, set/clear fault     | 0.15 |      |      | V    |

| Logic Inputs and Outputs    | Remarks                             | Min | Typ | Max | Unit       |
|-----------------------------|-------------------------------------|-----|-----|-----|------------|
| Input impedance             | $V(INx) = 15V$                      | 4.7 | 4.8 | 4.9 | k $\Omega$ |
| Turn-on threshold           | $V(INx)$                            |     | 8.8 |     | V          |
| Turn-off threshold          | $V(INx)$                            |     | 4.5 |     | V          |
| SOx pull-up resistor to VCC | On board                            |     | 10  |     | k $\Omega$ |
| SOx output voltage          | Failure condition, $I(SOx) < 6.5mA$ |     |     | 0.7 | V          |

| Short-Circuit Protection       | Remarks                                  | Min | Typ | Max | Unit    |
|--------------------------------|--|-----|-----|-----|---------|
| $V_{CE}$ -monitoring threshold | Factory set value (Note 18)              |     | 9.3 |     | V       |
| Minimum response time          | Note 9                                   |     | 5.1 |     | $\mu s$ |
| Blocking time                  | After fault. Factory set value (Note 10) |     | 130 |     | ms      |
| Minimum blocking time          | Note 10                                  |     | 9   |     | $\mu s$ |

## Preliminary Data Sheet

| Short-Circuit Protection           | Remarks                               | Min  | Typ  | Max  | Unit              |
|------------------------------------|---------------------------------------|------|------|------|-------------------|
| Delay in IGBT turn-off             | Factory-set value (Note 19)           |      | 0.2  |      | μs                |
| Timing Characteristics             | Remarks                               | Min  | Typ  | Max  | Unit              |
| Turn-on delay $t_{d(on)}$          | Note 6                                |      | 80   |      | ns                |
| Turn-off delay $t_{d(off)}$        | Note 6                                |      | 65   |      | ns                |
| Jitter of turn-on delay            | Note 16                               |      | ±2   |      | ns                |
| Jitter of turn-off delay           | Note 16                               |      | ±2   |      | ns                |
| Output rise time $t_{r(out)}$      | Note 7                                |      | 20   |      | ns                |
| Output fall time $t_{f(out)}$      | Note 7                                |      | 25   |      | ns                |
| Transmission delay of fault state  | Note 13                               |      | 450  |      | ns                |
| Electrical Isolation               | Remarks                               | Min  | Typ  | Max  | Unit              |
| Test voltage (50Hz/1s)             | Primary to secondary side (Note 14)   | 10.2 | 10.3 | 10.4 | kV <sub>eff</sub> |
|                                    | Secondary to secondary side (Note 14) | 10.2 | 10.3 | 10.4 | kV <sub>eff</sub> |
| Partial discharge extinction volt. | Primary to secondary side (Note 15)   | 5400 |      |      | V <sub>peak</sub> |
|                                    | Secondary to secondary side (Note 15) | 5400 |      |      | V <sub>peak</sub> |
| Creepage distance                  |                                       |      |      |      |                   |
| On the PCB                         | Primary to secondary side             | 34   |      |      | mm                |
| (Material group IIIa)              | Secondary to secondary side           | 34   |      |      | mm                |
| On the transformer                 | Primary to secondary side             | 29   |      |      | mm                |
| (Material group I)                 | Secondary to secondary side           | 25   |      |      | mm                |
| Clearance distance                 | Primary to secondary side             | 25   |      |      | mm                |
|                                    | Secondary to secondary side           | 18   |      |      | mm                |
| Output                             | Remarks                               | Min  | Typ  | Max  | Unit              |
| Blocking capacitance               | VISOx to VEx (Note 8)                 |      | 9.4  |      | μF                |
|                                    | VEx to COMx (Note 8)                  |      | 9.4  |      | μF                |

### Output voltage swing

The output voltage swing consists of two distinct segments. First, there is the turn-on voltage  $V_{GHx}$  between pins GHx and VEx.  $V_{GHx}$  is regulated and maintained at a constant level for all output power values and frequencies.

The second segment of the output voltage swing is the turn-off voltage  $V_{GLx}$ .  $V_{GLx}$  is measured between pins GLx and VEx. It is a negative voltage. It changes with the output power to accommodate the inevitable voltage drop across the internal DC/DC converter.

## Preliminary Data Sheet

| Output Voltage              | Remarks            | Min | Typ   | Max | Unit |
|-----------------------------|--------------------|-----|-------|-----|------|
| Turn-on voltage, $V_{GHx}$  | Any load condition |     | 15.0  |     | V    |
| Turn-off voltage, $V_{GLx}$ | No load            |     | -10.8 |     | V    |
| Turn-off voltage, $V_{GLx}$ | 6W output power    |     | -8.5  |     | V    |
| Turn-off voltage, $V_{GLx}$ | 9W output power    |     | -8.2  |     | V    |

### Footnotes to the Key Data

- 1) The maximum peak gate current refers to the highest current level occurring during the product lifetime. It is an absolute value and does also apply for short pulses.
- 2) The average supply input current is limited for thermal reasons. Higher values than specified by the absolute maximum rating are permissible (e.g. during power supply start up) if the average remains below the given value, provided the average is taken over a time period which is shorter than the thermal time constants of the driver in the application.
- 3) There is no means of actively controlling or limiting the input current in the driver. In the case of start-up with very high blocking capacitor values, or in case of short circuit at the output, the supply input current has to be limited externally.
- 4) The maximum output power must not be exceeded at any time during operation. The absolute maximum rating must also be observed for time periods shorter than the thermal time constants of the driver in the application.
- 5) An extended output power range is specified in the output power section for ambient temperatures limited from 0°C to 70°C.
- 6) The delay time is measured between 50% of the input signal and 10% voltage swing of the corresponding output. The delay time is independent on the output loading.
- 7) Output rise and fall times are measured between 10% and 90% of the nominal output swing with an output load of 4.7Ω and 270nF. The values are given for the driver side of the gate resistors. The time constant of the output load in conjunction with the present gate resistors leads to an additional delay at the load side of the gate resistors.
- 8) External blocking capacitors should be placed between the VISOx and VEx as well as the VEx and COMx terminals. Refer to "2SC0635T Description & Application Manual" (paragraph "DC/DC output (VISOx), emitter (VEx) and COMx terminals") for recommendations. Ceramic capacitors are recommended.
- 9) The minimum response time is valid for the circuit given in the description and application manual (Fig. 7) with the values of table 1.
- 10) The blocking time sets a minimum time span between the end of any secondary-side fault state and the start of normal operation (remove fault from pin SOx). The value of the blocking time can be adjusted at pin TB.
- 11) Undervoltage monitoring of the primary-side supply voltage (VCC to GND). If the voltage drops below this limit, a fault is transmitted to both SOx outputs and the power semiconductors are switched off.
- 12) Undervoltage monitoring of the secondary-side supply voltage (VISOx to VEx and VEx to COMx, which correspond to the approximate turn-on and turn-off gate-emitter voltages). If the corresponding voltage drops below this limit, a fault is transmitted to the corresponding SOx output and the IGBT is switched off after the corresponding delays. Refer to "2SC0635T Description & Application Manual" for more details.
- 13) Transmission delay of fault state from the secondary side to the corresponding primary-side status output.
- 14) HiPot testing (= dielectric testing) must generally be restricted to suitable components. This gate driver is suited for HiPot testing. Nevertheless, it is strongly recommended to limit the testing time to 1s slots. Excessive HiPot testing at voltages much higher than 3182V<sub>AC(eff)</sub> may lead to insulation degradation. No degradation has been observed over 1min. testing at 10.2kV<sub>AC(eff)</sub>. Every production sample shipped to customers has undergone 100% testing at the given value for 1s.

---

## Preliminary Data Sheet

- 15) Partial discharge measurement is performed in accordance with IEC 60270 and isolation coordination specified in IEC 60664-1. The partial discharge extinction voltage between primary and either secondary side is coordinated for basic isolation to IEC 60664-1.
- 16) Jitter measurements are performed with input signals INx switching between 0V and 15V referred to GND, with a corresponding rise time and fall time of 6ns.
- 17) The minimum operating temperature is limited to -40°C for the first series. This will be extended to -55°C upon completion of the ongoing qualification program.
- 18) The  $V_{CE}$ -monitoring threshold value can be reduced with an external resistor. Refer to "2SC0635T Description & Application Manual".
- 19) The turn-off event of the IGBT after a secondary-side fault (IGBT short circuit or undervoltage monitoring) can be additionally delayed with an external capacitor. Refer to "2SC0635T Description & Application Manual".

### RoHS Statement

On the basis of Annexes II and III of European Directive 2011/65/EC of 08 June 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (RoHS), we hereby state that the products described in this datasheet do not contain lead (Pb), mercury (Hg), hexavalent chromium (Cr VI), cadmium (Cd), polibrometo of biphenyl (PBB) or polibrometo diphenyl ether (PBDE) in concentrations exceeding the restrictions set forth in Annex II of 2011/65/EC with due consideration of the applicable exemptions as listed in Annex III of 2011/65/EC.

### Legal Disclaimer

The statements, technical information and recommendations contained herein are believed to be accurate as of the date hereof. All parameters, numbers, values and other technical data included in the technical information were calculated and determined to our best knowledge in accordance with the relevant technical norms (if any). They may base on assumptions or operational conditions that do not necessarily apply in general. We exclude any representation or warranty, express or implied, in relation to the accuracy or completeness of the statements, technical information and recommendations contained herein. No responsibility is accepted for the accuracy or sufficiency of any of the statements, technical information, recommendations or opinions communicated and any liability for any direct, indirect or consequential loss or damage suffered by any person arising therefrom is expressly disclaimed.

---

## Preliminary Data Sheet

### Ordering Information

The general terms and conditions of delivery of Power Integrations Switzerland GmbH apply.

**Type Designation****Description**

2SC0635T2A1-45

Dual-channel 4.5kV SCALE-2 driver core (Increased EMI capability)

Product home page: [www.power.com/igbt-driver/go/2SC0635T](http://www.power.com/igbt-driver/go/2SC0635T)

Refer to [www.power.com/igbt-driver/go/nomenclature](http://www.power.com/igbt-driver/go/nomenclature) for information on driver nomenclature

### Information about Other Products

**For other drivers, product documentation, and application support**

Please click: [www.power.com](http://www.power.com)

### Manufacturer

Power Integrations Switzerland GmbH  
Johann-Renfer-Strasse 15  
2504 Biel-Bienne, Switzerland

Phone +41 32 344 47 47  
Fax +41 32 344 47 40  
Email [igbt-driver.sales@power.com](mailto:igbt-driver.sales@power.com)  
Website [www.power.com/igbt-driver](http://www.power.com/igbt-driver)

© 2013...2015 Power Integrations Switzerland GmbH.

We reserve the right to make any technical modifications without prior notice.

All rights reserved.

Version 1.0 from 2015-03-10

## Preliminary Data Sheet

**Power Integrations Worldwide High Power Customer Support Locations****World Headquarters**

5245 Hellyer Avenue  
San Jose, CA 95138 | USA  
Main +1 408 414 9200  
Customer Service:  
Phone +1 408 414 9665  
Fax +1 408 414 9765  
Email [usasales@power.com](mailto:usasales@power.com)

**Switzerland (Biel)**

Johann-Renfer-Strasse 15  
2504 Biel-Bienne | Switzerland  
Phone +41 32 344 47 47  
Fax +41 32 344 47 40  
Email [igbt-driver.sales@power.com](mailto:igbt-driver.sales@power.com)

**Germany (Ense)**

HellwegForum 1  
59469 Ense | Germany  
Phone +49 2938 643 9990  
Email [igbt-driver.sales@power.com](mailto:igbt-driver.sales@power.com)

**Germany (Munich)**

Lindwurmstrasse 114  
80337 Munich | Germany  
Phone +49 895 527 39110  
Fax +49 895 527 39200  
Email [eurosales@power.com](mailto:eurosales@power.com)

**China (Shanghai)**

Rm 2410, Charity Plaza, No. 88  
North Caoxi Road  
Shanghai, PRC 200030  
Phone +86 21 6354 6323  
Fax +86 21 6354 6325  
Email [chinasales@power.com](mailto:chinasales@power.com)

**China (Shenzhen)**

17/F, Hivac Building, No 2,  
Keji South 8th Road,  
Nanshan District  
Shenzhen | China, 518057  
Phone +86 755 8672 8725  
Fax +86 755 8672 8690  
Hotline +86 400 0755 669  
Email [chinasales@power.com](mailto:chinasales@power.com)

**Italy (Milano)**

Via Milanese 20, 3rd. Fl.  
20099 Sesto San Giovanni | Italy  
Phone +39 024 550 8701  
Fax +39 028 928 6009  
Email [eurosales@power.com](mailto:eurosales@power.com)

**UK (Herts)**

First Floor, Unit 15, Meadway Court,  
Rutherford Close, Stevenage,  
Herts SG1 2EF | United Kingdom  
Phone +44 1252 730 141  
Fax +44 1252 727 689  
Email [eurosales@power.com](mailto:eurosales@power.com)

**India (Bangalore)**

#1, 14th Main Road  
Vasanthanagar  
Bangalore 560052 | India  
Phone +91 80 4113 8020  
Fax +91 80 4113 8023  
Email [indiasales@power.com](mailto:indiasales@power.com)

**Japan (Kanagawa)**

Kosei Dai-3 Bldg., 2-12-11, Shin-  
Yokohama, Kohoku-ku, Yokohama-shi,  
Kanagawa 222-0033 | Japan  
Phone +81 45 471 1021  
Fax +81 45 471 3717  
Email [japansales@power.com](mailto:japansales@power.com)

**Korea (Seoul)**

RM 602, 6FL  
Korea City Air Terminal B/D, 159-6  
Samsung-Dong, Kangnam-Gu  
Seoul 135-728 | Korea  
Phone +82 2 2016 6610  
Fax +82 2 2016 6630  
Email [koreasales@power.com](mailto:koreasales@power.com)

**Taiwan (Taipei)**

5F, No. 318, Nei Hu Rd., Sec. 1  
Nei Hu Dist.  
Taipei 11493 | Taiwan R.O.C.  
Phone +886 2 2659 4570  
Fax +886 2 2659 4550  
Email [taiwansales@power.com](mailto:taiwansales@power.com)



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Power Integrations:](#)

[2SC0635T2A1-45](#)