



UPS



Data Center




PHR-1290 12V 21.2 AH @ 20-hr. 90 W/Cell @ 15-min.

Rechargeable Sealed Lead Acid Battery
PHR – High-Rate Series


TERMINALS: (mm)

T12-A: Threaded insert with
3mm stud fastener






Torque: 2.0~3.0 Nxm

DIMENSIONS: inch (mm)



L: 7.14 (181)
W: 2.99 (76)
H: 6.56 (167)
HT: 6.56 (167)

Tolerances are +/- 0.04 in.
(+/- 1mm) and +/- 0.08 in.
(+/- 2mm) for height
dimensions. All data subject
to change without notice.



GLOBAL HEADQUARTERS (USA AND INTERNATIONAL EXCLUDING EMEA)

Power-Sonic Corporation
365 Cabela Dr Suite 300,
Reno, Nevada 89523
USA
T: +1 619 661 2020
E: customer-service@power-sonic.com

POWER-SONIC EMEA (EMEA – EUROPE, MIDDLE EAST AND AFRICA)

Smitsspol 4, 3861 RS Nijkerk,
The Netherlands
T NL: + 31 33 7410 700
T UK: + 44 1268 560 686
T FR: + 33 344 32 18 17
E: salesEMEA@power-sonic.com

FEATURES

- Superb high-rate discharge characteristics that ensure reliable performance in UPS applications for up to 10 years
- Specifically designed for UPS and critical power backup applications
- Valve regulated, maintenance free spill proof construction
- Precision plate pasting for higher consistency with 100% load testing to ensure uniform capacity
- Patented dual-paste process for enhanced active material bonding and computer guided volumetric electrolyte control for precision filling
- Rugged vibration and impact resistant ABS case and cover flame retardant to UL94-V0

APPROVALS

- Approved for transport by air. D.O.T., I.A.T.A., F.A.A. and C.A.B. certified
- U.L recognized
- ISO9001:2015 – Quality management systems

PERFORMANCE SPECIFICATIONS

Nominal Voltage	12 volts (6 cells)
Nominal Power (15 min.)	90 W/Cell
Rated Capacity	
20-hr. (1.06A to 10.80 volts)	21.2 AH
10-hr. (2.00A to 10.50 volts)	20.0 AH
8-hr. (2.44A to 10.50 volts)	19.5 AH
Approximate Weight	14.00 lbs. (6.35 kg)
Internal Resistance (approx.)	9.0 milliohms
Max Discharge Current (5 Sec.)	470 amperes
Shelf Life (% of nominal capacity at 68°F (20°C))	
1 Month	97%
3 Month	91%
6 Month	83%
Operating Temperature Range	
Charge	5°F (-15°C) to 122°F (50°C)
Discharge	-4°F (-20°C) to 140°F (60°C)
Case and Cover	Flame Retardant ABS Plastic UL94-V-0
Power Sonic Chargers	PSC-124000-PC PSC-243500-PC

PHR-1290 12V 21.2 AH @ 20-hr. 90 W/Cell @ 15-min.

Rechargeable Sealed Lead Acid Battery
PHR – High-Rate Series

CONSTANT CURRENT DISCHARGE (AMPERES) AT 25°C (77°F)

F.V/Time	5min	10min	15min	20min	30min	45min	1h	2h	3h	4h	5h	6h	8h	10h	20h
1.85V/cell	55.4	41.2	35.2	29.8	21.8	15.7	12.3	6.9	5.0	4.0	3.4	2.9	2.3	1.9	1.0
1.80V/cell	63.4	46.7	39.0	32.7	23.6	16.8	13.1	7.3	5.3	4.2	3.5	3.1	2.4	2.0	1.1
1.75V/cell	71.7	51.2	42.5	34.8	24.9	17.6	13.7	7.6	5.5	4.4	3.6	3.1	2.4	2.0	1.1
1.70V/cell	79.4	56.2	45.7	36.9	26.1	18.3	14.1	7.8	5.6	4.4	3.7	3.2	2.5	2.0	1.1
1.65V/cell	86.5	60.5	48.9	38.5	26.8	18.7	14.5	7.9	5.7	4.5	3.7	3.2	2.5	2.1	1.1
1.60V/cell	93.4	63.1	50.2	39.2	27.2	18.9	14.6	8.0	5.8	4.6	3.8	3.2	2.5	2.1	1.1

CONSTANT POWER DISCHARGE (WATTS/CELL) AT 25°C (77°F)

F.V/Time	5min	10min	15min	20min	30min	45min	1h	2h	3h	4h	5h	6h	8h	10h	20h
1.85V/cell	103.8	78.4	67.9	58.1	42.9	31.1	24.6	13.9	10.1	8.1	6.9	5.9	4.7	3.9	2.1
1.80V/cell	117.4	87.9	74.6	63.2	46.1	33.2	26.1	14.6	10.7	8.5	7.2	6.2	4.9	4.1	2.2
1.75V/cell	130.7	95.1	80.3	66.5	48.3	34.6	27.1	15.1	10.9	8.8	7.3	6.3	5.0	4.1	2.2
1.70V/cell	142.2	102.8	85.2	69.8	50.3	35.7	27.9	15.5	11.2	8.9	7.4	6.4	5.0	4.2	2.2
1.65V/cell	151.7	108.9	90.0	71.9	51.3	36.2	28.3	15.7	11.4	9.0	7.5	6.5	5.1	4.2	2.3
1.60V/cell	160.8	111.8	90.9	72.3	51.4	36.2	28.4	15.7	11.4	9.1	7.6	6.5	5.1	4.2	2.3

CHARGING

Cycle Applications: Apply constant voltage charge at 2.35v/c - 2.45v/c (14.1 – 14.7v for 12v Monobloc) at 20°C. Initial charging current should be set at less than 0.25C Amps. Switch to float charge to avoid overcharging.

"Float" or "Stand-By" Service: Apply constant voltage charge of 2.25v/c – 2.30v/c (13.5 to 13.8 volts for 12v Monobloc at 20°C. When held at this voltage, the battery will seek its own current level and maintain itself in a fully charged condition.

Temperature Compensation: Charging Voltage for both Cyclic and Standby applications should be regulated in relation to ambient temperature. As temperature rises charging voltage should be reduced to prevent overcharge and increased as temperature falls to avoid undercharge.

For further charging information including temperature compensation factors, see Power Sonic Technical Manual/ Power Sonic Charger specifications.

APPLICATIONS

- High Rate UPS
- Data Centers

GLOBAL HEADQUARTERS (USA AND INTERNATIONAL EXCLUDING EMEA)

Power-Sonic Corporation
365 Cabela Dr Suite 300,
Reno, Nevada 89523
USA
T: +1 619 661 2020
E: customer-service@power-sonic.com

POWER-SONIC EMEA (EMEA – EUROPE, MIDDLE EAST AND AFRICA)

Smitsspol 4, 3861 RS Nijkerk,
The Netherlands
T NL: + 31 33 7410 700
T UK: + 44 1268 560 686
T FR: + 33 344 32 18 17
E: salesEMEA@power-sonic.com

CHARGERS

Power Sonic offers a wide range of chargers suitable for batteries with a variety of capacities.

Please refer to our website for more information on our switch mode and transformer type chargers.

Please contact our technical department for advice if you have difficulty in locating a suitable charger.

FURTHER INFORMATION

Please refer to our website www.power-sonic.com for a complete range of useful downloads, such as product catalogs, material safety data sheets (MSDS), ISO certification, etc.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Power-Sonic:](#)

[PHR-1290 M6 FR](#)