




## PSH-655FR 6V 5.5 AH @ 20-hr. 21.1 W/Cell @ 15-min.

Rechargeable Sealed Lead Acid Battery  
PSH – High-Rate Series


### TERMINALS (mm)

F1: Quick disconnect tabs,  
0.187" x 0.032" – Mate with  
AMP. INC. FASTON "187" series




Torque – Not Applicable

### DIMENSIONS inch (mm)



L: 2.76 (70)  
W: 1.85 (47)  
H: 3.94 (100)  
HT: 4.17 (106)  
Tolerances are +/- 0.04 in.  
(+/- 1mm) and +/- 0.08 in.  
(+/- 2mm) for height  
dimensions. All data subject  
to change without notice.



### GLOBAL HEADQUARTERS (USA AND INTERNATIONAL EXCLUDING EMEA)

**Power-Sonic Corporation**  
365 Cabela Dr Suite 300,  
Reno, Nevada 89523  
USA  
T: +1 619 661 2020  
E: customer-service@power-sonic.com

### POWER-SONIC EMEA (EMEA – EUROPE, MIDDLE EAST AND AFRICA)

Smitsspol 4, 3861 RS Nijkerk,  
The Netherlands  
T NL: + 31 33 7410 700  
T UK: + 44 1268 560 686  
T FR: + 33 344 32 18 17  
E: salesEMEA@power-sonic.com

## FEATURES

- Absorbent Glass Mat (AGM) technology for superior performance
- Designed specifically for high-rate discharge applications
- Valve regulated, maintenance free spill proof construction
- Exceptionally high energy density
- Constant power (watts/cell)
- Rugged vibration and impact resistant ABS case and cover flame retardant to UL94-V0

## APPROVALS

- Approved for transport by air. D.O.T., I.A.T.A., F.A.A. and C.A.B. certified
- U.L recognized
- ISO9001:2015 – Quality management systems

## PERFORMANCE SPECIFICATIONS

<b>Nominal Voltage</b>	6 volts (3 cells)
<b>Nominal Power (15 min.)</b>	21.1 W/Cell
<b>Rated Capacity</b>	
20-hr. (275mA to 5.25 volts)	5.50 AH
10-hr. (950mA to 5.10 volts)	4.75 AH
5-hr. (540mA to 5.25 volts)	5.40 AH
1-hr. (3.7A to 4.50 volts)	3.70 AH
15-min. (11.2A to 4.50 volts)	2.80 AH
<b>Approximate Weight</b>	2.10 lbs. (0.95 kg)
<b>Internal Resistance (approx.)</b>	10.0 milliohms
<b>Max Discharge Current (5 Sec.)</b>	16.5 amperes
<b>Max Short-Duration Discharge Current (10 Sec.)</b>	55.0 amperes
<b>Shelf Life (% of nominal capacity at 68°F (20°C))</b>	
1 Month	97%
3 Month	91%
6 Month	83%
<b>Operating Temperature Range</b>	
Charge	5°F (-15°C) to 122°F (50°C)
Discharge	-4°F (-20°C) to 140°F (60°C)
<b>Case and Cover</b>	Flame Retardant ABS Plastic UL94-V-0
<b>Power Sonic Chargers</b>	PSC-6500A-C PSC-61000A-C PSC-61000-PC

## PSH-655FR 6V 5.5 AH @ 20-hr. 21.1 W/Cell @ 15-min.

Rechargeable Sealed Lead Acid Battery  
PSH – High-Rate Series

### CONSTANT POWER DISCHARGE (WATTS/CELL) AT 25°C (77°F)

Model	Final Voltage	Watts per Cell @ 25°C (68°F)						
		5min	10min	15min	20min	30min	45min	60min
PSH-655FR	1.75	37.5	26.2	20.1	16.2	11.7	8.36	6.72
	1.70	38.9	27.1	20.6	16.6	11.9	8.52	6.83
	1.67	40.0	27.7	21.1	16.9	12.1	8.63	6.92

## CHARGING

**Cycle Applications:** Apply constant voltage charge at 2.35v/c – 2.45v/c (14.1 – 14.7v for 12v Monobloc) at 20°C. Initial charging current should be set at less than 0.25C Amps. Switch to float charge to avoid overcharging.

**“Float” or “Stand-By” Service:** Apply constant voltage charge of 2.25v/c – 2.30v/c (13.5 to 13.8 volts for 12v Monobloc at 20°C. When held at this voltage, the battery will seek its own current level and maintain itself in a fully charged condition.

**Temperature Compensation:** Charging Voltage for both Cyclic and Standby applications should be regulated in relation to ambient temperature. As temperature rises charging voltage should be reduced to prevent overcharge and increased as temperature falls to avoid undercharge.

For further charging information including temperature compensation factors, see Power Sonic Technical Manual/Power Sonic Charger specifications.

## APPLICATIONS

- UPS
- Telecoms
- Data Center
- Fire and Security

## CHARGERS

Power Sonic offers a wide range of chargers suitable for batteries with a variety of capacities.


Please refer to our website for more information on our switch mode and transformer type chargers.

Please contact our technical department for advice if you have difficulty in locating a suitable charger.


## FURTHER INFORMATION

Please refer to our website [www.power-sonic.com](http://www.power-sonic.com) for a complete range of useful downloads, such as product catalogs, material safety data sheets (MSDS), ISO certification, etc.

## DISCHARGE CHARACTERISTICS



## SHELF LIFE & STORAGE



### GLOBAL HEADQUARTERS (USA AND INTERNATIONAL EXCLUDING EMEA)

**Power-Sonic Corporation**  
365 Cabela Dr Suite 300,  
Reno, Nevada 89523  
USA  
T: +1 619 661 2020  
E: [customer-service@power-sonic.com](mailto:customer-service@power-sonic.com)

### POWER-SONIC EMEA (EMEA – EUROPE, MIDDLE EAST AND AFRICA)

Smitsspol 4, 3861 RS Nijkerk,  
The Netherlands  
T NL: + 31 33 7410 700  
T UK: + 44 1268 560 686  
T FR: + 33 344 32 18 17  
E: [salesEMEA@power-sonic.com](mailto:salesEMEA@power-sonic.com)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Power-Sonic:

[PSH-655 FR](#) [PSH-655F1-HR](#)