


AST-01708MR-R 17mm Speaker




3541 Stop Eight Road • Dayton, Ohio 45414

Product Overview

- 17mm diameter speaker with Neodymium magnet for 90 dB sensitivity
- 0.2W continuous, 0.5W maximum power handling and 8Ω impedance
- Mylar cone for wide frequency response
- Thru hole design and wave solderable for PCB mount






AST-01708MR-R 17mm Speaker

Mechanical and Environment Testing

Test Description	Test Condition
High Temperature	55°C with random humidity for 96 hours
Low Temperature	-20°C with random humidity for 96 hours
Humidity	40°C with 90% to 95% relative humidity for 96 hours
Vibration	1.5 mm movement modulated at 10 to 55 Hz for 2 hours
Drop Test	75 cm free fall onto 40 mm thick board, 10 cycles
Temperature Cycle Test	-20°C to 55°C, 5 cycles (refer to Temperature Cycle Test Graph)


After tests, speaker shall rest for 1 hours. SPL shall not deviate ± 3 dB from pre-test measurement.

Temperature Cycle Test Graph





Wave Solder Profile

- Preheat temperature: Max 100° less than 80 seconds
- Soldering bath temperature 250°C (lead)/265°C (lead-free alloy)
- Wave soldering cycle time: 4 sec. (single wave), 6 sec. (dual wave)



Packaging Information



Outer Box	310mmx248mmx49mm	1x650PCS=650PCS
Carton	550mmx330mmx290mm	650PCSx10=6,500PCS




SPECIFICATIONS

PARAMETERS	VALUES	UNITS
RATED INPUT POWER	0.2	W
MAX INPUT POWER	0.5	W
IMPEDANCE	8 ± 15%	OHM
OUTPUT SPL @ 0.2W/0.1M (AT 2.0, 2.5, 3.0, 4.0 kHz)	87 ± 3	dBA
DISTORTION (MAX.)	5%	-
RESONANT FREQUENCY	1,500 ± 20%	Hz
FREQUENCY RANGE	1,500 ~ 20,000	Hz
HOUSING MATERIAL	PBT	-
CONE MATERIAL	MYLAR	-
MAGNET MATERIAL	Nd-Fe-B	-
OPERATING TEMPERATURE	-20 ~ +55	°C
WEIGHT	2	grams

THIS DOCUMENT CONTAINS DATA PROPRIETARY TO PROJECTS UNLIMITED, INC. ANY USE OR REPRODUCTION, IN ANY FORM, WITHOUT PRIOR WRITTEN PERMISSION OF PROJECTS UNLIMITED, INC. IS PROHIBITED.
©2003, Projects Unlimited Inc.

REVISION HISTORY

LTR	DESCRIPTION	DATE	APPROVED
-	RELEASED FROM ENGINEERING	11/2/2005	
A	ADDED OVERALL HEIGHT DIMENSION	2/24/2009	B.R.
B	REVISED TO INVENTOR 3-D DRAWING TEMPLATE	2/25/2009	B.R.



NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS.
2. SPECIFICATIONS SUBJECT TO CHANGE OR WITHDRAWAL WITHOUT NOTICE.
3. THIS PART IS RoHS 2002/95/EC COMPLIANT.

UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN MILLIMETERS, TOLERANCES ARE ±0.5 AND ANGLES ARE ±3°.	SIZE A3	Designed by	Date	Checked by	Date	Approved by	Date	Drawn Date
		J.A.F.	11/2/2005	B.R.	11/2/2005	E.P.	11/2/2005	2/25/2009
AST-01708MR-R.idw						AST-01708MR-R Speaker		
						Edition		Sheet
						-		1 / 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[PUI Audio:](#)

[AST-01708MR-R](#)