

SMT-0825-S-2-R 8.5 x 8.5mm Transducer


3541 Stop Eight Road • Dayton, Ohio 45414

Product Overview

- Side-firing electromechanical transducer designed for 2.5 to 4.5 Vp-p
- Small 8.5 x 8.5mm footprint and 4mm height for thin, modern devices
- 87 dBA minimum output (3.6Vp-p @ 10 cm) and 2.5kHz resonant frequency
- Designed for reflow soldering using a lead-free profile




Frequency Response (3.6 Vp-p @ 0.1 meters)



Authorized by PUI Audio Inc. and CFSI





SMT-0825-S-2-R

8.5 x 8.5mm


Transducer

Mechanical and Environment Testing


Test Description	Test Condition
High Temperature	85°C ($\pm 2^\circ\text{C}$) with random humidity for 96 hours
Low Temperature	-40°C ($\pm 2^\circ\text{C}$) with random humidity for 96 hours
Humidity	25°C to 60°C with 90% to 95% relative humidity for 12 hours, 10 cycles
Vibration	1.53 mm movement modulated at 10-55 Hz in 3 directions for 6 hours
Drop Test	120 cm free fall in six directions, 3 cycles
Temperature Cycle Test	-30°C to 70°C, five 90 minute cycles

After testing, part shall rest for two hours and then be tested for a clean, pure tone.


Recommended Reflow Profile



Tape Dimensions



Recommended Land Pattern



SPECIFICATIONS





PARAMETERS	VALUES	UNIT
RATED VOLTAGE	3.6	Vp-p
OPERATING VOLTAGE RANGE	2.5 ~ 4.5	Vp-p
RATED CURRENT (MAX)	90	mA
COIL RESISTANCE	15 ± 3	OHM
MINIMUM SPL @ 10 CM	87	dB
RESONANT FREQUENCY	2,500 ± 500	Hz
OPERATING TEMPERATURE	-30 ~ +70	°C
STORAGE TEMPERATURE	-40 ~ +85	°C
HOUSING MATERIAL	LCP	-
TERMINAL MATERIAL	Sn PLATED PHOSPHOR BRONZE	-
WEIGHT	0.45	grams

THIS DOCUMENT CONTAINS DATA PROPRIETARY TO PROJECTS UNLIMITED, INC. ANY USE OR REPRODUCTION, IN ANY FORM, WITHOUT PRIOR WRITTEN PERMISSION OF PROJECTS UNLIMITED, INC. IS PROHIBITED.
©2003, Projects Unlimited Inc.



REVISION HISTORY

LTR	DESCRIPTION	DATE	APPROVED
-	RELEASED FROM ENGINEERING	5/5/2006	
A	REVISED TO INVENTOR 3-D DRAWING TEMPLATE	4/29/2010	B.R.

A (5 : 1)



DETAIL "B"



NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS.
2. SPECIFICATIONS SUBJECT TO CHANGE OR WITHDRAWAL WITHOUT NOTICE.
3. THIS PART IS RoHS 2002/95/EC COMPLIANT.

UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN MILLIMETERS, TOLERANCES ARE ±0.5 AND ANGLES ARE ±3°.	SIZE	Designed by	Date	Checked by	Date	Approved by	Date	Drawn Date			
		J.D.	5/5/2006	E.P.	5/5/2006	B.R.	5/5/2006	4/30/2010			
	A3	 pui audio a projects unlimited company			SMT-0825-S-2-R						
					Transducer (Electro-Mech)					Edition	Sheet
										-	1 / 1
SMT-0825-S-2-R.idw											



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[PUI Audio:](#)

[SMT-0825-S-2-R](#)