



3541 Stop Eight Road • Dayton, Ohio 45414

## SMT-1341-T-2-R 12.5 x 12.5mm Transducer




### Product Overview

- Top-firing piezo-electric transducer designed for 1 to 25 Vp-p
- Small footprint and ultra-thin 2.5mm height for use in modern devices
- 4,100 Hz resonant frequency for device localization
- Designed for reflow soldering with a lead-free reflow profile



RoHS COMPLIANT





**pui  
audio**™ inc  
a projects unlimited company


## SMT-1341-T-2-R 12.5 x 12.5mm Transducer

### Mechanical and Environment Testing


Test Description	Test Condition
High Temperature	120°C with random humidity for 240 hours
Low Temperature	-40°C with random humidity for 240 hours
Humidity	40°C ( $\pm 2^\circ\text{C}$ ) with 90% to 95% relative humidity for 240 hours
Vibration	1.52 mm movement modulated at 10-55 Hz in 3 directions for 6 hours total
Shock Test	100 m/s <sup>2</sup> force on three axis, 3 cycles
Temperature Cycle Test	-40°C to 105°C, five 90 minute cycles

After testing, part shall rest for 2 hours and then be tested for a clean, pure tone.


### Recommended Reflow Profile



### Frequency Response and SPL Measurement Setup



### Recommended Land Pattern





# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[PUI Audio:](#)

[SMT-1341-T-2-R](#)