





NOTES:

- ROHS COMPLIANT
- HEADER: PHENOLIC WITH FLAMMABILITY RATING UL 94V-0 OR BETTER.
- 3. STORAGE TEMPERATURE: -50°C TO +125°C
- 4. COMPLIANCE TO J-STD:
 - A. J-STD-002: SOLDERABILITY AT 245°C REFLOW PROFILE
 - B. J-STD-020: LEVEL 1, NO MOISTURE SENSITIVE
 - C. J-STD-075: R7, 245°C MAXIMUM THROUGH REFLOW SOLDER
- 5. TO ORDER TAPE & REEL PACKAGING ADD A "T" SUFFIX TO THE PART NUMBER(i.e HX1259FNL BECOMES HX1259FNLT).








FINAL OUTLINE


@ Copyright, 2014. Pulse Electronics Corp. All rights reserved. Pulse confidential & proprietary. (06/17/14)


PRODUCT DESCRIPTION	TLA DRAWING	PS DRAWING	SHEET	PART NO.	DATASHEET REV.
MDL,QUAD,100D,1:1,SM,TU	HX1259FNL-10	PS-2743.001-A	1 OF 3	HX1259FNL	A














ELECTRICAL CHARACTERISTICS AT +25°C UNLESS OTHER SPECIFIED MEETS IEEE 802.3 SPECIFICATION

PARAMETER	SPECIFICATIONS							
OPERATING TEMPERATURE	−40°C ~ +85°C							
TURNS RATIO	1 : 1 ±2%							
POLARITY	PER SCHEMATIC							
	100 KHz			1-125 MHz				
INSERTION LOSS	-1.2	dB	MAX	-0.2-0.002*f ^{^1.4} dB MAX				
DETUDN LOSS 100DT	.1–	30	MHz	30-60 MHz	60-80 MHz			
RETURN LOSS, 100BT $(Z OUT = 100 OHM \pm 15\%)$	-16			-10+20*LOG ₁₀ (f/60 MHz) dB MIN	-10 dB MIN			
INDUCTANCE (OCL) (MEDIA SIDE, -40°C ~ +85°C)	350 uH MIN (MEASURED AT 100 KHz, 100 m			lz, 100 mVRMS) C BIAS				
	1 MHz			10-100 MHz				
CROSSTALK, ADJACENT CHANNELS	-50	dΒ	MIN	-55+22*LOG ₁₀ (f/10) dB MIN				
20141011 11005	2 MHz			30-200 MHz				
COMMON MODE REJECTION RATIO	-50	dB	MIN	-15+20*LOG ₁₀ (f/200) dB MIN				
DC RESISTANCE, 1/2 WINDING	.65 OHMS MAX							
DC RESISTANCE IMBALANCE	±.065 OHMS MAX (CENTER TAP SYMMETRY)							
INPUT — OUTPUT ISOLATION	1500 VRMS MIN @ 60 SECONDS			CONDS				

NOTE: f IS FREQUENCY IN MHz.


SCHEMATIC


© Copyright, 2014. Pulse Electronics Corp. All rights reserved. Pulse confidential & proprietary. (06/17/14)

PRODUCT DESCRIPTION	TLA DRAWING	PS DRAWING	SHEET	PART NO.	DATASHEET REV.
MDL,QUAD,100D,1:1,SM,TU	HX1259FNL-10	PS-2743.001-A	2 OF 3	HX1259FNL	A









.225 [5.72]

.004 \(\triangle \)

40 SURFBCES

.010 [0.25] - .049 [1.25] - .049 [1.25] - .040 0°-8°

DIMENSIONS ARE IN INCHES [MILLIMETERS] WITH THE FOLLOWING TOLERANCES: [MILLIMETERS] ARE FOR REFERENCE ONLY. .XX= \pm .01 [\pm 0.25] .XXX= \pm .005 [\pm 0.13]

@ Copyright, 2014. Pulse Electronics Corp. All rights reserved. Pulse confidential & proprietary. (06/17/14)

PRODUCT DESCRIPTION	TLA DRAWING	PS DRAWING	SHEET	PART NO.	DATASHEET REV.
MDL,QUAD,100D,1:1,SM,TU	HX1259FNL-10	PS-2743.001-A	3 OF 3	HX1259FNL	A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pulse:

HX1259FNLT HX1259FNL