[illegible]

NOTES:

1. VOLTAGE RATING : 125 VAC RMS.
2. CURRENT RATING : 1.5 AMP.
3. CONTACT RESISTANCE : 50 MILLIOHMS MAX.
4. INSULATION RESISTANCE: 1000 MEGOHMS MIN @ 500 VDC.
5. DIELECTRIC STRENGTH : 1000 VAC RMS 60HZ, 1MIN.


|                               |   |                           |          |
|-------------------------------|---|---------------------------|----------|
| 1. HOUSING MATERIAL           | : | NYLON +30%.G.F(FR52)      | UL94V-0. |
| 2. INSERT                     | : | NYLON+30%.G.F(FR52)       | UL94V-0  |
| 3. CONTACT MATERIAL           | : | PHOSPHOR BRONZE t=0.35mm. |          |
| 4. PLATING                    | : | GOLD PLATING OVER NICKEL. |          |
| 5. OPERATING LIFE             | : | 750 CYCLES MIN.           |          |
| 6.PCB RETENTION PRE-SOLDER    | : | 1 LB MIN.                 |          |
| 7. PCB RETENTION POST-SOLDER: | : | 10 LBS MIN.               |          |

1. STORAGE : -40°C TO +85°C.
2. OPERATION: -40°C TO +85°C.
3. WAVE SOLDERING TEMPERATURE: 255~265° (5~10 SECONDS)


FCC PART 68, SUBPART F.

ROHS PART NUMBER: E5908-~~XVAXXX~~-L

—Gold Thickness: 1- 3u" 2- 6u" 3-15u"  
4-30u" 5-50u"

- 10-FRONT PEG 4.57, W/O "FRE" &"UL" LOGO   
15- FRONT PEG 4.57, W/"FRE" &"UL" LOGO 

**Section 1**



THIRD ANGLE PROJECTION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pulse:

[E5908-5VA155-L](#)