

C2267NL


1:1 IMPEDANCE RATIO TRANSFORMER

SURFACE MOUNT

ROHS-COMPLIANT

NOTES: UNLESS OTHERWISE SPECIFIED

1. OPERATING TEMPERATURE: 0°C TO +70°C
2. STORAGE TEMPERATURE: -20°C TO +125°C
3. JEDEC MOISTURE: LEVEL 1.
4. DIMENSIONS ARE IN INCHES WITH THE FOLLOWING TOLERANCE:
.XX= ± 0.01
.XXX= ± 0.005
5. OPTIONAL TAPE & REEL PACKAGING CAN BE ORDERED BY ADDING A "T" SUFFIX TO THE PART NUMBER. ie: C2267NLT
6. ROHS COMPLIANT




SCHEMATIC

ELECTRICAL SPECIFICATIONS: @ 25°C

PARAMETER	SPECIFICATIONS
URNS RATIO	1:1 $\pm 5\%$
POLARITY	PER SCHEMATIC
PRIMARY INDUCTANCE	15 μ H MIN @100KHZ, .20 VRMS
LEAKAGE INDUCTANCE	.12 μ H MAX @100KHZ, 20 mVRMS
C _{ww}	5 PF MAX @100KHZ, 20 mVRMS
DC RESISTANCE	.20 OHMS MAX
HIPOT	1500 VRMS MIN @ 60 SECONDS

MECHANICAL SPECIFICATIONS:



© Copyright, 2012. Pulse Engineering, Inc. All rights reserved. Drawing specifications subject to change without notice. Date (06/08/12)

PULSE CONFIDENTIAL
&
PROPRIETARY

PRODUCT SPECIFICATION:

XFMR,FC,DUAL,1:1,15UH,OH,SM

DWG. NO./ PART NO.

C2267NL

SHEET:

1

REV.

M11

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pulse:

[C2267NLT](#) [C2267FNLT](#)