

**Features:**

- Motor: Brushless DC
- Motor Protection: IC
- Bearing Type: Two Ball or Hydro Dynamic
- Connection: UL 1061 AWG 26, 320mm Wire Leads
- Frame Material: Plastic UL94V-0
- Impeller Material: Plastic UL94V-0
- Operating Temp:
 - Two Ball: -10°C~70°C
 - Hydro Dynamic: -10°C~70°C
- Life Expectancy:
 - Two Ball: 70,000 Hours (40°C)
 - Hydro Dynamic: 40,000 Hours (40°C)

**Fan-S Division**



Model No.	Volt.	Current	Power	Rated Speed	Maximum AirFlow		Maximum Static Pressure		Noise Level	Weight
	(VDC)	(A)	(W)	(rpm)	(CMM)	(CFM)	(InAq)	(mmAq)	(dB/A)	(g)
FAD1-06025B * LW1 ** -A	5	0.20	1.00	2500	0.361	12.782	0.080	2.032	18.9	62.0
FAD1-06025B * MW1 ** -A	5	0.35	1.75	3500	0.506	17.900	0.152	3.860	28.1	62.0
FAD1-06025B * HW1 ** -A	5	0.35	1.75	4500	0.661	23.366	0.252	6.400	33.1	62.0
FAD1-06025C * LW1 ** -A	12	0.10	1.20	2500	0.361	12.782	0.080	2.032	18.9	62.0
FAD1-06025C * MW1 ** -A	12	0.13	1.56	3500	0.506	17.900	0.152	3.860	28.1	62.0
FAD1-06025C * HW1 ** -A	12	0.23	2.76	4500	0.661	23.366	0.252	6.400	33.1	62.0
FAD1-06025C * JW1 ** -A	12	0.23	2.76	5000	0.740	26.178	0.298	7.569	38.4	62.0
FAD1-06025CBKW1 ** -A	12	0.32	3.84	6000	0.895	31.643	0.445	11.303	42.7	62.0
FAD1-06025D * LW1 ** -A	24	0.06	0.72	2500	0.361	12.782	0.080	2.032	18.9	62.0
FAD1-06025D * MW1 ** -A	24	0.09	2.16	3500	0.506	17.900	0.152	3.860	28.1	62.0
FAD1-06025D * HW1 ** -A	24	0.12	2.88	4500	0.661	23.366	0.252	6.400	33.1	62.0
FAD1-06025D * JW1 ** -A	24	0.12	2.88	5000	0.740	26.178	0.298	7.569	38.4	62.0

* Indicates "B" (Ball Bearing), or "H" (Hydro Dynamic)

** Indicates "2" (No Special Function), "3" (Alarm), "4" (Speed Sensor), "9" (PWM), or "B" (PWM + Speed Sensor)

Part Number Example: FAD1-06025CBMW12-A (Ball Bearing fan with no Special Function)

Noise is measured at the distance of one (1) meter from the axis of intake.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Qualtek:

[FAD1-06025BBLW12-A](#) [FAD1-06025BBHW12-A](#) [FAD1-06025CBLW12-A](#) [FAD1-06025CBHW12-A](#) [FAD1-06025CBMW12-A](#) [FAD1-06025BBMW12-A](#)