


**Features:**


- Universal AC input/ Full Range
- Energy Efficiency Level VI
- Output Protections: SCP/OC
- No Load Power Consumption <0.1W
- 1 Year Warranty




| Model                         | QFWB-65-5                                          | QFWB-65-5.9 | QFWB-65-7 | QFWB-65-8 | QFWB-65-9 | QFWB-65-10 | QFWB-65-12 | QFWB-65-15 | QFWB-65-18 | QFWB-65-24 | QFWB-65-36 | QFWB-65-48 |
|-------------------------------|----------------------------------------------------|-------------|-----------|-----------|-----------|------------|------------|------------|------------|------------|------------|------------|
| Output Characteristics        |                                                    |             |           |           |           |            |            |            |            |            |            |            |
| DC Output                     | 5V                                                 | 5.9V        | 7V        | 8V        | 9V        | 10V        | 12V        | 15V        | 18V        | 24V        | 36V        | 48V        |
| Rated Current                 | 7.00A                                              | 7.00A       | 6.00A     | 6.00A     | 6.00A     | 6.00A      | 5.00A      | 4.30A      | 3.60A      | 2.70A      | 1.80A      | 1.35A      |
| Ripple and Noise              | 200mV Max                                          |             |           |           |           |            |            |            |            |            |            |            |
| Load Regulation (Typ.)        | ±5%                                                |             |           |           |           |            |            |            |            |            |            |            |
| Turn On Delay                 | 3S Max                                             |             |           |           |           |            |            |            |            |            |            |            |
| Hold-up Time (Typ.)           | 10mS @ Rated Load 115VAC, 20mS @ Rated Load 230VAC |             |           |           |           |            |            |            |            |            |            |            |
| Output Protection             | Short Circuit, Over Current                        |             |           |           |           |            |            |            |            |            |            |            |
| Ferrite Core                  | No                                                 |             |           |           |           |            |            |            |            |            |            |            |
| Input Characteristics         |                                                    |             |           |           |           |            |            |            |            |            |            |            |
| Voltage Range                 | 100VAC~240VAC                                      |             |           |           |           |            |            |            |            |            |            |            |
| Frequency Range               | 50Hz-60Hz                                          |             |           |           |           |            |            |            |            |            |            |            |
| Efficiency                    | DoE Level VI, Energy Star                          |             |           |           |           |            |            |            |            |            |            |            |
| AC Current (max)              | 1.5A                                               |             |           |           |           |            |            |            |            |            |            |            |
| Input Protection              | Internal Primary Current Fuse, Inrush Limiting     |             |           |           |           |            |            |            |            |            |            |            |
| Leakage Current               | 0.25mA @ 264VAC/50Hz                               |             |           |           |           |            |            |            |            |            |            |            |
| Environmental Characteristics |                                                    |             |           |           |           |            |            |            |            |            |            |            |
| Operating Temperature         | 0°C~40°C                                           |             |           |           |           |            |            |            |            |            |            |            |
| Operating Relative Humidity   | 10% RH to 80% RH                                   |             |           |           |           |            |            |            |            |            |            |            |
| Storage Temperature           | -20°C~80°C, 5% RH to 95% RH                        |             |           |           |           |            |            |            |            |            |            |            |
| Topology                      | Switching Flyback                                  |             |           |           |           |            |            |            |            |            |            |            |
| Dielectric Withstand          | 3000VAC/10mA Primary-Secondary                     |             |           |           |           |            |            |            |            |            |            |            |
| EMI Conduction & Radiation    | Compliance to EN55022 Class B, FCC Part 15 Class B |             |           |           |           |            |            |            |            |            |            |            |
| Harmonic Current              | Compliance to EN61000-3-2, 3                       |             |           |           |           |            |            |            |            |            |            |            |
| EMS Immunity                  | Compliance to IEC61000-4-2, 3, 4, 5, 6, 8, 11      |             |           |           |           |            |            |            |            |            |            |            |
| Characteristics               |                                                    |             |           |           |           |            |            |            |            |            |            |            |
| MTBF                          | 50,000Hrs (25°C, Telecordia SR-332)                |             |           |           |           |            |            |            |            |            |            |            |
| Dimension (LxWxH)             | 117.3x50.3x33.5mm                                  |             |           |           |           |            |            |            |            |            |            |            |
| Weight                        | 300g                                               |             |           |           |           |            |            |            |            |            |            |            |

**PART NUMBER SYSTEM**

## MECHANICAL SPECIFICATIONS



## DERATING CURVE



UNIT: mm

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Qualtek:

[QFWB-65-24-US01](#) [QFWB-65-12-US01](#)