

N-Channel Super Junction Power MOSFET III

General Description

The series of devices use advanced trench gate super junction technology and design to provide excellent $R_{DS(ON)}$ with low gate charge. This super junction MOSFET fits the industry's AC-DC SMPS requirements for PFC, AC/DC power conversion, and industrial power applications.

Features

- New technology for high voltage device
- Low on-resistance and low conduction losses
- Small package
- Ultra Low Gate Charge cause lower driving requirements
- 100% Avalanche Tested
- OHS compliant


Application

- Power factor correction (PFC)
- Switched mode power supplies(SMPS)
- Uninterruptible Power Supply (UPS)


Package Marking And Ordering Information

Device	Device Package	Marking
RM21N650T2	TO-220	21N650
RM21N650TI	TO-220F	21N650

V_{DS}	650	V
$R_{DS(ON) MAX}$	180	mΩ
I_D	21	A



Schematic diagram



TO-220

TO-220F

Table 1. Absolute Maximum Ratings ($T_c=25^\circ\text{C}$)

Parameter	Symbol	RM21N650T2	RM21N650TI	Unit
Drain-Source Voltage ($V_{GS}=0V$)	V_{DS}	650		V
Gate-Source Voltage ($V_{DS}=0V$), AC ($f>1\text{ Hz}$)	V_{GS}	± 30		V
Continuous Drain Current at $T_c=25^\circ\text{C}$	$I_{D(DC)}$	21	21*	A
Continuous Drain Current at $T_c=100^\circ\text{C}$	$I_{D(DC)}$	13.2	13.2*	A
Pulsed drain current ^(Note 1)	$I_{DM(pluse)}$	84	84*	A
Maximum Power Dissipation($T_c=25^\circ\text{C}$)	P_D	188	33.8	W
Derate above 25°C		1.5	0.27	W/ $^\circ\text{C}$
Single pulse avalanche energy ^(Note 2)	E_{AS}	441		mJ
Avalanche current ^(Note 1)	I_{AR}	10.5		A
Repetitive Avalanche energy , t_{AR} limited by T_{Jmax} ^(Note 1)	E_{AR}	0.7		mJ

Parameter	Symbol	RM21N650T2	RM21N650TI	Unit
Drain Source voltage slope, $V_{DS} \leq 480\text{ V}$,	dv/dt	50		V/ns
Reverse diode dv/dt , $V_{DS} \leq 480\text{ V}$, $I_{SD} < I_D$	dv/dt	15		V/ns
Operating Junction and Storage Temperature Range	T_J, T_{STG}	-55...+150		°C

* limited by maximum junction temperature

Table 2. Thermal Characteristic

Parameter	Symbol	RM21N650T2	RM21N650TI	Unit
Thermal Resistance, Junction-to-Case (Maximum)	R_{thJC}	0.66	3.69	°C /W
Thermal Resistance, Junction-to-Ambient (Maximum)	R_{thJA}	62.5	80	°C /W

Table 3. Electrical Characteristics (TA=25°C unless otherwise noted)

Parameter	Symbol	Condition	Min	Typ	Max	Unit
On/off states						
Drain-Source Breakdown Voltage	BV _{DSS}	V _{GS} =0V I _D =250μA	650			V
Zero Gate Voltage Drain Current(Tc=25℃)	I _{DSS}	V _{DS} =650V, V _{GS} =0V		0.05	1	μA
Zero Gate Voltage Drain Current(Tc=125℃)	I _{DSS}	V _{DS} =650V, V _{GS} =0V			100	μA
Gate-Body Leakage Current	I _{GSS}	V _{GS} =±20V, V _{DS} =0V			±100	nA
Gate Threshold Voltage	V _{GS(th)}	V _{DS} =V _{GS} , I _D =250μA	3	3.5	4	V
Drain-Source On-State Resistance	R _{DS(ON)}	V _{GS} =10V, I _D =10.5A		150	180	mΩ
Dynamic Characteristics						
Forward Transconductance	g _{FS}	V _{DS} = 20V, I _D = 10.5A		16		S
Input Capacitance	C _{iss}	V _{DS} =50V, V _{GS} =0V, F=1.0MHz		2600		PF
Output Capacitance	C _{oss}			95		PF
Reverse Transfer Capacitance	C _{rss}			7		PF
Total Gate Charge	Q _g	V _{DS} =480V, I _D =21A, V _{GS} =10V		48		nC
Gate-Source Charge	Q _{gs}			17		nC
Gate-Drain Charge	Q _{gd}			14		nC
Switching times						
Turn-on Delay Time	t _{d(on)}	V _{DD} =380V, I _D =11A, R _G =4Ω, V _{GS} =10V		11		nS
Turn-on Rise Time	t _r			6		nS
Turn-Off Delay Time	t _{d(off)}			61		nS
Turn-Off Fall Time	t _f			4.5		nS
Source- Drain Diode Characteristics						
Source-drain current(Body Diode)	I _{SD}	T _C =25℃			21	A
Pulsed Source-drain current(Body Diode)	I _{SDM}				84	A
Forward on voltage	V _{SD}	T _j =25℃, I _{SD} =21A, V _{GS} =0V		0.9	1.3	V
Reverse Recovery Time	t _{rr}	T _j =25℃, I _F =21A, di/dt=100A/μs		310		nS
Reverse Recovery Charge	Q _{rr}			5		uC
Peak Reverse Recovery Current	I _{rrm}			28		A

Notes 1.Repetitive Rating: Pulse width limited by maximum junction temperature

2. $T_J=25^\circ C, V_{DD}=50V, V_G=10V, R_G=25\Omega$

RATING AND CHARACTERISTICS CURVES (RM21N650T2,RM21N650TI)

Figure1. Safe operating area for TO-220




Figure2. Safe operating area for TO-220F




Figure3. Source-Drain Diode Forward Voltage




Figure4. Output characteristics




Figure5. Transfer characteristics





Figure6. Static drain-source on resistance



RATING AND CHARACTERISTICS CURVES (RM21N650T2,RM21N650TI)

Figure7. $R_{DS(ON)}$ vs Junction Temperature




Figure8. BV_{DSS} vs Junction Temperature




Figure9. Maximum I_D vs Junction Temperature




Figure10. Transient Thermal Impedance for TO-220







Figure11. Transient Thermal Impedance for TO-220F





Test circuit



1) Gate charge test circuit & Waveform



2) Switch Time Test Circuit:



3) Unclamped Inductive Switching Test Circuit & Waveforms





RECTRON

Marking on the body



← Rectron Logo

2 1 N 6 5 0 ← Part No.

1 6 X X

Year – Code


(Y:16-----2016

17-----2017.....)

Week – code


(WW:01~52)

TO-220-3L-C Package Information



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	4.400	4.600	0.173	0.181
A1	2.250	2.550	0.089	0.100
b	0.710	0.910	0.028	0.036
b1	1.170	1.370	0.046	0.054
c	0.330	0.650	0.013	0.026
c1	1.200	1.400	0.047	0.055
D	9.910	10.250	0.390	0.404
E	8.9500	9.750	0.352	0.384
E1	12.650	12.950	0.498	0.510
e	2.540 TYP.		0.100 TYP.	
e1	4.980	5.180	0.196	0.204
F	2.650	2.950	0.104	0.116
H	7.900	8.100	0.311	0.319
h	0.000	0.300	0.000	0.012
L	12.900	13.400	0.508	0.528
L1	2.850	3.250	0.112	0.128
V	7.500 REF.		0.295 REF.	
Φ	3.400	3.800	0.134	0.150

TO-220F Package Information



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	4.500	4.900	0.177	0.193
A1	2.340	2.740	0.092	0.108
A2	2.560	2.960	0.101	0.117
b1	0.700	0.900	0.028	0.035
b2	1.180	1.580	0.046	0.062
c	0.400	0.600	0.016	0.024
D	9.960	10.360	0.392	0.408
E	15.670	15.970	0.617	0.629
E1	6.500	6.900	0.256	0.272
E2	15.500	16.100	0.610	0.634
e	2.540 TYP		0.100 TYP	
Ø	3.080	3.280	0.121	0.129
L	12.640	13.240	0.498	0.521
L1	3.030	3.430	0.119	0.135

DISCLAIMER NOTICE

Rectron Inc reserves the right to make changes without notice to any product specification herein, to make corrections, modifications, enhancements or other changes. Rectron Inc or anyone on its behalf assumes no responsibility or liability for any errors or inaccuracies. Data sheet specifications and its information contained are intended to provide a product description only. "Typical" parameters which may be included on RECTRON data sheets and/ or specifications can and do vary in different applications and actual performance may vary over time. Rectron Inc does not assume any liability arising out of the application or use of any product or circuit.

Rectron products are not designed, intended or authorized for use in medical, life-saving implant or other applications intended for life-sustaining or other related applications where a failure or malfunction of component or circuitry may directly or indirectly cause injury or threaten a life without expressed written approval of Rectron Inc. Customers using or selling Rectron components for use in such applications do so at their own risk and shall agree to fully indemnify Rectron Inc and its subsidiaries harmless against all claims, damages and expenditures.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Rectron:](#)

[RM21N650T2](#) [RM21N650T1](#)