


GPP TRANSIENT VOLTAGE SUPPRESSOR 1500 WATT PEAK POWER 1.0 WATT STEADY STATE

FEATURES

- * Plastic package has underwriters laboratory
- * Glass passivated chip construction
- * 1500 watt surage capability at 1ms
- * Excellent clamping capability
- * Low zener impedance
- * Fast response time
- * P/N suffix V means Halogen-free
- * P/N suffix V means AEC-Q101 qualified, eg:TFMCJ5.0V



Ratings at 25 °C ambient temperature unless otherwise specified.

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS Ratings at 25 °C ambient temperature unless otherwise specified.

DEVICES FOR BIPOLAR APPLICATIONS

For Bidirectional use C or CA suffix for types TFMCJ5.0 thru TFMCJ170

Electrical characteristics apply in both direction

MAXIMUM RATINGS (At TA = 25°C unless otherwise noted)

RATINGS	SYMBOL	VALUE	UNITS
Peak Power Dissipation with a 10/1000uS (Note 1,2, Fig.1)	Рррм	Minimum 1500	Watts
Peak Pulse Current with a 10/1000uS waveform (Note 1, Fig.3)	Іррм	SEE TABLE 1	Amps
Steady State Power Dissipation at TL = 75°C (Note 2)	Рм(av)	5.0	Watts
Peak Forward Surge Current 8.3mS single half sine-wave superimposed on rated load (JEDEC method) (Note 2,3) unidirectional only	IFSM	200	Amps
Typical Current Squarad Time	l ² t	166	A ² Sec
Maximum Instantaneous Forward Voltage at 100A for unidirectional only (Note 3,5)	Vf	SEE NOTE 3,5	Volts
Operating and Storage Temperature Range	TJ, TSTG	-55 to + 150	٥C

NOTES : 1. Non-repetitive current pulse, per Fig.3 and derated above $T_A = 25^{\circ}C$ per Fig.2.

2. Mounted on 0.31 X 0.31" (8.0 X 8.0mm) copper pad to each terminal.


3. Lead temperature at TL = 25°C

4. Measured on 8.3mS single half sine-wave duty cycle = 4 pules per minute maximum.

5. VF = 3.5V on TFMCJ-5.0 thru TFMCJ-90 devices and VF = 5.0V on TFMCJ-100 thru TFMCJ-170 devices.

2018-04 REV:C

RATING AND CHARACTERISTIC CURVES (TFMCJ5.0 THRU TFMCJ170CA)



RECTRON

TRANSIENT VOLTAGE SUPPRESSORS

1500W SERIES TVS DIODES \angle DO-214AB (CASE 4) 1500W

	Breakdown Voltage			Reverse	Maximum	Maximum	Maximum	
ТҮРЕ	VBR (Volts)		@IT	Stand off Voltage Vwm	Reverse Leakage at VWM	Peak Pulse Current IPPM	Clamping Voltage at IPPM	
	MIN.	MAX.	(mA)	(Volts)	ID(uA)	(Amps)	VC (Volts)	
TFMCJ5.0	6.40	7.30	10	5.0	1000	164.0	9.6	
TFMCJ5.0A	6.40	7.00	10	5.0	1000	171.0	9.2	
TFMCJ6.0	6.67	8.15	10	6.0	1000	138.0	11.4	
TFMCJ6.0A	6.67	7.37	10	6.0	1000	152.0	10.3	
TFMCJ6.5	7.22	8.82	10	6.5	500.0	128.0	12.3	
TFMCJ6.5A	7.22	7.98	10	6.5	500.0	140.0	11.2	
TFMCJ7.0	7.78	9.51	10	7.0	200.0	118.0	13.3	
TFMCJ7.0A	7.78	8.86	10	7.0	200.0	131.0	12.0	
TFMCJ7.5	8.33	10.2	1.0	7.5	100.0	110.0	14.3	
TFMCJ7.5A	8.33	9.21	1.0	7.5	100.0	122.0	12.9	
TFMCJ8.0	8.89	10.9	1.0	8.0	50.0	105.0	15.0	
TFMCJ8.0A	8.89	9.83	1.0	8.0	50.0	115.0	13.6	
TFMCJ8.5	9.44	11.5	1.0	8.5	25	99.0	15.9	
TFMCJ8.5A	9.44	10.4	1.0	8.5	25	109.0	14.4	
TFMCJ9.0	10.0	12.2	1.0	9.0	10	93.0	16.9	
TFMCJ9.0A	10.0	15.0	1.0	9.0	10	102.0	15.4	
TFMCJ10	11.1	13.6	1.0	10.0	5.0	83.0	18.8	
TFMCJ10A	11.1	12.3	1.0	10.0	5.0	92.0	17.0	
TFMCJ11	12.2	14.9	1.0	11.0	5.0	78.0	20.1	
TFMCJ11A	12.2	13.5	1.0	11.0	5.0	86.0	18.2	
TFMCJ12	13.3	16.3	1.0	12.0	5.0	71.0	22.0	
TFMCJ12A	13.3	14.7	1.0	12.0	5.0	79.0	19.9	
TFMCJ13	14.4	17.6	1.0	13.0	5.0	66.0	23.8	
TFMCJ13A	14.4	15.9	1.0	13.0	5.0	73.0	21.5	
TFMCJ14	15.6	19.1	1.0	14.0	5.0	61.0	25.8	
TFMCJ14A	15.6	17.2	1.0	14.0	5.0	67.0	23.2	
TFMCJ15	16.7	20.4	1.0	15.0	5.0	58.0	26.9	
TFMCJ15A	16.7	18.5	1.0	15.0	5.0	64.0	24.4	
TFMCJ16	17.8	21.8	1.0	16.0	5.0	54.0	28.8	
TFMCJ16A	17.8	19.7	1.0	16.0	5.0	60.0	26.0	
TFMCJ17	18.9	23.1	1.0	17.0	5.0	51.0	30.5	
TFMCJ17A	18.9	20.9	1.0	17.0	5.0	57.0	27.6	
TFMCJ18	20.0	24.2	1.0	18.0	5.0	48.0	32.2	
TFMCJ18A	20.0	22.1	1.0	18.0	5.0	53.0	29.2	
TFMCJ20	22.2	27.1	1.0	20.0	5.0	43.0	35.8	
TFMCJ20A	22.2	24.5	1.0	20.0	5.0	48.0	32.4	
TFMCJ22	24.4	29.8	1.0	22.0	5.0	39.0	39.4	
TFMCJ22A	24.4	26.9	1.0	22.0	5.0	44.0	35.5	
TFMCJ24	26.7	32.6	1.0	24.0	5.0	36.0	43.0	
TFMCJ24A	26.7	29.5	1.0	24.0	5.0	40.0	38.9	
TFMCJ26	28.9	35.3	1.0	26.0	5.0	33.0	46.6	
TFMCJ26A	28.9	31.9	1.0	26.0	5.0	37.0	42.1	
TFMCJ28	31.1	38.0	1.0	28.0	5.0	31.0	50.1	
TFMCJ28A	31.1	34.4	1.0	28.0	5.0	34.0	45.4	
TFMCJ30	33.3	40.7	1.0	30.0	5.0	29.0	53.5	
TFMCJ30A	33.3	36.8	1.0	30.0	5.0	32.0	48.4	
TFMCJ33	36.7	44.9	1.0	33.0	5.0	26.0	59.0	
TFMCJ33A	36.7	40.6	1.0	33.0	5.0	29.0	53.3	
TFMCJ36	40.0	48.9	1.0	36.0	5.0	24.0	64.3	
TFMCJ36A	40.0	44.2	1.0	36.0	5.0	27.0	58.1	



TRANSIENT VOLTAGE SUPPRESSORS

1500W SERIES TVS DIODES \angle DO-214AB (CASE 4) 1500W

	Breakdown Voltage			Reverse	Maximum	Maximum	Maximum	
ТҮРЕ	VBR (Volts)		@IT	Stand off Voltage	Reverse Leakage	Peak Pulse Current	Clamping Voltage	
	MIN.	MAX.	(mA)	Vwм (Volts)	at Vwм ID(uA)	IPPM (Amps)	at IPPM VC (Volts)	
TFMCJ40	44.4	54.3	1.0	40	5.0	22.0	71.4	
TFMCJ40A	44.4	49.1	1.0	40	5.0	24.0	64.5	
TFMCJ43	47.8	58.4	1.0	43	5.0	20.0	76.7	
TFMCJ43A	47.8	52.8	1.0	43	5.0	22.0	69.4	
TFMCJ45	50.0	61.1	1.0	45	5.0	19.0	80.3	
TFMCJ45A	50.0	55.3	1.0	45	5.0	21.0	72.7	
TFMCJ48	53.3	65.1	1.0	48	5.0	18.0	85.5	
TFMCJ48A	53.3	58.9	1.0	48	5.0	20.0	77.4	
TFMCJ51	56.7	69.3	1.0	51	5.0	17.0	91.1	
TFMCJ51A	56.7	62.7	1.0	51	5.0	19.0	82.4	
TFMCJ54	60.0	73.3	1.0	54	5.0	16.0	96.3	
TFMCJ54A	60.0	66.3	1.0	54	5.0	18.0	87.1	
TFMCJ58	64.4	78.7	1.0	58	5.0	15.0	103	
TFMCJ58A	64.4	71.2	1.0	58	5.0	16.0	93.6	
TFMCJ60	66.7	81.5	1.0	60	5.0	14.0	107	
TFMCJ60A	66.7	73.7	1.0	60	5.0	16.0	96.8	
TFMCJ64	71.1	86.9	1.0	64	5.0	13.8	114	
TFMCJ64A	71.1	78.6	1.0	64	5.0	15.0	103	
TFMCJ70	77.8	95.1	1.0	70	5.0	12.6	125	
TFMCJ70A	77.8	86.0	1.0	70	5.0	13.9	113	
TFMCJ75	83.3	102	1.0	75	5.0	11.7	134	
TFMCJ75A	83.3	92.1	1.0	75	5.0	13.0	121	
TFMCJ78	86.7	106	1.0	78	5.0	11.3	139	
TFMCJ78A	86.7	95.8	1.0	78	5.0	12.5	126	
TFMCJ85	94.4	115	1.0	85	5.0	10.4	151	
TFMCJ85A	94.4	104	1.0	85	5.0	11.5	137	
TFMCJ90	100	122	1.0	90	5.0	9.8	160	
TFMCJ90A	100	111	1.0	90	5.0	10.7	146	
TFMCJ100	110	136	1.0	100	5.0	8.8	179	
TFMCJ100A	110	123	1.0	100	5.0	9.7	162	
TFMCJ110	122	149	1.0	110	5.0	8.0	196	
TFMCJ110A	122	135	1.0	110	5.0	8.9	177	
TFMCJ120	133	163	1.0	120	5.0	7.3	214	
TFMCJ120A	133	147	1.0	120	5.0	8.1	193	
TFMCJ130	144	176	1.0	130	5.0	6.8	231	
TFMCJ130A	144	159	1.0	130	5.0	7.5	209	
TFMCJ150	167	204	1.0	150	5.0	5.8	268	
TFMCJ150A	167	185	1.0	150	5.0	6.4	243	
TFMCJ160	178	218	1.0	160	5.0	5.4	287	
TFMCJ160A	178	197	1.0	160	5.0	6.0	259	
TFMCJ170	189	231	1.0	170	5.0	5.1	304	
TFMCJ170A	189	209	1.0	170	5.0	5.7	275	

NOTES : 1. V_{BR} measured after I_T applied for 300ms. I_T = square pluse or equivalent.

2. For bidirectional use C or CA suffixs for all types (ex. TFMCJ5.0C, TFMCJ170CA) electrical characteristics apply in both directions.

RECTRON ------


3. For bidirectional types having V_{WM} of 10 volts and less, the I_{D} limit is doubled.

PACKAGING OF DIODE AND BRIDGE RECTIFIERS

REEL PACK

PACKAGE	PACKING CODE	EA PER REEL	EA PER INNER BOX	COMPONENT SPACE (mm)	TAPE SPACE (mm)	REEL DIA (mm)	CARTON SIZE (mm)	EA PER CARTON	GROSS WEIGHT(Kg)
SMC	-T	500	1,500			178	390*205*310	12,000	6.65
SMC	-W	3,000	3,000			330	360*355*360	24,000	11.50

Marking Description



CRECTRON -

DISCLAIMER NOTICE

Rectron Inc reserves the right to make changes without notice to any product specification herein, to make corrections, modifications, enhancements or other changes. Rectron Inc or anyone on its behalf assumes no responsibility or liability for any errors or inaccuracies. Data sheet specifications and its information contained are intended to provide a product description only. "Typical" parameters which may be included on RECTRON data sheets and/ or specifications can and do vary in different applications and actual performance may vary over time. Rectron Inc does not assume any liability arising out of the application or use of any product or circuit.

Rectron products are not designed, intended or authorized for use in medical, life-saving implant or other applications intended for life-sustaining or other related applications where a failure or malfunction of component or circuitry may directly or indirectly cause injury or threaten a life without expressed written approval of Rectron Inc. Customers using or selling Rectron components for use in such applications do so at their own risk and shall agree to fully indemnify Rectron Inc and its subsidiaries harmless against all claims, damages and expenditures.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Rectron:

SMCJ33ASMCJ11A-WSMCJ51A-WSMCJ14A-WSMCJ33CA-WSMCJ9.0A-WSMCJ20CA-WSMCJ40A-WSMCJ30CA-WSMCJ48CA-WSMCJ75A-WSMCJ24A-WSMCJ16CA-WSMCJ13CA-WSMCJ43CA-WSMCJ60A-WWSMCJ17CA-WSMCJ64CA-WSMCJ22CA-WSMCJ6.0A-WSMCJ6.0CA-WSMCJ90CA-WSMCJ170A-WSMCJ12A-WSMCJ7.5A-WSMCJ130A-WSMCJ5.0CA-WSMCJ100A-WSMCJ7.5CA-WSMCJ70CA-WSMCJ6.5CA-WSMCJ160A-WSMCJ33A-WSMCJ20A-WSMCJ8.5A-WSMCJ8.0CA-WSMCJ26A-WWSMCJ13A-WSMCJ120A-WSMCJ40CA-WSMCJ15CA-WSMCJ54A-WSMCJ8.5CA-WSMCJ130CA-WSMCJ160CA-WSMCJ15CA-WSMCJ114CA-WSMCJ18.5CA-WSMCJ130CA-WSMCJ160CA-WSMCJ120CA-WSMCJ1120A-WSMCJ120A-WSMCJ130CA-WSMCJ160CA-WSMCJ120CA-WSMCJ114CA-WSMCJ48A-WSMCJ130CA-WSMCJ160CA-WSMCJ120CA-WSMCJ110CA-WSMCJ43A-WSMCJ150A-WSMCJ18A-WSMCJ28A-WSMCJ16.5A-WSMCJ170CA-WSMCJ150A-WSMCJ110A-WSMCJ7.0CA-WSMCJ100CA-WSMCJ16A-WSMCJ158CA-WSMCJ758A-WSMCJ17A-WSMCJ54CA-WSMCJ26CA-WSMCJ18CA-WSMCJ110CA-WSMCJ15A-WSMCJ90A-WWSMCJ58A-WSMCJ36A-WSMCJ26CA-WSMCJ18CA-WSMCJ100A-WSMCJ15A-WSMCJ45A-WWSMCJ58A-WSMCJ36A-WSMCJ26CA-WSMCJ18CA-WSMCJ10CA-WSMCJ15A-WSMCJ45A-WWSMCJ58A-WSMCJ36