




SMLP34 series

PICOLED™-RGB

SMLP34RGB1W

4pin type
 1010(0404)
 1.0×1.0mm(t=0.2mm)

Features

- The smallest 3 color type LED in the world* PICOLED™-RGB
- 4pin type
- Low height contributes to the improvement of color mixture




* Investigated Aug. 2010

Specifications


Part No.	Chip Structure	Emitting Color	Absolute Maximum Ratings (Ta=25℃)						Electrical and Optical Characteristics (Ta=25℃)										
			Power Dissipation Pd (mW)	Forward Current IF (mA)	Peak Forward Current IFP (mA)	Reverse Voltage VR (V)	Operating Temperature Topr (℃)	Storage Temperature Tstg (℃)	Forward Voltage VF Typ. (V)	IF (mA)	Reverse Current IR Max. (μA)	VR (V)	Dominant Wavelength λD Min.*2 Typ. (nm) Max.*2 (nm)			IF (mA)	Luminous Intensity Iv Min. (mcd) Typ. (mcd) IF (mA)		
 SMLP34RGB1W	InGaN	Blue							3.0				465	470	475		9	18	
		Green	-	20	100*1	5	-30 to +85	-40 to +100	3.1	5	100	5	520	527	535	5	22	45	5
	AlGaInP on GaAs	Red							2.1				620	624	629		14	28	
 SMLP34RGB2W	AlGaInP	Red							2.2				619	624	629		14	35	
	InGaN	Green	-	20	100*1	5	-40 to +85	-40 to +100	3.3	5	10	5	520	527	535	5	56	110	5
		Blue								3.2				465	470	475		28	45

* 1:Duty ≤ 1/20, 1kHz * 2:Reference


Dimensions



Recommended Solder Pattern





Viewing Angle





* PICOLED™ is ROHM's pending trademark.

Electrical Characteristics Curves



Forward Current-Forward Voltage





Luminous Intensity-Atmosphere Temperature



Luminous Intensity-Forward Current



Derating



Rank Reference of Brightness


SMLP34RGB1W

(Ta=25°C, If=5mA)															
	Package size (mm)	Height (mm)	Luminous intensity (mcd)	A	B	C	D	E	F	G	H	J	K	L	M
			Emitted Color												
			Blue	9 to 18	18 to 36	9 to 18	18 to 36	9 to 18	18 to 36	9 to 18	18 to 36	9 to 18	18 to 36	9 to 18	18 to 36
			Green	22 to 36		36 to 56		56 to 90		22 to 36		36 to 56		56 to 90	
Mini-mold Chip LEDs	1010 1510	0.2	Red	14 to 28						28 to 56					

SMLP34RGB2W

(Ta=25°C, If=5mA)															
	Package size (mm)	Height (mm)	Luminous intensity (mcd)	A	B	C	D	E	F	G	H	J	K	L	M
			Emitted Color												
			Blue	28 to 56	56 to 110	28 to 56	56 to 110	28 to 56	56 to 110	28 to 56	56 to 110	28 to 56	56 to 110	28 to 56	56 to 110
			Green	56 to 90		90 to 140		140 to 220		56 to 90		90 to 140		140 to 220	
Mini-mold Chip LEDs	1010 1510	0.2	Red	14 to 28						28 to 56					

Part No. Explanation



* Concerning the Brightness rank

- Please refer to the rank chart above for luminous intensity classification.
- Part name is individual for each rank.
- When shipped as sample, the part name will be a representative part name.

General products are free of ranks. Please contact sales if rank appointment is needed.

Packing Specification

ROHM LED products are being shipped with desiccant (silica gel) concluded in moisture-proof bags.

Pasting the moisture sensitive label on the outer surface of the moisture-proof bags or enclosing the humidity indication card inside the bag is available upon request.

Please contact the nearest sales office or distributor if necessary.

Notes

No copying or reproduction of this document, in part or in whole, is permitted without the consent of ROHM Co.,Ltd.

The content specified herein is subject to change for improvement without notice.

The content specified herein is for the purpose of introducing ROHM's products (hereinafter "Products"). If you wish to use any such Product, please be sure to refer to the specifications, which can be obtained from ROHM upon request.

Examples of application circuits, circuit constants and any other information contained herein illustrate the standard usage and operations of the Products. The peripheral conditions must be taken into account when designing circuits for mass production.

Great care was taken in ensuring the accuracy of the information specified in this document. However, should you incur any damage arising from any inaccuracy or misprint of such information, ROHM shall bear no responsibility for such damage.

The technical information specified herein is intended only to show the typical functions of and examples of application circuits for the Products. ROHM does not grant you, explicitly or implicitly, any license to use or exercise intellectual property or other rights held by ROHM and other parties. ROHM shall bear no responsibility whatsoever for any dispute arising from the use of such technical information.

The Products specified in this document are intended to be used with general-use electronic equipment or devices (such as audio visual equipment, office-automation equipment, communication devices, electronic appliances and amusement devices).

The Products specified in this document are not designed to be radiation tolerant.

While ROHM always makes efforts to enhance the quality and reliability of its Products, a Product may fail or malfunction for a variety of reasons.

Please be sure to implement in your equipment using the Products safety measures to guard against the possibility of physical injury, fire or any other damage caused in the event of the failure of any Product, such as derating, redundancy, fire control and fail-safe designs. ROHM shall bear no responsibility whatsoever for your use of any Product outside of the prescribed scope or not in accordance with the instruction manual.

The Products are not designed or manufactured to be used with any equipment, device or system which requires an extremely high level of reliability the failure or malfunction of which may result in a direct threat to human life or create a risk of human injury (such as a medical instrument, transportation equipment, aerospace machinery, nuclear-reactor controller, fuel-controller or other safety device). ROHM shall bear no responsibility in any way for use of any of the Products for the above special purposes. If a Product is intended to be used for any such special purpose, please contact a ROHM sales representative before purchasing.

If you intend to export or ship overseas any Product or technology specified herein that may be controlled under the Foreign Exchange and the Foreign Trade Law, you will be required to obtain a license or permit under the Law.



Thank you for your accessing to ROHM product informations.
More detail product informations and catalogs are available, please contact us.

ROHM Customer Support System

<http://www.rohm.com/contact/>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ROHM Semiconductor:](#)

[SMLP34RGB1W3](#)