0.1(T-1) Circular Type High Brightness Type
 Viewing Angle 201/2 : 40°>

SLR343 **** Series Pressu



Emitting Color	White
Material	InGaN on SiC
Emitting Surface Dimension(mm)	
Part No.	SLR343WBD2PT

note) "-" will be taken out for emitting color B/E series.


Absolute Maximum Ratings (Ta=25°C)

Part No.	Emitting color	Power dissipation Po (mW)	Forward current I⊧ (mA)	Peak forward current IFP (mA)	Reverse voltage VR (V)	Operating temperature Topr (°C)	Storage temperature Tstg (°C)
SLR343WBD2PT	White	126	30		5	-20 to+80	-30 to +100

Electrical Optical Characteristics (Ta=25°C)


Part No.	Resin	volt	vard age 'F	Rev curi I			romatio ordinat		Br	rightne: Iv	SS	
		Тур. (V)	lF (mA)	Max. (µA)	Vr (V)	x	у	lF (mA)	Min. (mcd)	Typ. (mcd)	lF (mA)	
SLR343WBD2PT	Phosphor included	3.2	20	100	5	0.31	0.31	20	1500	3300	20	

Chromaticity Diagram




0.283 0.244 0.280 0.312 0.302 0.338 0.330 0.30 0.299 0.269 0.302 0.338 0.330 0.370 0.354 0.280 0.312 0.313 0.286 0.330 0.307 0.36 0.260 0.272 0.299 0.269 ±0.02


Recommended Pad Layout




Packaging Specifications (Unit:mm)



Dimensions (Unit:mm)




Directivity (Typ.)






Note) The design and specifications are subject to change without prior notice. Before ordering or using, please check the latest technical specifications.

Electrical Characteristic Curves




Relative Luminous Intensity - Forward Current




SLR343WBD2PT

Ratio of Maximum Tolerable Peak Current - Pulse Duration



Derating



- SLR343WBD2PT

SLR343WBD2PT

	Notes
	ng or reproduction of this document, in part or in whole, is permitted without the f ROHM Co.,Ltd.
The conte	nt specified herein is subject to change for improvement without notice.
"Products	nt specified herein is for the purpose of introducing ROHM's products (hereinafte "). If you wish to use any such Product, please be sure to refer to the specifications be obtained from ROHM upon request.
illustrate t	of application circuits, circuit constants and any other information contained herein he standard usage and operations of the Products. The peripheral conditions mus nto account when designing circuits for mass production.
However,	e was taken in ensuring the accuracy of the information specified in this document should you incur any damage arising from any inaccuracy or misprint of sucl n, ROHM shall bear no responsibility for such damage.
examples implicitly, other part	ical information specified herein is intended only to show the typical functions of and of application circuits for the Products. ROHM does not grant you, explicitly o any license to use or exercise intellectual property or other rights held by ROHM and ies. ROHM shall bear no responsibility whatsoever for any dispute arising from the h technical information.
equipmen	icts specified in this document are intended to be used with general-use electronic t or devices (such as audio visual equipment, office-automation equipment, commu evices, electronic appliances and amusement devices).
The Produ	cts specified in this document are not designed to be radiation tolerant.
	HM always makes efforts to enhance the quality and reliability of its Products, a ay fail or malfunction for a variety of reasons.
against th failure of a shall bear	sure to implement in your equipment using the Products safety measures to guard e possibility of physical injury, fire or any other damage caused in the event of the any Product, such as derating, redundancy, fire control and fail-safe designs. ROHM no responsibility whatsoever for your use of any Product outside of the prescribed not in accordance with the instruction manual.
system wi may result instrument fuel-contro any of the	acts are not designed or manufactured to be used with any equipment, device on hich requires an extremely high level of reliability the failure or malfunction of which t in a direct threat to human life or create a risk of human injury (such as a medica t, transportation equipment, aerospace machinery, nuclear-reactor controller oller or other safety device). ROHM shall bear no responsibility in any way for use o Products for the above special purposes. If a Product is intended to be used for an ial purpose, please contact a ROHM sales representative before purchasing.
be control	nd to export or ship overseas any Product or technology specified herein that may led under the Foreign Exchange and the Foreign Trade Law, you will be required to cense or permit under the Law.



Thank you for your accessing to ROHM product informations. More detail product informations and catalogs are available, please contact us.

ROHM Customer Support System

http://www.rohm.com/contact/

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ROHM Semiconductor:

<u>SLR343WBD2PT21</u> <u>SLR343WBD2PT51</u> <u>SLR343WBD2PT31</u> <u>SLR343WBD2PT54</u> <u>SLR343WBD2PT53</u> SLR343WBD2PT52 SLR343WBD2PT2 SLR343WBD2PT1 SLR343WBD2PT5