

# 4-channel BTL driver for CD players and CD-ROMs

## BA5970FP

The BA5970FP is a 4-channel BTL driver developed to drive CD player motors and actuators. The driver input stage contains an operational amplifier, supports a variety of input formats, and allows simple configuration of a filter.

### ●Applications

CD players, CD-ROM

### ●Features

- 1) 4-channel BTL driver.
- 2) Wide dynamic range (4V when  $PREV_{CC} = 8V$ ,  $POWV_{CC} = 5V$ , and  $R_L = 8\Omega$ ).
- 3) Internal thermal shutdown circuit.
- 4) Driver gain is adjustable with externally connected resistor.
- 5) Independent power supplies  $PREV_{CC}$ ,  $POWV_{CC}$  (for channels 1 and 2), and  $POWV_{CC}$  (for channels 3 and 4), and low voltage operation for a highly efficient drive.
- 6) Independent mute pins for channels 1 and 2 and channels 3 and 4.
- 7) Perfect for compact applications with the use of the HSOP28-pin power package.

### ●Absolute maximum ratings ( $T_a = 25^\circ\text{C}$ )


Parameter	Symbol	Limits	Unit
Power supply voltage	$PREV_{CC}$ , $POWV_{CC}$	13.5	V
Power dissipation	$P_d$	1.7* <sup>1</sup>	W
Operating temperature	$T_{opr}$	$-35 \sim +85$	$^\circ\text{C}$
Storage temperature	$T_{stg}$	$-55 \sim +150$	$^\circ\text{C}$

\*1 When mounted on a 70mm × 70mm × 1.6mm glass epoxy board with copper foil coverage of less than 3%.  
Reduced by 13.6mW for each increase in  $T_a$  of  $1^\circ\text{C}$  over  $25^\circ\text{C}$ .

### ●Recommended operating conditions ( $T_a = 25^\circ\text{C}$ )

Parameter	Symbol	Limits	Unit
Power supply voltage	$PREV_{CC}$	4.5~13.2	V
	$POWV_{CC}$	4.5~ $PREV_{CC}$	V

## ● Block diagram




## ● Pin descriptions

Pin No.	Pin name	Function	Pin No.	Pin name	Function
1	BIAS IN	Bias amplifier input	15	VO4 (+)	Driver channel 4 positive output
2	OPIN1 (+)	Channel 1 pre-amplifier non-inverse input	16	VO4 (-)	Driver channel 4 negative output
3	OPIN1 (-)	Channel 1 pre-amplifier inverse input	17	VO3 (+)	Driver channel 3 positive output
4	OPOUT1	Channel 1 pre-amplifier output	18	VO3 (-)	Driver channel 3 negative output
5	OPIN2 (+)	Channel 2 pre-amplifier non-inverse input	19	POWV <sub>cc</sub>	POWV <sub>cc</sub> (channels 3 and 4)
6	OPIN2 (-)	Channel 2 pre-amplifier inverse input	20	MUTE2	Mute control for channels 3 and 4
7	OPOUT2	Channel 2 pre-amplifier output pin	21	GND	GND
8	GND	GND	22	OPOUT3	Channel 3 pre-amplifier output
9	MUTE1	Mute control for channels 1 and 2	23	OPIN3 (-)	Channel 3 pre-amplifier inverse input
10	POWV <sub>cc</sub>	POWV <sub>cc</sub> (channels 1 and 2)	24	OPIN3 (+)	Channel 3 pre-amplifier non-inverse input
11	VO2 (-)	Driver channel 2 negative output	25	OPOUT4	Channel 4 pre-amplifier output
12	VO2 (+)	Driver channel 2 positive output	26	OPIN4 (-)	Channel 4 pre-amplifier inverse input
13	VO1 (-)	Driver channel 1 negative output	27	OPIN4 (+)	Channel 4 pre-amplifier non-inverse input
14	VO1 (+)	Driver channel 1 positive output	28	PREV <sub>cc</sub>	PREV <sub>cc</sub>


Note : Positive output and negative output are the polarities with respect to the input.  
(For example, if pin 4 voltage is high, then pin 14 voltage becomes high.)

## ● Input / output circuits


## Pre-amplifier input




## Pre-amplifier output (driver input)




## Bias



## Driver output



## Mute



- Electrical characteristics (unless otherwise noted, Ta = 25°C, PREV<sub>CC</sub> = 8V, POWV<sub>CC1</sub> = 5V, POWV<sub>CC2</sub> = 8V, BIAS = 2.5V, R<sub>L</sub> = 8Ω)

Parameter	Symbol	Min.	Typ.	Max.	Unit	Conditions
Quiescent current	I <sub>Q1</sub>	—	20	30	mA	Input open
〈Driver〉						
Output offset voltage 1	V <sub>OO1</sub>	−70	0	70	mV	channel 1, 2
Output offset voltage 2	V <sub>OO2</sub>	−90	0	90	mV	channel 3, 4
Maximum output amplitude 1	V <sub>OM1</sub>	3.6	4.0	—	V	channel 1, 2, V <sub>IN</sub> = ±2.0V
Maximum output amplitude 2	V <sub>OM2</sub>	5.4	6.0	—	V	channel 3, 4, V <sub>IN</sub> = ±2.0V
Voltage gain 1	GV <sub>C1</sub>	10	12	14	dB	V <sub>IN</sub> = ±0.5V
Voltage gain 2	GV <sub>C2</sub>	16	18	20	dB	V <sub>IN</sub> = ±0.5V
Mute on voltage	V <sub>MON</sub>	2.0	—	—	V	
Mute off voltage	V <sub>MOFF</sub>	—	—	0.5	V	
〈Pre-stage operational amplifier〉						
Common-mode input voltage	V <sub>ICM</sub>	−0.3	—	6.8	mV	
Offset voltage	V <sub>OFOF</sub>	−6	0	6	mV	
Input bias current	V <sub>BOP</sub>	—	—	300	nA	
Output high level voltage	V <sub>OHOP</sub>	6.9	7.35	—	V	
Output low level voltage	V <sub>OLOP</sub>	—	0.75	1.1	V	
Output drive current sink	I <sub>SI</sub>	1	—	—	mA	50Ω at V <sub>CC</sub>
Output drive current source	I <sub>SO</sub>	1	—	—	mA	50Ω at GND
Slew rate	SR <sub>OP</sub>	—	1	—	V/μs	100kHz rectangular wave, 2V <sub>P-P</sub> output

◎Not designed for radiation resistance.

## ● Measurement circuit




Fig.1

● Measurement circuit switch table

(1) Driver block (OPB → 1, NF → 1, OPRL → 1)

Symbol	Switch	Input		Remarks	Measurement point
	RL	V <sub>IN</sub>	VM1, 2		
IQ	OFF	2.5V	0V	—	IQ
VOO1	ON	2.5V	0.5V	—	VO (channel 1, 2)
VOO2	ON	2.5V	0.5V	—	VO (channel 3, 4)
VOOM1	ON	±2.0V	0.5V	V <sub>IN</sub> =0.5V and 4.5V	VO (channel 1, 2)
VOOM2	ON	±2.0V	0.5V	V <sub>IN</sub> =0.5V and 4.5V	VO (channel 3, 4)
GVC1	ON	±0.5V	0.5V	V <sub>IN</sub> =2.0V and 3.0V	VO (channel 1, 2)
GVC2	ON	±0.5V	0.5V	V <sub>IN</sub> =2.0V and 3.0V	VO (channel 3, 4)
VMTON	ON	3.0V	2.0V	Verify output voltage is muted	VO
VMTOFF	ON	3.0V	0.5V	Verify output voltage is muted	VO

(2) Pre-stage operational amplifier block (VN1 = VM2 = 0V, RL → OFF)

Symbol	Switch			Input	Remarks	Measurement point
	OPB	NF	OPRL	V <sub>IN</sub>		
VOFOP	1	1	1	2.5V	—	VIOF
VBOP	3	2	1	2.5V	—	VBOP/1MΩ
VOHOP	1	1	1	5V	—	VOOP
VOLOP	1	1	1	0V	—	VOOP
ISI	1	1	3	2.5V	—	VDROP/50Ω
ISO	1	1	2	2.5V	—	VDROP/50Ω
SROP	2	1	1	±1V	100kHz rectangular wave, 2.5±1V input	VOOP

## ●Application example




Fig.2

### ● Operation notes

- (1) The BA5970FP contains a thermal shutdown circuit. When the chip temperature reaches 175°C (Typ.), the output current is muted. If the chip temperature then drops below 150°C (Typ.), then the mute is released.
- (2) By having the mute pin voltage pulled up to 2.0V or greater, you can mute the output current. For normal conditions, have mute pin open or at 0.5V or below. (Pin 9 mutes channels 1 and 2, and pin 20 mutes channels 3 and 4.)
- (3) If the voltage of the bias pin (pin 1) drops below 1.4V (Typ.), outputs are muted. For normal conditions, have the voltage above 1.7V.
- (4) If the power supply voltage drops below 3.8V (Typ.),

internal circuits turns off. If the power supply voltage then rises to 4.0V (Typ.), the circuits turn on.

- (5) If the voltage of the thermal shutdown, mute ON, or bias pin drops, or if the power supply voltage drops, the mute is activated; however, in these situations, only the drivers are muted. Also, the output pin voltage becomes the internal bias voltage (approx.  $V_{CC}/2$  for channels 1 and 2, and  $(V_{CC}-V_F)/2$  for channels 3 and 4).
- (6) Connect a bypass capacitor (approx. 0.1μF) between the bases of the power supply pins of this IC.
- (7) Even though the radiation fins are connected to ground within the package, be sure to also connect them to a ground externally as well.

### ● Electrical characteristic curves










Fig.3 Thermal derating curve

Fig.4 I/O characteristics  
(channels 1 and 2)Fig.5 I/O characteristics  
(channels 3 and 4)Fig.6 Power supply voltage vs.  
output offset voltageFig.7 Power supply voltage vs.  
operational amplifier offset voltageFig.8 Operational amplifier  
I/O characteristics



●External dimensions (Units: mm)



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ROHM Semiconductor:](#)

[BA5970FP-E2](#)