

Crimpers and Wire Prep Tools

Automotive Aftermarket and Heavy Duty

**SARGENT
QUALITY
TOOLS**

A Member of the Oetiker Group

AUTOMOTIVE




METRI-PACK, MICRO-PACK & HEAT SHRINK CONNECTORS



Circular Contact Crimp Tool

3104 DSCT




- Ratcheted crimp tool
- Crimp circular contacts



Metri-Pack Unsealed Crimp Tool

3184 LCT




- Core & insulation wings crimped in single motion
- Spring loaded clip holds and positions terminal
- Same as GM 12070947 (J-39848)



Metri-Pack Packard Style Crimp Tool

3185 CT




- Crimps Metri-Pack 480 & 630 sealed connectors
- 10TRK12 AWG
- Same as GM 12071687



Metri-Pack 280 Unsealed Crimp Tool

3187 CT




- Five cavities
- 22TRK12 AWG
- Same as GM 12085271 (J-38125-7)



Metri-Pack Sealed & Unsealed

3188 CT




- Crimps Core and Insulation
- Ratcheted for positive performance
- Built-in locator to orient contacts
- Same as GM 12039500 (J-38123)



Metri-Pack 150 & 280 Sealed Terminal Crimp Tool

3189 CT

- Same as GM 12155975
- 20-14 AWG
- Core and seal are crimped in two separate motions








Heat Shrink Splices & "C" Clips Ratchet Crimp Tool

3190 CT



- Same as GM 12085115 (J-38125-8)
- Ratcheted crimp tool
- Crimp heat shrink splices and "C" clips



Metri-Pack Packard Style Crimp Tool

3303 64CT




- Crimps Micro-Pack .64, 100 & 100W and GT 630 terminals
- Crimps core and/or insulation wings depending on terminal
- Included in Repair Kit 3330 TRK



Metri-Pack, Micro-Pack & GT Unsealed Crimp Tool

3305 MPCT



- Crimps Metri-Pack 150, 280, 480, & 630; Micro-Pack .64 & 100 and GT 150, 280 & 630 terminals
- Included in Repair Kit 3330 TRK



Metri-Pack, Micro-Pack & GT Sealed Crimp Tool

3306 MPCT

- Crimps Metri-Pack 150, 280, 480, & 630; Micro-Pack .64 & 100 and GT 150, 280 & 630 terminals
- Included in Repair Kit 3330 TRK



Automotive Terminal Repair Crimp Tool Kit

3330 TRK

Five terminal crimping tools cover

- Weather Pack – 20, 18, 16, 14, 12 & 10 AWG terminals
- Micro-Pack – .64, 100 & 100W and GT 150, 280 & 630 terminals
- Metri-Pack – 150, 280, 480 & 630

Includes

- 3301 WPCT – Weather Pack Terminals 20–14 AWG Crimp Tool
- 3302 WPCT – Weather Pack Terminals 12–10 AWG Crimp Tool
- 3303 64CT – Micro-Pack .64mm Contact Crimp Tool
- 3305 MPCT – Metri-Pack Unsealed Crimp Tool
- 3306 MPCT – Metri-Pack Sealed Crimp Tool
- Terminal Repair Manual, 32 Pages:
 - OEM terminal number/tool number matrix
 - Detailed terminal replacement and quality check procedures




AUTOMOTIVE TERMINAL REPAIR CRIMP TOOLS



Open Barrel Contact Crimp Tool

1026 CT




- Crimps a wide variety of open barrel contacts in small size wire ranges
- “Oval” type insulation crimps are produced in two cavities: A 20–16 AWG and B 30–22 AWG
- “B” type conductor crimps are produced in three cavities: C 18–16 AWG, D 22–20 AWG and E 30–24 AWG



B Type Medium Size Wire Crimp Tool

1028 CT




- Crimps a wide variety of open barrel contacts in medium size wire ranges.
- Insulation crimps are “B” type and are produced in two cavities: A 18–14 AWG and B 24–20 AWG
- Conductor crimps are “B” type and are produced in three cavities: C 16–14 AWG, D 20–18 AWG and E 24–22 AWG



Heat Shrink Sealed Splices

3104 DSCT




- Same as GM 12085115
- Ratcheted crimp tool
- Crimp Metri-Pack unsealed terminals and heat shrink splices



Circular Contacts Ratchet Crimp Tool

3107 DTCT




- Three cavities: 20, 16 & 12 AWG
- Ratcheted for positive performance



Ratchet Conductor Crimp Tool

3120 CT




- Three cavities: Red 22–16 AWG, Blue 16–14 AWG & Yellow 12–10 AWG
- Crimps conductor portion of insulated terminals



Unsealed 20–14 AWG, One Step Crimp Tool

3182 LCT

- Same as GM 08913440
- Crimps Packard 56, 58 & 59 Series connectors
- Core & insulation wings crimped in single motion
- Spring loaded clip holds and positions terminal








Circular Contacts Super Crimp Tool

2186 CT

- Crimps commercial grade solid circular pins and sockets in three cavities: 20, 16 & 12 AWG
- Fine blanked high carbon steel construction dies
- Jaws accept other dies for additional applications



Multi Function Electrical Crimper, Stripper, Wire & Bolt Cutter

1020 CT

Cutters




- Two cutters
- Anvil type nose cutter conveniently up front for tight spaces
- Scissor type cutter located behind the pivot point minimizes distortion when cutting stranded wire

Crimps

- Crimps automotive "F" type ignition terminals 7-8 mm size in one cavity
- Crimps conductor portion of insulated terminals and splices.
- Crimps Red 22-16 AWG, Blue 16-14 AWG & Yellow 12-10 AWG
- Crimps non-insulated terminals and splices

Strips




- Precision ground scissor type wire stripper provides a clean nick free strip on 8 AWG solid to 22 AWG stranded
- Cavities are marked by wire sizes and "solid" or "stranded"



Power Crimp Tool

6220 CT

- Crimps conductor portion of insulated and non-insulated terminals
- Four cavities: 8, 6, 4 & 2 AWG
- Cavities are identified by wire size and product type






AUTOMOTIVE WEATHER PACK CRIMP TOOLS



Weather Pack Terminals Crimp Tool, short handle

3138 CT



- 20–18 AWG & 16–14 AWG
- Ratcheted for positive performance



Weather Pack Two Cavity Crimp Tool

3181 CT




- 20–10 AWG
- Spring loaded
- Same as GM06285847



Weather Pack Terminals Crimp Tool, long handle

3183 LCT




- 20–14 AWG & 16–14 AWG
- Includes locator to orient contacts
- Same as GM12014254 (J-38852)



Weather Pack Terminals 20–14 AWG Crimp Tool

3186 CT



- Five Cavities
- Ratcheted for positive performance
- Same as GM12085270 (J-38125-6)



Weather Pack Terminals 20–14 AWG Crimp Tool

3301 WPCT




- One tool for crimping terminal core wings and seal wings
- Separate cavities for precise crimping (14–16 AWG & 18–20 AWG)
- Included in Terminal Repair Kit 3330 TRK



Weather Pack Terminals 12–10 AWG Crimp Tool

3302 WPCT

- One tool for crimping terminal core wings and seal wings
- Separate cavities for precise crimping (10 AWG & 12 AWG)
- Included in Terminal Repair Kit 3330 TRK



GM TOOL NUMBER	SARGENT® TOOL NUMBER
GM06285847	3181 CT
GM08913440	3182 LCT
GM12014254	3183 LCT
GM12039500	3188 CT
GM12070947	3184 LCT

GM TOOL NUMBER	SARGENT® TOOL NUMBER
GM12071687	3185 CT
GM12085115	3190 CT
GM12085270	3186 CT
GM12085271	3187 CT
GM12155975	3189 CT

AUTOMOTIVE BATTERY LUG CRIMP TOOLS




- Precision machined crimping cavities
- No dies to move or switch
- 19" tool length for maximum leverage and mechanical advantage
- Ergonomic cushioned grips remain comfortable
- Easy to adjust
- Designed to exceed tensile strength requirements



B-Crimp Tool for Open Barrel Terminals

6225 CT

- Positive contact and excellent durability
- OEM style crimp – superior mechanical strength and electrical conductivity




NEST	OPEN BARREL CONNECTORS
A	2-6 AWG Conductor
B	2-6 AWG Insulation
C	4-6 AWG Conductor, 1-2 AWG Insulation



Crimp Tool for Cast Heavy Duty Tube Lugs & Terminals and Standard Wall Lugs

6226 CT

- Square shaped crimp for positive electrical contact and excellent pull resistance
- Dual cavity




NEST	CAST BATTERY TERMINAL/LUG	HEAVY WALL TERMINAL/LUG	STANDARD WALL LUG
250 MCM	4/0 AWG	4/0 AWG	
4/0		3/0 AWG	4/0 AWG



Crimp Tool for Cast Heavy Duty Tube Lugs & Terminals and Standard Wall Lugs

6227 CT

- Square shaped crimp for positive electrical contact and excellent pull resistance
- Triple cavity




NEST	CAST BATTERY TERMINAL/LUG	HEAVY WALL TERMINAL/LUG	STANDARD WALL LUG
4/0	3/0, 2/0	3/0, 2/0	3/0 AWG
2/0		1, 1-2, 2	2/0, 1/0
1/0	1-2		1 AWG



Crimp Tool for Cast Heavy Duty Tube Lugs & Terminals and Standard Wall Lugs

6228 CT

- Square shaped crimp for positive electrical contact and excellent pull resistance
- Four cavity



NEST	CAST BATTERY TERMINAL/LUG	HEAVY WALL TERMINAL/LUG	STANDARD WALL LUG
1/0			1 AWG
2		4,6 AWG	2 AWG
4	4,6 AWG		4,6,8 AWG
6		8 AWG	

Oetiker Tool Corp.

30 East Industrial Rd.

Branford, CT 06405 USA

Phone +01 203 488 8665

Fax +01 203 488 6497

Email orders.us.branford@oetiker.com

www.sargenttools.com

www.oetiker.com



Connecting Technology

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Sargent Tools:

[3138CT](#) [3120CT](#) [3187CT](#)