

Ultra Compact and Versatile Filtered Power Entry Module



- Single stage filter
- Ultra compact design
- Rated currents up to 10 A
- dual-fuse holder
- Fuses Ø5x20 mm
- 2-pole rocker switch
- Good attenuation performance
- Faston or spring cage terminals



Performance indicators

Attenuation performance



Technical Specifications

Maximum continuous operating voltage	250 VAC, 50/60 Hz			
Rated currents	1 to 10 A @ 40°C max			
Operating frequency	DC to 400 Hz			
Leakage current	Standard: <500 uA at 250 VAC/50 Hz Medical: <5 uA at 250 VAC/50 Hz			
High potential test voltage	P -> PE 2000 VAC for 2 sec (standard types) P -> PE 2500 VAC for 2 sec (B types) P -> N 760 VAC for 2 sec			
Design corresponding to	UL 1283, CSA 22.2 No. 8 1986, EN 60939, EN 60950, EN 60601-1, UL 544, EN 60320			
Flammability corresponding to	UL 94 V-2 or better			
Temperature range (operation and storage)	- 25°C to +85°C (25/85/21)			
Protection category	IP 40 according to IEC 60529 (front side)			
MTBF @ 40°C/230 V (Mil-HB-217F)	>1,000,000 hours			
Switch ratings				
Rocker switch	2-pole, dark not illuminated, Marking I - 0			
USA (UL) and Canada (C-UL)	10 A, 125 VAC; 10 A, 250 VAC; 1/3 HP			
Europe (ENEC)	10 A (4 A), 250 VAC**			
Mechanical life	50,000 cycles			
Electrical specifications	Inrush current 82 A 6,000 on-off operations according to UL 1054 10,000 on-off operations according to ENEC			
Fuse holder	2 fuses (Ø5 x 20 mm) max. 250 V (certified to IEC 60127-6)			

- 10 A version is 8 A UL and CSA approved
- Value in () relates to the inductive current charge: $\cos \gamma = 0.65$

Approvals & Compliances









(CQC except HI-types; Patent US 20110227692/US 8766761: CN ZL201080069589.0)

Choosing FN 9280/90 product line brings you the rapid availability of a standard filter associated with the necessary safety acceptances and a high attenuation performance. For higher attenuation performance the FN 9290 family with a dual stage filter and identical panel cut-out can be used.

Standard IEC connector filters are a practical solution to pass EMI system approval in a short time. A wide selection of amperage ratings, mounting possibilities and also filters for medical applications are designed to offer you the best solution.

Features and Benefits


- Good conducted attenuation performance, based on chokes with high saturation resistance and excellent thermal behavior
- Deep-drawn iron-sheet housing for best possible shielding against magnetic fields
- Rear/front flange mounting or snap-in versions
- Dual and additional spare fuse holder
- 2-pole rocker switch
- Faston or spring cage terminals
- FN 928X B versions comply with the requirements of 1MOP acc. to IEC/EN 60601-1
- All versions according IEC/EN 62368-1

Typical Applications


- Portable electrical and electronic equipment
- Consumer goods
- EDP and office equipment
- Single-phase and switch-mode power supplies
- Test and measurement equipment
- Medical electrical devices (MD) and In-Vitro-Diagnostics (IVD) equipment
- Audio/Video, information and communication technologies

Typical electrical schematic

FN 9280 Standard types (B types without Cy)



FN 9280 E types (B types without Cy)




Filter Selection Table

Filter*	Rated current	Leakage current**	Inc	ductance	Cap	oacitance	Resistance		Output	Weight
	@ 40°C	@ 250 VAC /50 Hz	L1	L2	Cx	Су	R	со	nnections	
		(@ 120 VAC /60 Hz)								
	[A]	[mA]	[mH]	[mH]	[nF]	[nF]	[kOhm]			[g]
FN 9280-1	1	0.31 (0.18)	10.9	0	220	2.2	1000	-06	-100	101
FN 9280-2	2	0.31 (0.18)	4.4	0	220	2.2	1000	-06	-100	102
FN 9280-4	4	0.31 (0.18)	1.7	0	220	2.2	1000	-06	-100	105
FN 9280-6	6	0.31 (0.18)	0.78	0	220	2.2	1000	-06	-100	104
FN 9280-10	10	0.31 (0.18)	0.32	0	220	2.2	1000	-06	-100	106
FN 9280 B-1	1	0.00	10.9	0	220	0	1000	-06	-100	101
FN 9280 B-2	2	0.00	4.4	0	220	0	1000	-06	-100	102
FN 9280 B-4	4	0.00	1.7	0	220	0	1000	-06	-100	105
FN 9280 B-6	6	0.00	0.78	0	220	0	1000	-06	-100	104
FN 9280 B-10	10	0.00	0.32	0	220	0	1000	-06	-100	106
FN 9289-1	1	0.31 (0.18)	10.9	0	220	2.2	1000	-06	-100	101
FN 9289-2	2	0.31 (0.18)	4.4	0	220	2.2	1000	-06	-100	102
FN 9289-4	4	0.31 (0.18)	1.7	0	220	2.2	1000	-06	-100	105
FN 9289-6	6	0.31 (0.18)	0.78	0	220	2.2	1000	-06	-100	104
FN 9289-10	10	0.31 (0.18)	0.32	0	220	2.2	1000	-06	-100	106
FN 9289 B-1	1	0.00	10.9	0	220	0	1000	-06	-100	101
FN 9289 B-2	2	0.00	4.4	0	220	0	1000	-06	-100	102
FN 9289 B-4	4	0.00	1.7	0	220	0	1000	-06	-100	105
FN 9289 B-6	6	0.00	0.78	0	220	0	1000	-06	-100	104
FN 9289 B-10	10	0.00	0.32	0	220	0	1000	-06	-100	106
FN 9280 E-1	1	0.31 (0.18)	10.9	0.4	220	2.2	1000	-06	-100	135
FN 9280 E-2	2	0.31 (0.18)	4.4	0.4	220	2.2	1000	-06	-100	136
FN 9280 E-4	4	0.31 (0.18)	1.66	0.4	220	2.2	1000	-06	-100	137
FN 9280 E-6	6	0.31 (0.18)	0.78	0.4	220	2.2	1000	-06	-100	138
FN 9280 E-10	10	0.31 (0.18)	0.32	0.4	220	2.2	1000	-06	-100	139
FN 9280 EB-1	1	0.00	10.9	0.4	220	0	1000	-06	-100	135
FN 9280 EB-2	2	0.00	4.4	0.4	220	0	1000	-06	-100	136
FN 9280 EB-4	4	0.00	1.66	0.4	220	0	1000	-06	-100	137
FN 9280 EB-6	6	0.00	0.78	0.4	220	0	1000	-06	-100	138
FN 9280 EB-10	10	0.00	0.32	0.4	220	0	1000	-06	-100	139
FN 9289 E-1	1	0.31 (0.18)	10.9	0.4	220	2.2	1000	-06	-100	135
FN 9289 E-2	2	0.31 (0.18)	4.4	0.4	220	2.2	1000	-06	-100	136
FN 9289 E-4	4	0.31 (0.18)	1.66	0.4	220	2.2	1000	-06	-100	137
FN 9289 E-6	6	0.31 (0.18)	0.78	0.4	220	2.2	1000	-06	-100	138
FN 9289 E-10	10	0.31 (0.18)	0.32	0.4	220	2.2	1000	-06	-100	139
FN 9289 EB-1	1	0.00	10.9	0.4	220	0	1000	-06	-100	135
FN 9289 EB-2	2	0.00	4.4	0.4	220	0	1000	-06	-100	136
FN 9289 EB-4	4	0.00	1.66	0.4	220	0	1000	-06	-100	137
FN 9289 EB-6	6	0.00	0.78	0.4	220	0	1000	-06	-100	138
FN 9289 EB-10	10	0.00	0.32	0.4	220	0	1000	-06	-100	139

^{*} To compile a complete part number, please replace the -.. with the required output connection style (e.g. FN 9289-1-06, FN 9282-4-100) ** Maximum leakage current under normal conditions (according to IEC60939-3)

Product selector



All FN 9280/FN 9290 are equipped with a dual fuse holder with a spare fuse holder.


Note: All FN 9280/FN 9280 B/FN 9289/FN 9289 B/FN 9290/FN 9290 B/FN 9299/FN 9299 B are stock types from our distribution partners.


Order Examples:


FN 9280 B-6-100: Medical version of single stage, dual fuse EMC/EMI filter, flange set for vertical/horizontal/front/rear mounting, 6 A, spring cage terminals, from stock available.


FN 9298-6-06-30: Dual stage, dual fuse EMC/EMI filter, snap-in version, snappers for snap-in panel thickness range >2.5 to 3.5 mm, snapper on vertical side, 6 A, fast-on terminals, non-stock order type

Accessories: The 4D flanges can be ordered separately. The order number is 427532. Please note that the minimum order quantity is one box of 50 pieces. One item includes both type of flanges (vertical and horizontal).










^{*} Fuses are not included


Typical Filter Attenuation

FN 9280 Series | Per CISPR 17; A=50 Ω /50 Ω sym; B=50 Ω /50 Ω asym


1 A types




2 A types



4 – 6 A types




10 A types




FN 9280 B Series | Per CISPR 17; A=50 Ω /50 Ω sym; B=50 Ω /50 Ω asym


1 A types




2 A types



4 – 6 A types




10 A types




FN 9280 E Series | Per CISPR 17; A=50 Ω /50 Ω sym; B=50 Ω /50 Ω asym


1 A types




2 A types



4 – 6 A types




10 A types




FN 9280 EB Series | Per CISPR 17; A=50 Ω /50 Ω sym; B=50 Ω /50 Ω asym


1 A types




2 A types




4 – 6 A types





10 A types




Mechanical Data













Mechanical Data











Assembly Instructions



Terminal -100		19.2	Push the knob above
clamping range, solid wire / flex wire	0,20 mm ² –1,5 mm ² , AWG24 –AWG16	85	the terminal to insert the wire.
operating force of slider	max. 40 N		
recommended stripped length	8 mm		
		7.5	

Removal Of The Combined Switch / Fuse Holder Unit



An additional fuse mark on the switch indicates the fuses holders behind the switch. The red frame shows the outline of the removable unit.

With a simple tool like a Swiss Army knife or a screwdriver No 1 or smaller the unit (1) can be removed from the filter. On the topside (2) behind the switch there are two fuse holders for each live connection. On the bottom side (3) is a clip to carry an additional spare fuse.

Please visit www.schaffner.com to find more details on filter connectors.

Accessories

Power Cord with angled Locking System C13



- Protects appliances that are vulnerable to vibration
- Connector cannot be accidentally pulled or vibrated out of the inlet
- Space availability/constraints
- Different angles for ease of access
- Space saving
- Release locking mechanism
- Prevents accidental disconnection

Technical Data Sheet >

IL 13P IEC C13 Rewireable Angled Connectors with Locking System



- Protects appliances that are vulnerable to vibration
- Connector cannot be accidentally pulled or vibrated out of the inlet
- Space availability/constraints
- Different angles for ease of access
- Space saving
- Release locking mechanism
- Prevents accidental disconnection

Technical Data Sheet >

IL 13P IEC C13 Rewireable Connectors with Locking System



The locking system has a tensile force of typical 300N. It is recommended to use it with flange mount filters. For details refer to our Application Note "Using IEC Lock Power Cords with IEC Inlets

Schaffner power connector with IEC lock guard against accidental disconnection of all electrical appliances with an IEC inlet. No exchange or modification of the IEC inlet or IEC inlet filter system is needed. Easy retrofit .for all electronic equipments and devices

Technical Data Sheet >

Headquarters, Global Innovation and Development

Switzerland

Schaffner Holding AG

Industrie Nord Nordstrasse 11e Luterbach +41 32 681 66 26 info@schaffner.com

find your local partner within Schaffner's global network <u>schaffner.com</u>

© 2022 Schaffner Group

The content of this document has been carefully checked and understood. However, neither Schaffner nor its subsidiaries assume any liability whatsoever for any errors or inaccuracies of this document and the consequences thereof. Published specifica-tions are subject to change without notice. Product suitability for any area of application must ultimately be determined by the customer. In all cases, products must never be operated outside their published specifications. Schaffner does not guarantee the availability of all published products. This disclaimer shall be governed by substantive Swiss law and resulting disputes shall be settled by the courts at the place of business of Schaffner Holding AG. Latest publications and a complete disclaimer can be downloa-ded from the Schaffner website. All trademarks recognized.

Sales and Application Centers

Schaffner EMC Ltd. Shanghai

T20-3 C, No 565 Chuangye Road, Pudong district 201201

Shanghai

+86 2138139500

cschina@schaffner.com

Finland

Schaffner Oy

Sauvonrinne 19 H

8500

Lohja

+358 50 468 7284

finlandsales@schaffner.com

France

Schaffner EMC S.A.S.

16-20 Rue Louis Rameau

95875

Bezons

+33 1 34 34 30 60

francesales@schaffner.com

Germany

Schaffner Deutschland GmbH

Schoemperlenstrasse 12B

76185

Karlsruhe

+49 721 56910

germanysales@schaffner.com

India

Schaffner India Pvt. Ltd

Reaus World Trade Centre

WTC, 22nd Floor Unit No 2238, Brigade Gateway Campus, 26/1, Dr. Rajkumar Road

Malleshwaram (W)

560055

Bangalore

+91 8067935355 indiasales@schaffner.com

Schaffner EMC S.r.l.

Via Ticino, 30 20900

Monza (MB)

+39 039 21 41 070

italysales@schaffner.com

Japan

Schaffner EMC K.K.

ISM Sangenjaya 7F

1-32-12 Kamiuma, Setagaya-ku

154-0011

Tokyo

+81 3 5712 3650

japansales@schaffner.com

Singapore

Schaffner EMC Pte Ltd.

Blk 3015A Ubi Road 1, #05-09, Kampong Ubi Industrial Estate

Singapore

+65 63773283

singaporesales@schaffner.com

Schaffner EMC España

Calle Caléndula 93, Miniparc III, Edificio E El

Soto de Moraleja, Alcobendas

28109

Madrid

+34 917 912 900

spainsales@schaffner.com

Sweden

Schaffner EMC AB

Östermalmstrora 1

114 42

Stockholm

+46 8 5050 2425

swedensales@schaffner.com

Switzerland

Schaffner EMV AG

Industrie Nord Nordstrasse 11e

4542

Luterbach

+41 32 681 66 26

switzerlandsales@schaffner.com

Schaffner EMV Ltd.

U-Town

20 Floor-2, No 97, Section 1, XinTai 5th Road,

Xi7hi District

New Taipei City

+886 226975500

taiwansales@schaffner.com

Thailand

Schaffner EMC Co. Ltd.

Sathorn Square Tower

Room 3780, 37FL, 98 North-Sathorn Rd,

Silom, Bangrak

Banakok

+66 621056397

thailandsales@schaffner.com

United Kingdom

Schaffner Ltd.

1. Oakmede Place

Terrace Road RG42 4JF

Binfield

+44 118 9770070

uksales@schaffner.com

United States

Schaffner EMC Inc.

52 Mayfield Avenue Edison. New Jersev

+1 732 225 9533

usasales@schaffner.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Schaffner:

FN9280-10-06 FN9280-10-100 FN9280-1-06 FN9280-1-100 FN9280-2-06 FN9280-2-100 FN9280-4-06 FN9280-4-06 FN9280-4-06 FN9280B-10-100 FN9280B-10-100 FN9280B-1-100 FN9280B-1-100 FN9280B-1-100 FN9280B-1-100 FN9280B-1-100 FN9280B-1-100 FN9289-10-100 FN9289-10-100 FN9289-10-100 FN9289-10-100 FN9289-10-100 FN9289B-1-100 FN9289B-2-100 FN9289B-2-100 FN9289B-2-100 FN9289B-2-100 FN9289B-3-100 FN9280B-3-100 FN9280B-3-100