

## Connector - PV-CM-S 2,5-6 (-) - 1774687

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Photovoltaic connector, Nominal current: 40 A, Nom. voltage: 1100 V, Connection type: Spring-cage, Color: black, Can only be released using a tool



### Key Commercial Data

Packing unit	1 pc
Minimum order quantity	50 pc
Weight per Piece (excluding packing)	13.6 g
Custom tariff number	85359000
Country of origin	Germany

### Technical data

#### Dimensions

External cable diameter	5 mm ... 8 mm
-------------------------	---------------

#### Ambient conditions

Degree of protection (when plugged in)	IP66 / IP68 (2 m / 24 h)
Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (assembly)	-25 °C ... 50 °C

#### General

Design	Male connector
Tightening torque nut	2 Nm $\pm$ 0.1 Nm
Insertion force	45 N $\pm$ 10 N
Disconnect force	250 N $\pm$ 50 N
Pull-out force of cable $\geq$ disconnect force	> 330 N
Rated voltage	1100 V
Rated current (2.5 mm <sup>2</sup> )	27 A
Rated current (4.0 mm <sup>2</sup> )	40 A

# Connector - PV-CM-S 2,5-6 (-) - 1774687

## Technical data

### General

Rated current (6.0 mm <sup>2</sup> )	40 A
Protection class	II

### Material

Color	black
Insulating material	mPPE
Contact material	Cu
Contact surface material	Ag
Flammability rating according to UL 94	V0

### Connection data

Connection method	Spring-cage
Connection capacity	2.5 mm <sup>2</sup> ... 6 mm <sup>2</sup>
Contact resistance with connected conductor	0.45 mΩ
Stripping length	15 mm
Cable type	PV1-F cables

### Standards and Regulations

Flammability rating according to UL 94	V0
----------------------------------------	----

## Classifications

### eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260704
eCl@ss 7.0	27440402
eCl@ss 8.0	27440102

### ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC001753
ETIM 5.0	EC002635

### UNSPSC

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409

# Connector - PV-CM-S 2,5-6 (-) - 1774687

## Classifications

### UNSPSC

UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

## Approvals

### Approvals

#### Approvals


ETLus / VDE Zeichengenehmigung / EAC / VDE Zeichengenehmigung / ETLus / EAC / ETLus / EAC

#### Ex Approvals

#### Approvals submitted

## Approval details

ETLus	
mm <sup>2</sup> /AWG/kcmil	14
Nominal current I <sub>N</sub>	15 A
Nominal voltage U <sub>N</sub>	1000 V

VDE Zeichengenehmigung 	
mm <sup>2</sup> /AWG/kcmil	2.5
Nominal current I <sub>N</sub>	27 A
Nominal voltage U <sub>N</sub>	1100 V

EAC	
-----	--

# Connector - PV-CM-S 2,5-6 (-) - 1774687

## Approvals

VDE Zeichengenehmigung	
mm <sup>2</sup> /AWG/kcmil	2.5
Nominal current IN	27 A
Nominal voltage UN	1100 V

ETLus	
mm <sup>2</sup> /AWG/kcmil	14
Nominal current IN	15 A
Nominal voltage UN	1000 V

EAC
-----

ETLus	
mm <sup>2</sup> /AWG/kcmil	14
Nominal current IN	15 A
Nominal voltage UN	1000 V

EAC
-----

## Accessories

### Accessories

#### Protective cap

Protective cap - PV-C PROTECTION CAP - 1785430

Protective cap for SUNCLIX photovoltaic connector; transport protection for the mating face.



### Screwdriver tools

## Connector - PV-CM-S 2,5-6 (-) - 1774687

### Accessories

Screwdriver - SZF 1-0,6X3,5 - 1204517



Actuation tool, for ST terminal blocks, also suitable for use as a bladed screwdriver, size: 0.6 x 3.5 x 100 mm, 2-component grip, with non-slip grip

---

### Sealing plugs

Filler plugs - PV-C PLUG - 1775631



Protective cap for SUNCLIX photovoltaic connector, for IP67 protection in the cable gland.

---

### Stripping tool

Stripping pliers - QUICK WIREFOX 6 SC - 1207637



Stripping tool for short-circuit proof conductors, stripping range: 1.5 up to 6 mm<sup>2</sup>, wire cutting up to 6 mm<sup>2</sup> cable stopper up to 18 mm<sup>2</sup>

---

Stripping tool - WIREFOX-D SR 6-1 - 1212511




Stripping tool, for standard 2.5, 4, and 6 mm<sup>2</sup> solar cables, with 15 mm length stop, for SUNCLIX field connectors

---

### Drawings

## Connector - PV-CM-S 2,5-6 (-) - 1774687

Dimensional drawing



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1774687](#)