Product data sheet Characteristics

9013GHG2J62X

Pumptrol, 9013GH, pump or compressor switch, adjustable differential, 140 175 PSI



Main	
Range of Product	Square D Pumptrol
Pressure sensor name	9013GH
Pressure sensor size	200 psi (1378.95 kPa) 40170 psi (275.79 1172.11 kPa))
Value of setting	140175 psi
Electrical circuit type	Power circuit
Product Specific Application	Control electrically driven water pumps and air compressors
Quantity per Set	1
Type of Packing	Individual

Complementary

Pressure sensor type	Electromechanical pressure switch
Controlled fluid	Air -22257 °F (-30125 °C)) Fresh water -22257 °F (-30125 °C))
Adjustable range on rising pressure	65200 psi (448.161378.95 kPa)
Approximate adjustable differential	2040 psi (137.90275.79 kPa)
Destruction pressure	300 psi (2068.43 kPa)
Pressure actuator	Diaphragm
Pressure switch type of operation	Regulation between 2 thresholds
Scale type	Adjustable differential
Setting	Internal
Local display	Without
Contacts type and composition	2 NC, snap action, DPST-DB, Form YY
Cable entry number	3 knock-outs for 1/2" conduit UL 508
Electrical connection	Screw-clamp terminals 10 AWG Screw-clamp terminals 5.261 mm²
Fluid connection type	0.25 inch NPSF internal UL 508
Short-circuit protection	20 A cartridge fuse gG
Materials in contact with fluid	Zinc plated steel or equivalent flange Nitrile (Buna-N) or equivalent rubber diaphragm
Material	Polypropylene Cover Noryl thermoplastic resin or equivalent Cover
Operating position	Any position
Motor power kW	1.5 KW 2 hp)115 V AC, 1 phase 2.2 KW 3 hp)115 V AC, 3 phase 2.2 KW 3 hp)230 V AC, 1 phase 0.75 KW 1 hp)115 V DC 0.75 KW 1 hp)230 V DC 3.75 KW 5 hp)230 V AC, 3 phase 3.7 KW 5 hp)460 V AC, 1 phase 3.7 KW 5 hp)460 V AC, 3 phase 3.7 KW 5 hp)575 V AC, 1 phase 3.7 KW 5 hp)575 V AC, 3 phase
Electrical durability	100000 cycles 10 cyc/mn
Mechanical durability	300000 cycles
Terminal block type	4 terminals
Maximum operating rate	10 cyc/mn
[Ui] rated insulation voltage	575 V UL 508
Net Weight	2.25 lb(US) (1.02 kg)

Repeat accuracy	+/- 3 %	
Terminals description ISO n°1	L1-T1 L2-T2	
Width	4.19 in (106.43 mm)	
Height	5.4 in (137.16 mm)	
Depth	3.88 in (98.55 mm)	
Factory modification	2-way pressure release valve	

Environment

Standards	NSF ANSI 372 CE UL 508
Ambient Air Temperature for Operation	-33257 °F (-36125 °C)
Ambient Air Temperature for Storage	-33257 °F (-36125 °C)
Protective treatment	None
NEMA degree of protection	NEMA 1 UL 50
IP degree of protection	IP20 conforming to IEC 60529
Product Certifications	CSA file LR25490 UL listed file E12158

Ordering and shipping details

Category	21536-9013 G COMMERCIAL PRESSURE SWITCH
Discount Schedule	CP7G
GTIN	785901053149
Nbr. of units in pkg.	1
Package weight(Lbs)	33.44 oz (948.0 g)
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE	
Package 1 Height	4.88 in (12.4 cm)	
Package 1 width	4.29 in (10.9 cm)	
Package 1 Length	6.10 in (15.5 cm)	

Offer Sustainability

Green Premium product
WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
☑ REACh Declaration
Pro-active compliance (Product out of EU RoHS legal scope)
Yes
₫Yes
Product Environmental Profile
End Of Life Information

Contractual warranty

Warranty	18 months

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Schneider Electric: 9013GHG2J62X