



Overview

Lead time	Special Order - Call for Quoted Lead Times
-----------	--

General

Provided Equipment	Installation guide Rack Mounting brackets Safety guide Serial configuration cable
--------------------	--

Physical

Cable length	6 ft (1.83 m)
Color	Black
Depth	2.09 in (5.3 cm)
Height	99.61 in (253 cm)
Product Weight	25.00 lb(US) (11.34 kg)
Width	2.20 in (5.6 cm)

Input

Input Frequency	50/60 Hz
Line Rated Current	32 A
Plug standard	IEC 60309 60 A 3P+N+E
Number of cables	1
Input current limits	40 A
Load Capacity	23000 VA
Nominal Input Voltage	3 phase

Output

Max current draw	32 A
Number of power socket outlets	30 IEC 60320 C13 12 IEC 60320 C19
Protection Type	Circuit breaker
Output voltage	240 V

Conformance

Product Certifications	CUL Listed UL Listed VCCI Class A
Standards	EN 55022 Class A EN 55024 EN 61000-3-2 EN 61000-3-3 FCC Part 15 class A ICES-003

Environmental

Ambient Air Temperature for Operation	32...122 °F (0...50 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

Package weight(Lbs)	31.99 lb(US) (14.51 kg)
---------------------	-------------------------

Packing Units

Package 1 Height	112.99 in (287 cm)
Package 1 width	8.70 in (22.1 cm)
Package 1 Length	4.41 in (11.2 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[AP8888X892](#)