

# AP8959NA3

Rack PDU 2G, Switched,, 20A, 208V,  
(21) C13 & (3) C19, L620 Cord (BEING  
DISCONTINUED - SEE APDU9959NA3)



## Overview

Presentation	APC Switched Rack PDUs distribute reliable rack power distribution via a single input with multiple output receptacles. Individual outlet control provides advanced load management. Real-time remote monitoring and user-defined alarms help prevent potential circuit overloads that can cause accidental power loss to critical equipment. Included capabilities include individual remote on/off by outlet, power-on sequencing with time delays, outlet level grouping, and outlet grouping on multiple APC Switched Rack PDUs. Easily access, configure, and manage this metered PDU from remote locations. A network management interface provides standards-based management via Web, SNMP, and Command Line Interface. This Switched PDU from APC provides (21) IEC 60320 C13, (3) IEC 60320 C19 outlets to supply power to rack equipment. User customized alarms and an embedded memory log are included. Volts, amps, real power (kW), and energy (kWh) data is provided to support energy management. An embedded log memory to reports historic metered data. Display details current, power, and voltage measurements and offers local user access. An environmental monitoring port for external temperature/humidity monitoring is available (sensor sold separately model AP9335T or AP9335TH). Easily mount this vertical PDU in racks or enclosures. It occupies zero U of valuable rack space, which allows space for more equipment in the rack. This vertical PDU does not require additional tools to mount into APC NetShelter Enclosures. Enables a quick recovery from overload events and breakers are ultra-low profile. Packaging Includes PDU, Installation guide, Locking input power cord, Rack Mounting brackets, Safety guide, Serial configuration cable.
Lead time	Usually in Stock

## Main

Main Input Voltage	200 V 208 V 230 V
Main Output Voltage	208 V
Plug standard	NEMA L6-20P
Number of rack unit	0U
Cable length	9.84 ft (3.00 m)
Number of cables	1
Provided equipment	Installation guide Locking input power cord Rack Mounting brackets Serial configuration cable Safety guide

## Physical

Color	Black
Height	70.51 in (179.1 cm)
Width	2.20 in (5.6 cm)
Depth	1.81 in (4.6 cm)
Net Weight	12.63 lb(US) (5.73 kg)
Mounting Location	Side
Mounting preference	No preference
Mounting Mode	Not rack-mountable
USB compatible	No

## Input

Line Rated Current	16 A
Acceptable Input Voltage	200...240 V
Input current limits	20 A
Load Capacity	3300 VA
Input Frequency	50/60 Hz

## Output

Number of power socket outlets	21 IEC 60320 C13 3 IEC 60320 C19
--------------------------------	-------------------------------------

## Conformance

Product certifications	CUL Listed PSE UL Listed VCCI Class A VDE
Standards	EN 55022 Class A EN 55024 EN 61000-3-2 EN 61000-3-3 FCC Part 15 class A ICES-003

## Environmental

Ambient Air Temperature for Operation	23...140 °F (-5...60 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)






## Ordering and shipping details

GTIN	731304277156
Package weight(Lbs)	18.94 lb(US) (8.59 kg)

## Packing Units

Package 1 Height	78.82 in (200.2 cm)
Package 1 width	6.50 in (16.5 cm)
Package 1 Length	4.49 in (11.4 cm)
Number of Units in Package 3	48

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#"> REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#"> EU RoHS Declaration</a>
Lead free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#"> Yes</a>
Environmental Disclosure	<a href="#"> Product Environmental Profile</a>
Circularity Profile	<a href="#"> End Of Life Information</a>
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[AP8959NA3](#)