

Product data sheet

Characteristics

TSXCANCA300

CANopen standard cable - IP20 - IEC 60332-1
- 300 m

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Range of product	CANopen
Bus type	CANopen
Accessory / separate part category	Connection accessories
Accessory / separate part type	Connecting cable
Accessory / separate part destination	CANopen bus
Cable length	984.25 ft (300 m)

Complementary

Marking	CE
Product weight	54.15 lb(US) (24.56 kg)

Environment

IP degree of protection	IP20
-------------------------	------

Ordering and shipping details

Category	22531 - PLCS, TWIDO, TWD
Discount Schedule	PC12
GTIN	003595862011914
Nbr. of units in pkg.	1
Package weight(Lbs)	55.120000000000005
Returnability	N
Country of origin	IT

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1005 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[TSXCANCA300](#)