

Product availability: Non-Stock - Not normally stocked in distribution facility



### Main

Range of product	ConneXium
Product or component type	Ethernet TCP/IP managed switch
Concept	Transparent Ready
Communication port protocol	Ethernet TCP/IP
Port Ethernet	100BASE-FX - 2 port(s) fiber optic 10BASE-T/100BASE-TX - 14 port(s) copper cable
Maximum number of switches in cascade	Unlimited

### Complementary

Integrated connection type	Duplex SC fiber optic Shielded RJ45 copper cable
Transmission support medium	Single mode optical fiber copper cable Twisted shielded pairs cable CAT 5E fiber optic
Attenuation	16 dB 9/125 µm
Ethernet service	SNTP client VLAN IGMP Snooping Data stream control Rapid Spanning Tree Protocol (RSTP) Secure port Configuration via web server Priority port FDR SMTP V3 Multicast filtering
Maximum number of switches in a ring	50
Redundancy	Redundant single ring Redundant power supplies Ring coupling
[Us] rated supply voltage	24 V
Supply voltage limits	18...30 V AC SELV 9.6...60 V DC SELV
Power consumption in W	11.8 W
Electrical connection	Removable connector 6 ways power supply
Mounting support	35 mm symmetrical DIN rail
Marking	CE
Local signalling	1 LED fault 2 LEDs P1 P2 power supplies 1 LED ring manager 1 LED stand-by 1 LED per channel copper port activity 1 LED per channel copper port status
Alarm output	1 voltfree contact 1 A
Alarm function	Redundancy ring fault Data link status Power supply fault Switch fault
Ethernet cabling system	TF switches
Width	4.37 in (111 mm)
Height	5.16 in (131 mm)

Depth	4.37 in (111 mm)
Product weight	1.32 lb(US) (0.6 kg)

## Environment

Ambient air temperature for operation	32...140 °F (0...60 °C)
Relative humidity	> 0...95 % without condensation
IP degree of protection	IP20
Standards	UL 1604 Class 1 Division 2 EN/IEC 61131-2 UL 508 CSA C22.2 No 214 CSA C22.2 No 213 Class I Division 2
Product certifications	C-Tick GL

## Ordering and shipping details

Category	18225 - PLC NTWRK HRDWR & PROWORX SOFTWARE
Discount Schedule	PC41
GTIN	003595864115450
Nbr. of units in pkg.	1
Package weight(Lbs)	2.21
Returnability	N
Country of origin	DE


## Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1050 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------

## Dimensions



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[TCSESM163F2CS0](#)