



Main

Range	Easy TeSys
Device short name	GPEFC
Product or component type	Auxiliary contact block
Mounting location	Front side
Pole contact composition	1 NO + 1 NC
Connections - terminals	Screw clamp terminals1 0.00...0.00 in ² (1... 2.5 mm ²) - solid Screw clamp terminals2 0.00...0.00 in ² (1... 2.5 mm ²) - solid Screw clamp terminals1 0.00...0.00 in ² (0.75... 2.5 mm ²) - flexible without cable end Screw clamp terminals2 0.00...0.00 in ² (0.75... 2.5 mm ²) - flexible without cable end Screw clamp terminals1 0.00...0.00 in ² (0.75... 1.5 mm ²) - flexible with cable end
Quantity per set	Set of 10

Complementary

[Ui] rated insulation voltage	300 V UL 60947-4-1 300 V cUL 250 V IEC 60947-1
[Ue] rated operational voltage	24...240 V AC 24...60 V DC
[Ith] conventional free air thermal current	2.5 A
Protection type	GG fuse 10 A GB2CB06 circuit breaker 10 A
Mechanical durability	100000 cycles
Minimum switching current	5 mA
Minimum switching voltage	17 V
Rated operational power in VA	120 VA at 110...120 V AC-15 - electrical durability: 100000 cycles 120 VA at 230...240 V AC-15 - electrical durability: 100000 cycles 48 VA at 24 V AC-15 - electrical durability: 100000 cycles 60 VA at 48 V AC-15 - electrical durability: 100000 cycles
Rated operational power in W	15 W at 48 V DC-13 - electrical durability: 100000 cycles 24 W at 24 V DC-13 - electrical durability: 100000 cycles 9 W at 60 V DC-13 - electrical durability: 100000 cycles
Tightening torque	1.4 N.m - on screw clamp terminals
Height	0.43 in (11 mm)
Width	1.77 in (45 mm)
Depth	1.14 in (29 mm)
Net Weight	0.04 lb(US) (0.02 kg)

Environment

Environmental characteristic	Normal environment
------------------------------	--------------------

Offer Sustainability

REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[GPEFC11](#)