

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Range	TeSys
Product name	TeSys GK1
Product or component type	Fuse-disconnector
Device short name	GK1 E
Poles description	3P + N

Complementary

Mounting support	Rail
Mounting position	Vertical +/- 23°
Control type	Toggle
System Voltage	690 V power circuit 500 V signalling circuit 440 V signalling circuit
[Ie] rated operational current	50 A for power circuit 6 A signalling circuit
Contacts type and composition	1 NO early-break
Fuse size	14 x 51 mm
Fuse type	GG AM
Connections - terminals	1 solid cable(s) 0...0.04 in ² (2.5...25 mm ²) on connector power circuit 1 flexible cable(s) 0...0.04 in ² (2.5...25 mm ²) without cable end on connector power circuit 1 flexible cable(s) 0...0.02 in ² (2.5...16 mm ²) with cable end on connector power circuit
Tightening torque	17.7 lbf.in (2 N.m) power circuit: on connector

Environment

Standards	IEC 60947-3
IP degree of protection	IP20
Protective treatment	TC
Ambient air temperature for operation	-58...158 °F (-50...70 °C)
Height	3.82 in (97 mm)
Width	4.49 in (114 mm)
Depth	3.52 in (89.5 mm)
Product weight	1.26 lb(US) (0.57 kg)

Ordering and shipping details

Category	22621 - IEC PANEL ACCESSORIES
Discount Schedule	I
GTIN	003389110256369
Nbr. of units in pkg.	1
Package weight(Lbs)	1.5800000000000001

Returnability	N
Country of origin	CZ

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer.
- - - - - Substance 2	Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[GK1EM](#)