

Product data sheet

Characteristics

GS2AHT130

External rotary handle, TeSys GS, black handle, front mounting, 3 positions Test-I-O, NEMA 3R, for GS 30-400A UL



Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 187.50 USD



Main

Range of product	TeSys
Range	TeSys
Device short name	GS2AHT
Product or Component Type	Rotary handle
Range compatibility	TeSys GS GS2EU TeSys GS GS2GU TeSys GS GS2JU TeSys GS GS2MU TeSys GS GS2QU
Type of operating handle	External frontal
Handle colour	Black
Handle front plate colour	Grey

Complementary

Marking	Test-O-I
Rotary handle padlocking	With
Line Rated Current	30 A 60 A 100 A 200 A 400 A
Standards	CSA UL
Product Weight	0.53 Lb(US) (0.24 kg)

Environment

NEMA degree of protection	NEMA 3R/12
---------------------------	------------

Ordering and shipping details

Category	22640 - IEC DISCONNECT-GS1,LK3
Discount Schedule	I11
GTIN	3389119411936
Nbr. of units in pkg.	1
Package weight(Lbs)	8.47 Oz (240 g)
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.76 In (7 cm)
Package 1 width	3.54 In (9 cm)
Package 1 Length	7.09 In (18 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: S-tyrene, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[GS2AHT130](#)