


SPECIFICATIONS

PARAMETERS	VALUES	UNITS
RATED INPUT POWER	0.5	W
MAX INPUT POWER	1	W
IMPEDANCE	$8 \pm 15\%$	OHM
OUTPUT SPL @ 0.5W/0.5M (AT 0.8, 1.0, 1.2, 1.5 kHz)	85 ± 2	dBA
DISTORTION (MAX.)	5%	-
RESONANT FREQUENCY	$600 \pm 20\%$	Hz
FREQUENCY RANGE	600 ~ 20,000	Hz
HOUSING MATERIAL	METAL	-
CONE MATERIAL	MYLAR	-
MAGNET MATERIAL	Nd-Fe-B	-
OPERATING TEMPERATURE	-20 ~ +60	°C
WEIGHT	7.2	grams


THIS DOCUMENT CONTAINS DATA PROPRIETARY TO PROJECTS UNLIMITED, INC. ANY USE OR REPRODUCTION, IN ANY FORM, WITHOUT PRIOR WRITTEN PERMISSION OF PROJECTS UNLIMITED, INC. IS PROHIBITED.
©2003, Projects Unlimited Inc.

REVISION HISTORY

LTR	DESCRIPTION	DATE	APPROVED
-	RELEASED FROM ENGINEERING	11/15/2006	
A	REVISED TO INVENTOR 3-D DRAWING TEMPLATE	7/23/2013	R.W.



4.4 ± 0.3



NOTES:


1. ALL DIMENSIONS ARE IN MILLIMETERS.
2. SPECIFICATIONS SUBJECT TO CHANGE OR WITHDRAWAL WITHOUT NOTICE.
3. THIS PART IS RoHS 2011/65/EU COMPLIANT.

UNLESS OTHERWISE SPECIFIED:

DIMENSIONS ARE IN MILLIMETERS,
TOLERANCES ARE ± 0.5 AND ANGLES ARE $\pm 3^\circ$.

SIZE
A3

AS02808MR-2-R.idw

Designed by	Date	Checked by	Date	Approved by	Date	Drawn Date
J.D.	11/15/2006	D.F.	11/15/2006	R.W.	11/15/2006	7/23/2013
 AS02808MR-2-R Speaker						Edition -
						Sheet 1 / 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[PUI Audio:](#)

[AS02808MR-2-R](#)