

Data Sheet

SMS-1508MS-HT-R


PUI Audio's **High-Temp** line of products is designed to meet and exceed the needs of the automotive industry with ultra-wide operating temperatures. The **SMS-1508MS-HT-R** is designed for high output at 800Hz in a small package.

- Wide -40°C to +105°C operating temperature
- 92 dB output at 10cm with 0.8W input
- Wide 400Hz to 10,000 Hz frequency range


Specifications

Parameters	Values	Units
Rated Input Power	0.8	Watts
Max Input Power	1.0	Watts
Impedance	8±20%	Ohms
Sensitivity @ 1k, 1.6k, 2.0k & 3.2kHz Ave	92±3	dB
Resonant Frequency	800±15%	Hz
Frequency Range	400 ~ 10,000	Hz
Weight	1.7	Grams
Acceptable Soldering Methods	Hand Solder, Reflow	See below for soldering information
Environmental Compliances	RoHS	-
Storage Temperature	-40 ~ +105	°C
Operating Temperature	-40 ~ +105	°C


Measurement Method (0.8W sine sweep, microphone spaced at 10cm, speaker in 1cc enclosure)



Typical Frequency Response (0.8W sine-sweep with microphone spaced at 10cm)




Recommended Soldering Procedure




Profile Feature	Pb-Free Assembly
Average ramp-up rate(T_L to T_p)	3 °C/second max.
Preheat	
-Temperature Min.(T_{smin})	150 °C
-Temperature Min.(T_{smx})	200 °C
-Temperature Min.(t_s)	60~180 seconds
T_{smx} to T_L	
-Ramp-up Rate	3 °C/second max.
Time maintained above:	
- Temperature(T_L)	217 °C
-Time(T_L)	60~150 seconds
Peak temperature(T_p)	245 °C+0/-5 °C
Time within 5 °C of actual Peak temperature (t_p)	6 seconds max.
Ramp-down Rate	6 °C/second max.
Time 25 °C to Peak Temperature	8 minutes max.

Type of Test	Test Specifications
High Temperature Test	Test part at +105°C for 120 hours
Low Temperature Test	Test part at -40°C for 120 hours
Humidity Test	40±2°C, 90 ~ 95% RH, 120 hours
Temperature Cycle Testing	Total 5 cycles, 1 cycle consisting of -40±2°C, 30 minutes 20±5°C 15 minutes 105±2°C, 30 minutes 20±5°C 15 minutes
Vibration Test	The part shall be subjected to a vibration cycle of 10Hz for a period of 1 minute. Total peak amplitude shall be 1.52mm (9.3g). The vibration test shall consist of 2 hours per plane in each three mutually perpendicular planes for a total time of 6 hours.
Shock Test	Sounder shall be measured after being applied a shock of 980m/s ² for each three mutually perpendicular directions to each of 3 times by a half sine wave.
Drop Test	Drop from 700mm height onto the surface of a 10mm thick wooden board.

Dimensions (Tolerance: $\pm 0.5\text{mm}$ unless otherwise specified)



Packaging (Cont'd)



NOTES:

1. 600 PCS per box
2. Total 10 boxes per carton
3. Total 6000 PCS carton
4. Volume: $42 \times 35.5 \times 36.5 \text{ cm}$

Specifications Revisions

Revision	Description	Date
-	Released from Engineering	3/6/2020

Note:

1. Unless otherwise specified:
 - A. All dimensions are in millimeters.
 - B. Default tolerances are $\pm 0.5\text{mm}$ and angles are $\pm 3^\circ$.
2. Specifications subject to change or withdrawal without notice.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[PUI Audio:](#)

[SMS-1508MS-HT-R](#)