







NOTES:

1. ROHS COMPLIANT
2. STORAGE TEMPERATURE: -50°C TO $+150^{\circ}\text{C}$
3. COMPLIANCE TO J-STD:
 - A. J-STD-002: SOLDERABILITY AT 245°C REFLOW PROFILE
 - B. J-STD-020: LEVEL 1, NO MOISTURE SENSITIVE
4. QUALIFIED PER AEC-Q200
5. PPAP LEVEL 3
6. FACTORY TS-16949 CERTIFIED
7. PARTS ARE PACKAGED IN TAPE AND REEL




RECOMMENDED FOOTPRINT



FINAL OUTLINE

ELECTRICAL CHARACTERISTICS AT $+25^{\circ}\text{C}$ UNLESS OTHER SPECIFIED

PARAMETER	SPECIFICATIONS		
OPERATING TEMP	-40°C TO $+125^{\circ}\text{C}$		
URNS RATIO AND POLARITY PINS (1-4) TO PINS (2-3)	$1.00 \pm 2\%$, PER SCHEMATIC		
DC RESISTANCE PINS 1-4; PINS 2-3	5.0 OHMS MAX		
INDUCTANCE (OCL) PINS 1-4; PINS 2-3	160 μH TYP. @ 100 kHz, 100 mV		
INSERTION LOSS (SDD21) PINS (1-2) TO PINS (3-4)	DC-100 KHz	1-60 MHz	
	-0.5 dB MAX	-1.0 dB MAX	
RETURN LOSS (SDD11) (Z OUT = 100 OHM \pm 1%)	1-10 MHz	30 MHz	60 MHz
	-26 dB MIN	-21.1 dB MIN	-18 dB MIN
COMMON- TO COMMON- MODE REJECTION (SCC21)	1 MHz	10-100 MHz	400 MHz
	-23 dB MIN	-42 dB MIN	-25 dB MIN
COMMON- TO DIFFERENTIAL- MODE REJECTION (SDS21)	1-10 MHz	100 MHz	1000 MHz
	-70 dB MIN	-50 dB MIN	-24 dB MIN
CURRENT RATING	100 mA MAX		
VOLTAGE RATING	60 VDC MAX		



SCHEMATIC

ALL DIMENSION ARE SHOWN IN MILLIMETERS.
UNLESS OTHERWISE SPECIFIED,
THE FOLLOWING TOLERANCES APPLY:
X.X = ± 0.1

© Copyright, 2019. Pulse Electronics Corp. All rights reserved. Pulse confidential & proprietary. (03/20/19)

PRODUCT DESCRIPTION	TLA DRAWING	PS DRAWING	SHEET	PART NO.	DATASHEET REV.
CM CHOKE,100BASE-T1,1812 SIZE	AE2002-10	PS-2808.002-D	1 OF 1	AE2002	S

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pulse:

AE2002