



NOTES: UNLESS OTHERWISE SPECIFIED


1. NOTICE: THIS IS A ROHS COMPLIANT COMPONENT/PRODUCT.
ROHS MUST HAVE PRIOR APPROVAL BY THE DESIGN CENTER.

- 2. PLASTIC: THERMOSET PLASTIC MATERIAL WITH FLAMMABILITY RATING UL 94V-0 OR BETTER.
- 3. SOLDERABILITY: CONFORMS TO ANSI/J-STD-002, 245°C REFLOW PEAK TEMPERATURE PER IPC/EIA J-STD-003A
- 4. OPERATING TEMPERATURE: 0°C TO +70°C
- 5. STORAGE TEMPERATURE: -20°C TO +125°C
- JEDEC MOISTURE: LEVEL 1.
- 7. DIMENSIONS ARE IN INCHES WITH THE FOLLOWING TOLERANCES:


 .XX= ±.01
 - .XXX= ±.005
- B. REVISION: MP1,MP2, ARE PRELIMINARY.








SUGGESTED LAND PATTERN



@ Copyright, 2013. Pulse Electronics Corp. All rights reserved. Drawing specifications subject to change without notice. (08/27/13)

PULSE CONFIDENTIAL PRODUCT DESCRIPTION		PS DRAWING	SHEET:	DWG. NO./ PART NO.	REV.
PROPRIETARY 10/	10/100 PCMCIA XFMR/CHOKE	PS-2762.001-A	1	H0013FNL	MP1





SCHEMATIC

ELECTRICAL CHARACTERISTICS AT +25°C

PARAMETER	SPECIFICATIONS						
OPERATING TEMP	0°C - 70 °C						
TURNS RATIO	1 : 1 ±2%						
POLARITY	PER SCHEMATIC						
	100 KHz			1-125 MHz			
INSERTION LOSS	-1.2	dB	MAX	-0.2-0.002*f ^{^1.4} dB MAX			
RETURN LOSS	.1-	30	MHz	30-60 MHz	60-80 MHz		
$(Z \text{ OUT} = 100 \text{ OHM } \pm 15\%)$	-16	dΒ	MIN	-10+20*L0G ₁₀ (f/60 MHz) dB MIN	-10 dB MIN		
INDUCTANCE (OCL) (MEDIA SIDE, 0°C-70°C)	350 uH MIN (MEASURED AND WITH		(MEASURED AT 100 KH AND WITH 8 mA D	z, 100 mVRMS) C BIAS			
	1 MHz		z	10-100 MHz			
CROSSTALK, ADJACENT CHANNELS	-50	dΒ	MIN	-55+22*LOG ₁₀ (f/10) dB MIN			
COMMON MODE	2 MHz			30-200 MHz			
COMMON MODE REJECTION RATIO	-50	dΒ	MIN	-15+20*LOG ₁₀ (f/200) dB MIN			
DC RESISTANCE, 1/2 WINDING	.65 OHMS MAX						
DC RESISTANCE IMBALANCE	±.065 OHMS MAX (CENTER TAP SYMMETRY)						
INPUT — OUTPUT 1500 VRMS N			VRMS MIN @ 60 SE	CONDS			

NOTE: f IS FREQUENCY IN MHz.

@ Copyright, 2013. Pulse Electronics Corp. All rights reserved. Drawing specifications subject to change without notice. (08/27/13)

PULSE CONFIDENTIAL	PRODUCT DESCRIPTION	PS DRAWING	SHEET:	DWG. NO./ PART NO.	REV.
PROPRIETARY	10/100 PCMCIA XFMR/CHOKE	PS-2762.001-A	2	H0013FNL	MP1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pulse: