

Description: 2.4-2.5 / 5.15-7.125 GHz Stick Antenna

Series: External Antenna

PART NUMBER: W5029X



W5029

W5029RASM

W5029RPG

W5029RPGT

**Features:**

- WiFi-6E Dual-Band
- DSRC
- Multi band 2.4-2.5/5.15-7.125GHz
- IP65
- P/N: W5029

R/A RP SMA Male, length 78mm

- P/N: W5029RPG/W5029RPGT

RP SMA Male. length 76mm

- P/N: W5029RASM

R/A SMA Male, length 76.5mm

Applications:

- Zigbee, BLE/BT, WLAN (2.4GHz, 5-7GHz)
- DSRC V2x communication
- Rugged Outdoor Systems
- Marine, Mining, Utility, Oil/Gas Environments
- Industrial Applications
- Metering, Security, IoT Applications
- Outdoor Networking
- Data Transmission, Access Points

Issue: 2103

In the effort to improve our products, we reserve the right to make changes judged to be necessary.

CONFIDENTIAL AND PROPRIETARY INFORMATION

This document contains confidential and proprietary information of Pulse Electronics, Inc. (Pulse) and is protected by copyright, trade secret and other state and federal laws. Its receipt or possession does not convey any rights to reproduce, disclose its contents, or to manufacture, use or sell anything it may describe. Reproduction, disclosure or use without specific written authorization of Pulse is strictly forbidden.

For more information:

Pulse Worldwide Headquarters
15255 Innovation Drive #100
San Diego, CA 92128
USA
Tel: 1-858-674-8100

Pulse/Larsen Antennas
18110 SE 34th St Bldg 2 Suite 250
Vancouver, WA 98683
USA
Tel: 1-360-944-7551

Europe Headquarters
Pulse GmbH & Co, KG
Zeppelinstrasse 15
Herrenberg, Germany
Tel: 49 7032 7806 0

Pulse (Suzhou) Wireless Products Co, Inc.
99 Huo Ju Road(#29 Bldg, 4th Phase
Suzhou New District
Jiangsu Province, Suzhou 215009 PR China
Tel: 86 512 6807 9998



Description: 2.4-2.5 / 5.15-7.125 GHz Stick Antenna

Series: External Antenna

PART NUMBER: W5029X

This document covers all product variants of the following product family

Antennas	Length	Connector
W5029	78mm	Right Angle RP SMA male (Au plating)
W5029RASM	76.5mm	Right Angle SMA male (Au plating)
W5029RPG	76mm	Straight RP SMA Male (Au plating)
W5029RPGT	76mm	Straight RP SMA Male (Ni plating)

Issue: 2103

In the effort to improve our products, we reserve the right to make changes judged to be necessary.

CONFIDENTIAL AND PROPRIETARY INFORMATION

This document contains confidential and proprietary information of Pulse Electronics, Inc. (Pulse) and is protected by copyright, trade secret and other state and federal laws. Its receipt or possession does not convey any rights to reproduce, disclose its contents, or to manufacture, use or sell anything it may describe. Reproduction, disclosure or use without specific written authorization of Pulse is strictly forbidden.

Description: 2.4-2.5 / 5.15-7.125 GHz Stick Antenna

Series: External Antenna

PART NUMBER: W5029X

ELECTRICAL SPECIFICATIONS

Frequency	2.4-2.5GHz/5.15-7.125GHz
Nominal Impedance	50Ω
Return Loss	2.4-2.5GHz <-10dB 5.15-7.125GHz <-4dB
Peak Gain	2.4-2.5GHz 1.8dBi +/-0.4 dB 5.15-7.125GHz 2.55dBi +/-2dB Radiation Pattern Omni in Horizontal plane
Polarization:	Vertical
Power withstanding	1W

Description: 2.4-2.5 / 5.15-7.125 GHz Stick Antenna

Series: External Antenna

PART NUMBER: W5029X


MECHANICAL SPECIFICATIONS

Plastic radome	TPEE
Color	Black
Weight	
W5029	11.36 g
W5029RASM	11.36 g
W5029RPG	7.82 g
W5029RPGT	7.82 g
Overall Length	
W5029	78 mm
W5029RASM	76.5mm
W5029RPG	76 mm
W5029RPGT	76 mm
IP Rate	IP65

ENVIRONMENTAL SPECIFICATIONS

Operating temperature	-35/+65° C
Storage Temperature	-30/+75° C

MECHANICAL DRAWING



1, Dimension show as mm (inch)

2, Item 1 is tube, and item 2 is connector


Description: 2.4-2.5 / 5.15-7.125 GHz Stick Antenna

Series: External Antenna

PART NUMBER: W5029X

CHARTS

Return Loss



(*) All RF parameters measured with free space

Issue: 2103

In the effort to improve our products, we reserve the right to make changes judged to be necessary.

CONFIDENTIAL AND PROPRIETARY INFORMATION

This document contains confidential and proprietary information of Pulse Electronics, Inc. (Pulse) and is protected by copyright, trade secret and other state and federal laws. Its receipt or possession does not convey any rights to reproduce, disclose its contents, or to manufacture, use or sell anything it may describe. Reproduction, disclosure or use without specific written authorization of Pulse is strictly forbidden.


Description: 2.4-2.5 / 5.15-7.125 GHz Stick Antenna

Series: External Antenna

PART NUMBER: W5029X

CHARTS

Efficiency(%)



(*) All RF parameters measured with free space


Description: 2.4-2.5 / 5.15-7.125 GHz Stick Antenna

Series: External Antenna

PART NUMBER: W5029X

CHARTS

Peak Gain (dBi)




(*) All RF parameters measured with free space


CHARTS

Free Space Radiation Pattern

Elevation Plane



Horizontal Plane



(*) All RF parameters measured with free space

Description: 2.4-2.5 / 5.15-7.125 GHz Stick Antenna


Series: External Antenna

PART NUMBER: W5029X


CHARTS

Free Space Radiation Pattern

Elevation Plane



Horizontal Plane



(*) All RF parameters measured with free space

Issue: 2103

In the effort to improve our products, we reserve the right to make changes judged to be necessary.

CONFIDENTIAL AND PROPRIETARY INFORMATION

This document contains confidential and proprietary information of Pulse Electronics, Inc. (Pulse) and is protected by copyright, trade secret and other state and federal laws. Its receipt or possession does not convey any rights to reproduce, disclose its contents, or to manufacture, use or sell anything it may describe. Reproduction, disclosure or use without specific written authorization of Pulse is strictly forbidden.

Description: 2.4-2.5 / 5.15-7.125 GHz Stick Antenna**Series: External Antenna****PART NUMBER: W5029X****PACKAGING**

20PCS/Bullet PE bag
30 Bullet PE bag/ Carton box
Total 600PCS antenna/ Carton box

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pulse:

[W5029](#) [W5029RPGT](#) [W5029RPG](#)