


THESE DRAWINGS ARE THE PROPERTY OF QUALTEK ELECTRONICS AND NOT TO BE REPRODUCED FOR OR COMMUNICATED TO A THIRD PARTY WITHOUT THE EXPRESS WRITTEN PERMISSION OF AN OFFICER OF QUALTEK ELECTRONICS.

REVISION			
REV.	DESCRIPTION	DATE	APPROVED
B	RoHS Compliancy	06-01-06	DP



NOTES:

MATERIAL:

MOULDING: NYLON, FLAMMABILITY RATING UL 94V-0
CONTACTS: BRASS PINS, NICKEL PLATED
TAGS, TIN PLATED
SCREW TERMINALS, NICKEL PLATED

RATING:

UL,CSA: 15A 250V AC
VDE: 10A 250V AC
CONTACT RESISTANCE: <10m OHM
INSULATION RESISTANCE: >10³M OHM
A.C. BREAKDOWN:
POLE-POLE: 5kV
POLES-PANEL: 5.4kV
OPERATING TEMPERATURE: -40° C TO +70° C
MAX. PIN TEMPERATURE: +65° C
APPROVALS: UL,CSA,VDE
RoHS COMPLIANT

CONTROLLED

Dim range (mm)	Tolerance +/- (mm)	Qualtek Electronics Corp. PPC DIVISION		
		Part Number: 713-00/63	RoHS Compliant	
0-1	0.15	Description: AC RECEPTACLE		
1-6	0.20			
6-18	0.30	Drawn / Date B.Zhang 04-15-02	UNIT: mm	REV. B
18-50	0.50		Checked / Date	Approved / Date
50-120	0.70			
120-250	0.90			
250-500	1.20			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Qualtek:](#)

[713-00/63](#)