

280x89mm

AC AXIAL FAN

FKA2-28089 Series

**Features:**

- Motor: Capacitor-Run Induction Motor
- Motor Protection: Thermal Protected
- Bearing Type: Two Ball
- Connection: UL 1430 AWG 22, 300mm Wire Leads or Terminal
- Frame Material: Aluminum Alloy
- Impeller Material: Plastic UL94V-0
- Operating Temp:
Two Ball: -10°C~70°C
- Life Expectancy:
Two Ball: 50,000 Hours


**Fan-S Division**

Model No.	Volt.	Freq.	Current	Power	Rated Speed	Maximum AirFlow		Maximum Static Pressure		Noise Level	Weight
	(VAC)	(Hz)	(A)	(W)	(rpm)	(CMM)	(CFM)	(InAq)	(mmAq)	(dB/A)	(g)
FKA2-28089NBM** 3F	115	50/60	0.82/0.67	61.0/60.0	1500/1700	19.2/22.9	680/810	0.39/0.50	9.8/12.8	56.0/59.0	3500
FKA2-28089QBM** 3F	230	50/60	0.42/0.35	62.0/65.0	1500/1700	19.2/22.9	680/810	0.39/0.50	9.8/12.8	56.0/59.0	3500



** Indicates "W" (Wire Leads) or "T" (Terminal)

Noise is measured at the distance of one (1) meter from the axis of intake.

50Hz



60Hz



Qualtek
Electronics Corporation

ISO-9001 Company

www.qualtekusa.com

REV. D

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Qualtek:](#)

[FKA2-28089NBHT3F](#) [FKA2-28089NBHW3F](#) [FKA2-28089NBMT3F](#) [FKA2-28089NBMW3F](#) [FKA2-28089QBHT3F](#)
[FKA2-28089QBHW3F](#) [FKA2-28089QBMT3F](#) [FKA2-28089QBMW3F](#)